

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583294

Luminaire Tested: **HCC6S07D010MW-HM60525827-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583294
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010MW-HM60525827-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 813.2 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583294
CATALOG NUMBER: HCC6S07D010MW-HM60525827-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583294

CATALOG NUMBER: HCC6S07D010MW-HM60525827-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23929	23929	23929
5°	24989	23861	22766
10°	25673	23446	21387
15°	26305	22946	20046
20°	26427	21906	18406
25°	25870	20505	16882
30°	24548	18857	15471
35°	22292	16945	13887
40°	19429	15100	12488
45°	16800	13211	10978
50°	14678	11377	9620
55°	12970	9997	8248
60°	11666	8760	7160
65°	10429	7627	6940
70°	9312	6508	6508
75°	8091	5465	6100
80°	6472	4641	5588
85°	4403	4088	4780



TEST NUMBER: P583294

CATALOG NUMBER: HCC6S07D010MW-HM60525827-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	5.0
10°-20°	114.0	14.0
20°-30°	158.9	19.5
30°-40°	163.8	20.1
40°-50°	135.7	16.7
50°-60°	97.5	12.0
60°-70°	62.1	7.6
70°-80°	31.9	3.9
80°-90°	8.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.0	38.6
0°-40°	477.8	58.8
0°-60°	711.0	87.4
0°-90°	813.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	813.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	436	436	436	436	436	
5°	454	447	434	420	414	44
15°	464	446	404	367	353	131
25°	428	398	339	296	279	196
35°	333	306	253	220	208	207
45°	217	202	170	149	142	168
55°	136	124	105	93	86	122
65°	80	72	59	51	54	81
75°	38	33	26	27	29	41
85°	7	6	6	7	8	9
90°	0	0	0	0	0	



TEST NUMBER: P583294

CATALOG NUMBER: HCC6S07D010MW-HM60525827-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	436.5	436.5	436.5	436.5	436.5	436.5	436.5	436.5	436.5
2.5°	444.8	443.0	440.6	438.2	434.7	430.7	427.1	426.0	424.2
5°	454.1	451.8	447.1	441.2	433.6	426.0	419.5	415.4	413.7
7.5°	460.0	457.1	450.6	440.6	429.5	418.3	408.9	403.0	400.7
10°	461.2	458.3	449.5	436.0	421.2	406.0	394.3	387.1	384.2
12.5°	462.9	458.9	447.6	431.8	413.0	395.4	380.7	372.0	369.0
15°	463.5	458.9	445.9	426.6	404.3	383.1	367.2	356.7	353.2
17.5°	461.2	455.9	440.6	417.2	391.9	369.6	350.8	339.6	334.9
20°	453.0	447.1	429.5	403.0	375.5	351.9	332.5	320.8	315.5
22.5°	442.4	434.7	414.8	386.6	357.8	333.1	313.7	301.9	296.7
25°	427.7	420.7	398.4	368.3	339.0	313.2	295.5	283.1	279.1
27.5°	410.7	402.4	379.6	349.5	319.6	293.8	276.7	265.6	260.3
30°	387.8	380.1	357.2	327.2	297.9	273.8	256.2	246.8	244.4
32.5°	360.7	354.3	332.0	303.8	275.5	253.2	238.5	228.5	226.1
35°	333.1	325.5	306.1	279.6	253.2	233.3	219.7	211.0	207.5
37.5°	303.2	296.2	279.6	256.2	232.7	213.9	202.1	194.4	190.9
40°	271.5	266.1	250.8	232.0	211.0	194.4	184.5	178.0	174.5
42.5°	242.0	236.8	226.1	208.6	190.9	176.3	167.5	161.6	158.6
45°	216.7	212.1	201.6	186.3	170.4	158.1	148.6	144.6	141.6
47.5°	191.6	189.2	179.8	165.6	151.0	140.4	133.9	129.3	126.9
50°	172.1	169.2	160.4	145.7	133.4	125.2	119.3	115.1	112.8
52.5°	152.2	149.2	141.1	128.7	118.6	111.0	105.1	101.6	99.3
55°	135.7	133.4	124.5	113.4	104.6	98.1	92.8	88.7	86.3
57.5°	120.4	118.1	109.9	99.3	91.7	85.8	81.1	77.6	74.7
60°	106.4	104.6	96.3	86.3	79.9	74.0	69.9	67.0	65.3
62.5°	94.0	90.5	83.4	74.7	68.8	64.0	59.9	58.1	59.4
65°	80.4	78.7	71.7	64.0	58.8	54.0	51.1	52.3	53.5
67.5°	69.3	67.0	61.1	54.0	49.4	45.8	44.1	46.5	47.0
70°	58.1	55.9	50.5	44.6	40.6	38.2	38.2	40.0	40.6
72.5°	47.6	45.8	41.1	36.5	33.5	31.7	32.9	34.1	34.7
75°	38.2	36.5	32.9	28.8	25.8	25.8	27.1	28.2	28.8
77.5°	29.3	28.2	24.7	21.8	20.5	20.5	21.8	22.3	22.9
80°	20.5	19.4	17.7	15.9	14.7	15.9	17.0	17.0	17.7
82.5°	13.5	12.9	11.8	10.5	10.5	11.2	11.8	12.3	12.3
85°	7.0	7.0	6.5	5.9	6.5	7.0	7.0	7.6	7.6
87.5°	2.4	2.4	2.4	2.4	2.9	2.9	2.9	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)