

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582826

Luminaire Tested: **HCC6W50D010MB-HM64560935-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MB-HM64560935-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4491.7 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582826
CATALOG NUMBER: HCC6W50D010MB-HM64560935-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582826

CATALOG NUMBER: HCC6W50D010MB-HM64560935-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	132182	132182	132182
5°	138053	131801	125732
10°	141809	129529	118151
15°	145319	126720	110693
20°	145974	120976	101666
25°	142907	113269	93247
30°	135584	104155	85456
35°	123145	93612	76667
40°	107294	83378	68972
45°	92839	72961	60642
50°	81089	62829	53141
55°	71653	55205	45590
60°	64403	48384	39492
65°	57672	42093	38318
70°	51483	35887	35887
75°	44670	30246	33678
80°	35863	25603	30717
85°	24531	22455	26543



TEST NUMBER: P582826
 CATALOG NUMBER: HCC6W50D010MB-HM64560935-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.6	5.0
10°-20°	630.0	14.0
20°-30°	877.9	19.5
30°-40°	904.6	20.1
40°-50°	749.7	16.7
50°-60°	538.8	12.0
60°-70°	343.1	7.6
70°-80°	176.2	3.9
80°-90°	44.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1734.5	38.6
0°-40°	2639.1	58.8
0°-60°	3927.5	87.4
0°-90°	4491.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4491.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2411	2411	2411	2411	2411	
5°	2509	2470	2395	2317	2285	241
15°	2560	2463	2233	2028	1950	722
25°	2363	2200	1873	1632	1542	1083
35°	1840	1691	1399	1214	1146	1143
45°	1198	1113	941	821	782	927
55°	750	688	578	513	477	675
65°	445	396	324	282	295	445
75°	211	182	143	149	159	225
85°	39	36	36	39	42	50
90°	0	0	0	0	0	



TEST NUMBER: P582826

CATALOG NUMBER: HCC6W50D010MB-HM64560935-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2411.2	2411.2	2411.2	2411.2	2411.2	2411.2	2411.2	2411.2	2411.2
2.5°	2456.7	2446.9	2434.0	2421.0	2401.6	2378.8	2359.4	2352.9	2343.1
5°	2508.7	2495.7	2469.7	2437.2	2395.1	2352.9	2317.1	2294.4	2284.8
7.5°	2541.0	2524.9	2489.2	2434.0	2372.3	2310.6	2258.8	2226.3	2213.3
10°	2547.5	2531.4	2482.7	2408.1	2326.9	2242.5	2177.6	2138.7	2122.5
12.5°	2557.3	2534.5	2472.9	2385.3	2281.5	2184.1	2103.0	2054.2	2038.1
15°	2560.5	2534.5	2463.2	2356.1	2232.8	2116.0	2028.4	1969.9	1950.4
17.5°	2547.5	2518.4	2434.0	2304.1	2164.7	2041.4	1937.4	1875.8	1849.8
20°	2502.2	2469.7	2372.3	2226.3	2073.7	1943.9	1836.8	1772.0	1742.7
22.5°	2443.7	2401.6	2291.1	2135.4	1976.4	1840.1	1733.0	1668.0	1638.9
25°	2362.6	2323.6	2200.3	2034.9	1872.6	1729.8	1632.4	1564.2	1541.6
27.5°	2268.5	2223.0	2096.5	1930.9	1765.5	1622.7	1528.6	1466.9	1437.6
30°	2141.9	2099.7	1973.1	1807.6	1645.4	1512.3	1415.0	1363.0	1350.0
32.5°	1992.6	1956.9	1833.6	1677.8	1522.1	1398.8	1317.6	1262.4	1249.5
35°	1840.1	1798.0	1690.8	1544.7	1398.8	1288.4	1213.7	1165.1	1145.6
37.5°	1674.5	1635.7	1544.7	1415.0	1285.2	1181.4	1116.4	1074.2	1054.8
40°	1499.3	1470.1	1385.8	1281.9	1165.1	1074.2	1019.1	983.3	963.8
42.5°	1337.1	1307.8	1249.5	1152.1	1054.8	973.6	925.0	892.5	876.2
45°	1197.5	1171.6	1113.1	1028.8	941.1	873.0	821.0	798.4	782.2
47.5°	1057.9	1044.9	993.1	915.2	834.0	775.7	739.9	713.9	701.0
50°	950.8	934.6	886.0	804.9	736.7	691.2	658.8	636.1	623.1
52.5°	840.5	824.3	778.9	710.7	655.6	613.4	580.9	561.4	548.5
55°	749.7	736.7	688.1	626.4	577.6	542.0	512.8	490.0	477.0
57.5°	665.3	652.3	606.9	548.5	506.3	473.8	447.8	428.3	412.2
60°	587.4	577.6	532.3	477.0	441.3	408.9	386.2	370.0	360.2
62.5°	519.3	499.8	460.8	412.2	379.7	353.7	331.0	321.2	327.7
65°	444.6	434.8	395.9	353.7	324.5	298.6	282.4	288.9	295.4
67.5°	383.0	370.0	337.5	298.6	272.6	253.1	243.4	256.4	259.6
70°	321.2	308.4	279.1	246.6	223.9	210.9	210.9	220.7	223.9
72.5°	262.9	253.1	227.2	201.2	184.9	175.3	181.8	188.3	191.4
75°	210.9	201.2	181.8	159.0	142.8	142.8	149.3	155.8	159.0
77.5°	162.3	155.8	136.3	120.1	113.6	113.6	120.1	123.3	126.6
80°	113.6	107.1	97.3	87.6	81.1	87.6	94.1	94.1	97.3
82.5°	74.6	71.5	65.0	58.5	58.5	61.6	65.0	68.1	68.1
85°	39.0	39.0	35.7	32.5	35.7	39.0	39.0	42.2	42.2
87.5°	13.0	13.0	13.0	13.0	16.2	16.2	16.2	16.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)