

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582819

Luminaire Tested: **HCC6W50D010SL-HM64560935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010SL-HM64560935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4851.9 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582819
CATALOG NUMBER: HCC6W50D010SL-HM64560935-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582819

CATALOG NUMBER: HCC6W50D010SL-HM64560935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	135740	135740	135740
5°	137156	135901	135010
10°	139103	135485	134038
15°	142373	134638	133349
20°	143693	130631	131011
25°	140548	124060	126413
30°	133115	115246	119151
35°	120535	105330	109245
40°	104968	95214	98699
45°	89064	84280	87304
50°	78872	73618	75563
55°	69474	62966	62660
60°	62265	53011	48746
65°	55557	42508	34945
70°	48902	30678	21847
75°	41239	18554	12391
80°	31759	8208	5114
85°	18367	2013	2013



TEST NUMBER: P582819
 CATALOG NUMBER: HCC6W50D010SL-HM64560935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.0	4.8
10°-20°	675.5	13.9
20°-30°	976.5	20.1
30°-40°	1027.5	21.2
40°-50°	863.8	17.8
50°-60°	606.2	12.5
60°-70°	333.5	6.9
70°-80°	118.4	2.4
80°-90°	15.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1887.0	38.9
0°-40°	2914.5	60.1
0°-60°	4384.5	90.4
0°-90°	4851.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4851.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2476	2476	2476	2476	2476	
5°	2492	2486	2470	2460	2453	238
15°	2509	2466	2372	2343	2350	708
25°	2324	2207	2051	2054	2090	1063
35°	1801	1697	1574	1606	1632	1116
45°	1149	1116	1087	1113	1126	901
55°	727	688	659	659	656	654
65°	428	383	328	269	269	426
75°	195	156	88	58	58	209
85°	29	16	3	3	3	40
90°	0	0	0	0	0	



TEST NUMBER: P582819

CATALOG NUMBER: HCC6W50D010SL-HM64560935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2476.1	2476.1	2476.1	2476.1	2476.1	2476.1	2476.1	2476.1	2476.1
2.5°	2476.1	2476.1	2472.9	2472.9	2466.4	2466.4	2463.1	2463.1	2463.1
5°	2492.4	2492.4	2485.9	2476.1	2469.6	2459.9	2459.9	2456.6	2453.4
7.5°	2502.1	2498.9	2489.1	2476.1	2459.9	2443.6	2437.2	2440.4	2437.2
10°	2498.9	2492.4	2479.4	2453.4	2433.9	2411.2	2407.9	2404.8	2407.9
12.5°	2505.4	2495.6	2469.6	2437.2	2404.8	2378.8	2375.5	2375.5	2378.8
15°	2508.6	2498.9	2466.4	2417.7	2372.3	2346.3	2343.1	2346.3	2349.6
17.5°	2498.9	2485.9	2437.2	2372.3	2320.3	2294.3	2294.3	2300.8	2307.3
20°	2463.1	2443.6	2375.5	2297.6	2239.2	2219.7	2226.2	2239.2	2245.7
22.5°	2398.3	2375.5	2297.6	2210.0	2148.4	2132.2	2148.4	2164.5	2171.0
25°	2323.6	2297.6	2206.8	2115.9	2051.0	2031.6	2054.2	2080.2	2089.9
27.5°	2223.0	2193.8	2109.4	2005.6	1940.6	1930.9	1956.9	1986.1	1992.6
30°	2102.9	2070.4	1976.4	1879.0	1820.6	1817.3	1846.5	1872.5	1882.3
32.5°	1956.9	1927.6	1846.5	1749.2	1697.2	1697.2	1726.5	1749.2	1758.9
35°	1801.1	1768.7	1697.2	1616.1	1573.9	1577.2	1606.4	1622.6	1632.4
37.5°	1616.1	1606.4	1551.2	1483.1	1453.8	1460.3	1483.1	1496.1	1505.8
40°	1466.8	1440.9	1405.2	1350.0	1330.5	1337.0	1359.8	1372.8	1379.2
42.5°	1304.5	1288.4	1259.2	1220.2	1207.2	1217.0	1236.4	1246.2	1242.9
45°	1148.8	1145.6	1116.4	1093.6	1087.1	1100.1	1113.1	1122.9	1126.1
47.5°	1035.3	1022.3	996.3	980.1	973.6	986.6	999.5	1006.0	1006.0
50°	924.8	912.0	886.0	869.7	863.2	876.2	886.0	892.5	886.0
52.5°	814.5	801.5	778.9	759.4	756.2	762.7	765.9	769.1	775.6
55°	726.9	713.9	687.9	665.3	658.8	662.1	658.8	658.8	655.6
57.5°	642.6	629.6	603.6	577.6	567.9	564.6	555.0	551.6	548.5
60°	567.9	551.6	525.8	496.5	483.5	470.5	454.3	444.6	444.6
62.5°	496.5	480.3	451.1	425.2	405.7	382.9	357.0	344.0	344.0
65°	428.3	415.4	382.9	353.7	327.7	298.6	269.4	262.9	269.4
67.5°	363.5	350.5	318.0	288.9	256.4	220.7	194.7	194.7	201.2
70°	305.1	292.1	262.9	227.2	191.4	155.8	136.3	136.3	136.3
72.5°	249.9	236.9	204.4	172.0	136.3	100.6	90.8	94.1	90.8
75°	194.7	184.9	155.8	120.1	87.6	61.6	58.5	55.2	58.5
77.5°	146.1	136.3	110.3	77.8	48.7	35.7	32.5	32.5	32.5
80°	100.6	90.8	71.5	45.5	26.0	16.2	16.2	16.2	16.2
82.5°	61.6	52.0	39.0	22.7	9.7	9.7	9.7	9.7	9.7
85°	29.2	22.7	16.2	6.5	3.2	3.2	3.2	3.2	3.2
87.5°	6.5	6.5	3.2	3.2	0.0	3.2	3.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)