

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583291

Luminaire Tested: **HCC6S07D010MB-HM60525827-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010MB-HM60525827-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 857.8 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583291
CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583291

CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89																
	2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78	78	78	78	78	78	78	78	78	78	78	78																
	3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69	69	69	69	69	69	69	69	69	69	69	69	69															
	4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62	62	62	62	62	62	62	62	62	62	62	62	62															
	5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56	56	56	56	56	56	56	56	56	56	56	56	56															
	6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51	51	51	51	51	51	51	51	51	51	51	51	51															
	7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46	46	46	46	46	46	46	46	46	46	46	46	46	46														
	8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42	42	42	42	42	42	42	42	42	42	42	42	42	42														
	9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	39	39	39	39	39	39	39	39	39	39	39	39	39														
	10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36	36	36	36	36	36	36	36	36	36	36	36	36	36														

AVERAGE LUMINANCE (cd/sqm):

	0°	
0°	29274	
5°	29254	
10°	28974	
15°	28672	
20°	27862	
25°	26687	
30°	24763	
35°	21308	
40°	15551	
45°	10652	
50°	8571	
55°	7474	
60°	6896	
65°	6551	
70°	6123	
75°	5740	
80°	5177	
85°	4403	



TEST NUMBER: P583291
 CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	5.9
10°-20°	141.9	16.5
20°-30°	201.8	23.5
30°-40°	194.3	22.6
40°-50°	111.8	13.0
50°-60°	70.8	8.3
60°-70°	50.1	5.8
70°-80°	28.6	3.3
80°-90°	8.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	394.1	45.9
0°-40°	588.4	68.6
0°-60°	771.0	89.9
0°-90°	857.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	857.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	534	
5°	532	50
15°	505	142
25°	441	202
35°	318	194
45°	137	112
55°	78	71
65°	50	50
75°	27	29
85°	7	8
90°	0	



TEST NUMBER: P583291
CATALOG NUMBER: HCC6S07D010MB-HM60525827-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	534.0
2.5°	531.6
5°	531.6
7.5°	528.1
10°	520.5
12.5°	512.8
15°	505.2
17.5°	493.4
20°	477.6
22.5°	460.0
25°	441.2
27.5°	418.3
30°	391.2
32.5°	358.4
35°	318.4
37.5°	269.7
40°	217.3
42.5°	171.5
45°	137.4
47.5°	115.7
50°	100.5
52.5°	88.1
55°	78.2
57.5°	69.3
60°	62.9
62.5°	57.0
65°	50.5
67.5°	44.6
70°	38.2
72.5°	32.3
75°	27.1
77.5°	21.8
80°	16.4
82.5°	11.8
85°	7.0
87.5°	2.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)