

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593374

Luminaire Tested: **HCC6W50D010MB-HM64560950-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MB-HM64560950-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4633.4 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593374
CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWW

Luminous Intensity Polar Plot





TEST NUMBER: P593374

CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	136360	136360	136360
5°	142406	135962	129694
10°	146290	133620	121880
15°	149904	130716	114189
20°	150577	124792	104875
25°	147414	116837	96187
30°	139863	107441	88153
35°	127033	96557	79083
40°	110679	86004	71155
45°	95770	75271	62557
50°	83656	64817	54821
55°	73909	56954	47033
60°	66442	49919	40731
65°	59488	43429	39524
70°	53118	37025	37025
75°	46111	31199	34737
80°	37000	26424	31696
85°	25285	23147	27424



TEST NUMBER: P593374
 CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.8	5.0
10°-20°	649.8	14.0
20°-30°	905.6	19.5
30°-40°	933.1	20.1
40°-50°	773.4	16.7
50°-60°	555.8	12.0
60°-70°	353.9	7.6
70°-80°	181.8	3.9
80°-90°	46.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1789.2	38.6
0°-40°	2722.4	58.8
0°-60°	4051.5	87.4
0°-90°	4633.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4633.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2487	2487	2487	2487	2487	
5°	2588	2548	2471	2390	2357	248
15°	2641	2541	2303	2092	2012	744
25°	2437	2270	1932	1684	1590	1117
35°	1898	1744	1443	1252	1182	1179
45°	1235	1148	971	847	807	956
55°	773	710	596	529	492	697
65°	459	408	335	291	305	459
75°	218	187	147	154	164	232
85°	40	37	37	40	44	51
90°	0	0	0	0	0	



TEST NUMBER: P593374

CATALOG NUMBER: HCC6W50D010MB-HM64560950-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4	2487.4
2.5°	2534.2	2524.2	2510.8	2497.5	2477.3	2453.9	2433.8	2427.1	2417.0
5°	2587.8	2574.5	2547.7	2514.1	2470.7	2427.1	2390.2	2366.8	2356.8
7.5°	2621.2	2604.6	2567.7	2510.8	2447.2	2383.6	2330.0	2296.6	2283.1
10°	2628.0	2611.2	2561.0	2484.0	2400.4	2313.3	2246.4	2206.1	2189.5
12.5°	2638.0	2614.6	2551.0	2460.6	2353.5	2253.0	2169.4	2119.1	2102.4
15°	2641.3	2614.6	2540.9	2430.5	2303.2	2182.7	2092.4	2032.0	2012.0
17.5°	2628.0	2597.8	2510.8	2376.9	2232.9	2105.7	1998.6	1935.0	1908.3
20°	2581.1	2547.7	2447.2	2296.6	2139.1	2005.3	1894.8	1827.8	1797.7
22.5°	2520.8	2477.3	2363.5	2202.8	2038.8	1898.2	1787.7	1720.7	1690.6
25°	2437.1	2397.0	2269.8	2099.0	1931.6	1784.4	1683.9	1613.6	1590.2
27.5°	2340.0	2293.1	2162.6	1991.9	1821.2	1673.8	1576.8	1513.2	1483.1
30°	2209.5	2166.0	2035.5	1864.7	1697.3	1560.1	1459.6	1406.1	1392.6
32.5°	2055.5	2018.7	1891.5	1730.8	1570.1	1442.8	1359.2	1302.3	1288.8
35°	1898.2	1854.6	1744.2	1593.5	1442.8	1329.1	1252.1	1201.8	1181.7
37.5°	1727.4	1687.3	1593.5	1459.6	1325.7	1218.6	1151.6	1108.1	1088.1
40°	1546.6	1516.5	1429.5	1322.4	1201.8	1108.1	1051.2	1014.4	994.3
42.5°	1379.3	1349.2	1288.8	1188.4	1088.1	1004.3	954.1	920.6	903.9
45°	1235.3	1208.5	1148.3	1061.2	970.9	900.5	847.0	823.5	806.9
47.5°	1091.4	1078.0	1024.4	944.1	860.4	800.1	763.3	736.5	723.1
50°	980.9	964.2	914.0	830.2	760.0	713.1	679.5	656.2	642.8
52.5°	867.1	850.3	803.4	733.2	676.2	632.8	599.2	579.2	565.8
55°	773.3	760.0	709.7	646.1	595.9	559.1	529.0	505.5	492.1
57.5°	686.3	672.9	626.0	565.8	522.2	488.8	462.0	441.9	425.2
60°	606.0	595.9	549.0	492.1	455.3	421.9	398.4	381.7	371.5
62.5°	535.6	515.5	475.4	425.2	391.7	364.9	341.4	331.4	338.1
65°	458.6	448.5	408.4	364.9	334.8	308.0	291.2	298.0	304.7
67.5°	395.0	381.7	348.2	308.0	281.2	261.1	251.1	264.4	267.9
70°	331.4	318.0	287.9	254.4	231.0	217.7	217.7	227.7	231.0
72.5°	271.2	261.1	234.3	207.5	190.8	180.8	187.4	194.2	197.5
75°	217.7	207.5	187.4	164.0	147.3	147.3	154.0	160.7	164.0
77.5°	167.3	160.7	140.7	123.9	117.2	117.2	123.9	127.2	130.6
80°	117.2	110.4	100.4	90.3	83.7	90.3	97.1	97.1	100.4
82.5°	77.0	73.7	67.0	60.2	60.2	63.7	67.0	70.3	70.3
85°	40.2	40.2	36.8	33.4	36.8	40.2	40.2	43.6	43.6
87.5°	13.3	13.3	13.3	13.3	16.8	16.8	16.8	16.8	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)