

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593020

Luminaire Tested: **HCC6S07D010SL-HM60525850-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593020
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010SL-HM60525850-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 980.2 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593020
CATALOG NUMBER: HCC6S07D010SL-HM60525850-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593020
 CATALOG NUMBER: HCC6S07D010SL-HM60525850-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92				92															
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84				84															
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77				77															
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70				70															
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64															
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59				59															
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54				54															
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50				50															
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46				46															
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43				43															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38385
5°	38642
10°	39089
15°	39892
20°	40113
25°	38863
30°	35259
35°	28670
40°	19029
45°	10590
50°	5944
55°	3288
60°	1809
65°	1388
70°	962
75°	699
80°	442
85°	440



TEST NUMBER: P593020
 CATALOG NUMBER: HCC6S07D010SL-HM60525850-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.0	6.8
10°-20°	198.2	20.2
20°-30°	292.1	29.8
30°-40°	261.3	26.7
40°-50°	113.3	11.6
50°-60°	33.3	3.4
60°-70°	10.6	1.1
70°-80°	3.7	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.3	56.9
0°-40°	818.6	83.5
0°-60°	965.2	98.5
0°-90°	980.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	980.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	700	
5°	702	67
15°	703	198
25°	642	292
35°	428	261
45°	137	113
55°	34	33
65°	11	11
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P593020
CATALOG NUMBER: HCC6S07D010SL-HM60525850-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	700.2
2.5°	698.3
5°	702.2
7.5°	703.6
10°	702.2
12.5°	702.2
15°	702.9
17.5°	698.9
20°	687.6
22.5°	668.4
25°	642.5
27.5°	606.0
30°	557.0
32.5°	498.6
35°	428.4
37.5°	348.2
40°	265.9
42.5°	194.3
45°	136.6
47.5°	97.4
50°	69.7
52.5°	49.7
55°	34.4
57.5°	23.2
60°	16.5
62.5°	13.3
65°	10.7
67.5°	7.9
70°	6.0
72.5°	4.6
75°	3.3
77.5°	2.6
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)