

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583367

Luminaire Tested: **HCC6W07D010BZ-HM60525927-61WWWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583367  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W07D010BZ-HM60525927-61WWWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 711.1 lumens  
Efficiency: N/A  
Efficacy: 88.9 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583367  
CATALOG NUMBER: HCC6W07D010BZ-HM60525927-61WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P583367

CATALOG NUMBER: HCC6W07D010BZ-HM60525927-61WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	19905	19905	19905
5°	20339	19904	19547
10°	20958	19717	19054
15°	21618	19450	18576
20°	21964	18727	17828
25°	21600	17614	16803
30°	20566	16332	15699
35°	18759	14743	14502
40°	16402	13239	13168
45°	14118	11652	11916
50°	12273	10157	10371
55°	10714	8908	9013
60°	9517	7730	7072
65°	8496	6499	5409
70°	7485	5321	4536
75°	6418	4194	4300
80°	5146	3599	4230
85°	3397	3145	3774



TEST NUMBER: P583367

CATALOG NUMBER: HCC6W07D010BZ-HM60525927-61WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.4	4.8
10°-20°	97.9	13.8
20°-30°	139.7	19.6
30°-40°	146.3	20.6
40°-50°	123.2	17.3
50°-60°	87.7	12.3
60°-70°	51.3	7.2
70°-80°	24.3	3.4
80°-90°	6.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.0	38.2
0°-40°	418.3	58.8
0°-60°	629.2	88.5
0°-90°	711.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	711.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	363	363	363	363	363	
5°	370	366	362	357	355	36
15°	381	367	343	329	327	108
25°	357	332	291	277	278	163
35°	280	257	220	213	217	174
45°	182	169	150	151	154	141
55°	112	103	93	93	94	101
65°	66	58	50	42	42	65
75°	30	25	20	19	20	32
85°	5	4	5	6	6	7
90°	0	0	0	0	0	



TEST NUMBER: P583367

CATALOG NUMBER: HCC6W07D010BZ-HM60525927-61WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	363.1	363.1	363.1	363.1	363.1	363.1	363.1	363.1	363.1
2.5°	363.6	363.6	363.1	362.6	361.7	360.1	359.2	358.1	358.1
5°	369.6	368.6	366.5	364.0	361.7	358.6	356.7	355.2	355.2
7.5°	374.5	372.5	368.6	364.0	359.6	355.6	352.1	350.2	349.6
10°	376.5	374.0	368.0	361.1	354.2	348.7	344.8	342.3	342.3
12.5°	378.4	375.5	367.5	357.7	348.7	341.3	337.3	335.4	334.8
15°	380.9	376.9	367.1	354.6	342.7	334.3	328.9	327.3	327.3
17.5°	380.9	375.9	363.6	348.2	333.3	323.9	318.9	317.5	317.9
20°	376.5	371.1	356.1	337.3	321.0	311.0	306.0	305.0	305.6
22.5°	368.0	361.7	344.8	324.4	306.6	296.2	291.6	291.6	291.2
25°	357.1	350.2	331.9	310.6	291.2	280.8	277.2	277.8	277.8
27.5°	342.7	335.8	317.5	294.7	275.3	264.9	262.4	263.4	263.9
30°	324.9	317.5	298.1	275.8	258.0	247.6	246.0	247.6	248.0
32.5°	303.1	297.6	278.7	255.9	239.1	230.1	229.7	231.1	233.2
35°	280.3	274.3	257.0	236.1	220.3	212.8	212.8	215.3	216.7
37.5°	255.5	249.5	233.6	216.3	202.9	195.9	196.9	199.4	199.9
40°	229.2	224.7	211.3	196.5	185.0	179.6	181.1	183.5	184.0
42.5°	204.4	200.4	189.4	176.1	167.7	163.7	165.6	168.7	169.6
45°	182.1	177.5	168.7	157.3	150.3	148.3	150.8	152.7	153.7
47.5°	161.7	157.7	150.3	139.9	134.9	133.9	136.4	137.4	138.3
50°	143.9	139.9	132.4	123.0	119.1	119.1	121.0	122.0	121.6
52.5°	126.4	123.0	116.0	108.1	105.7	105.7	107.2	107.6	108.7
55°	112.1	108.7	102.6	95.3	93.2	92.2	93.2	93.2	94.3
57.5°	98.7	95.7	90.3	83.3	80.9	79.9	79.3	78.9	79.9
60°	86.8	84.3	78.4	72.4	70.5	68.0	65.9	64.0	64.5
62.5°	75.9	73.4	68.0	62.0	60.0	56.5	54.0	51.6	52.6
65°	65.5	63.0	58.0	53.0	50.1	46.1	42.1	40.7	41.7
67.5°	56.1	54.0	49.1	44.2	41.7	37.2	33.2	33.2	33.8
70°	46.7	44.6	40.7	36.3	33.2	29.2	27.8	28.3	28.3
72.5°	38.2	36.7	32.7	28.8	25.8	23.3	23.3	23.8	24.4
75°	30.3	29.2	25.3	21.9	19.8	18.4	19.4	19.8	20.3
77.5°	23.3	21.9	18.8	16.3	14.8	15.4	16.3	16.9	17.3
80°	16.3	15.9	13.4	11.9	11.4	11.9	12.9	13.4	13.4
82.5°	10.4	10.0	8.4	7.9	7.9	8.4	9.4	9.4	9.4
85°	5.4	5.0	4.4	4.4	5.0	5.4	6.0	6.0	6.0
87.5°	2.0	1.5	2.0	2.0	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)