

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583358

Luminaire Tested: **HCC6W07D010MB-HM60525927-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010MB-HM60525927-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 739.3 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583358
CATALOG NUMBER: HCC6W07D010MB-HM60525927-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583358

CATALOG NUMBER: HCC6W07D010MB-HM60525927-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20075	20075	20075
5°	20185	20289	20289
10°	20741	20385	20301
15°	21408	20500	20500
20°	21655	20033	20494
25°	21219	19029	19931
30°	20073	17686	18718
35°	18170	16175	16972
40°	15801	14627	15200
45°	13498	13048	13498
50°	11846	11428	11897
55°	10341	9625	10007
60°	9144	8004	7883
65°	8107	6304	5409
70°	7149	4456	3270
75°	6100	2521	1589
80°	4546	789	474
85°	2516	314	314



TEST NUMBER: P583358
 CATALOG NUMBER: HCC6W07D010MB-HM60525927-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.1	4.8
10°-20°	102.8	13.9
20°-30°	150.1	20.3
30°-40°	157.4	21.3
40°-50°	132.6	17.9
50°-60°	92.9	12.6
60°-70°	49.8	6.7
70°-80°	16.7	2.3
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.0	39.0
0°-40°	445.4	60.2
0°-60°	671.0	90.8
0°-90°	739.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	739.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	366	366	366	366	366	
5°	367	368	369	369	369	35
15°	377	372	361	359	361	106
25°	351	336	315	320	330	161
35°	272	258	242	249	254	168
45°	174	171	168	173	174	136
55°	108	105	101	103	105	97
65°	62	57	49	40	42	62
75°	29	22	12	8	8	31
85°	4	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583358

CATALOG NUMBER: HCC6W07D010MB-HM60525927-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2	366.2
2.5°	363.7	363.7	364.7	365.7	366.8	366.8	367.2	367.7	367.2
5°	366.8	366.8	368.2	368.7	368.7	368.2	368.7	368.7	368.7
7.5°	371.2	370.2	370.7	369.7	368.7	368.2	367.7	367.7	367.7
10°	372.6	371.6	370.7	368.7	366.2	364.7	364.3	364.7	364.7
12.5°	374.7	373.7	371.2	367.2	364.3	361.8	361.2	362.2	362.2
15°	377.2	376.2	372.2	365.7	361.2	358.8	359.3	360.3	361.2
17.5°	377.2	375.1	368.7	360.3	354.9	352.4	354.3	356.8	358.3
20°	371.2	369.2	360.3	349.9	343.4	341.9	345.3	349.9	351.3
22.5°	363.2	359.3	348.9	336.4	329.5	329.5	334.5	339.9	341.9
25°	350.8	347.8	335.9	321.5	314.6	314.1	320.1	327.6	329.5
27.5°	337.0	333.0	320.1	305.2	297.8	298.2	304.7	312.1	314.1
30°	317.1	312.1	300.7	286.3	279.4	281.3	287.8	293.2	295.7
32.5°	294.8	290.3	279.9	266.5	260.5	262.5	268.0	272.9	274.9
35°	271.5	266.5	257.5	245.6	241.7	243.6	248.6	252.5	253.6
37.5°	245.2	241.7	235.2	225.8	222.9	225.2	229.2	231.7	232.7
40°	220.8	217.9	212.4	205.4	204.4	206.4	210.4	211.9	212.4
42.5°	197.0	194.5	191.0	186.0	186.0	188.1	191.6	192.5	193.1
45°	174.1	172.7	171.2	167.2	168.3	170.7	172.7	174.1	174.1
47.5°	154.3	154.8	152.8	149.9	150.8	153.3	154.8	156.4	156.4
50°	138.9	137.4	135.5	132.4	134.0	136.0	138.0	138.9	139.5
52.5°	121.1	120.6	119.1	115.6	116.6	117.6	119.6	121.1	121.6
55°	108.2	106.7	104.7	100.7	100.7	101.7	102.8	103.7	104.7
57.5°	95.7	94.3	91.3	86.8	86.3	86.3	85.9	86.8	88.4
60°	83.4	82.8	78.4	74.4	73.0	71.5	69.5	70.0	71.9
62.5°	72.4	71.5	67.5	62.5	59.6	57.1	54.6	54.0	56.1
65°	62.5	61.5	57.1	52.1	48.6	44.2	40.2	40.2	41.7
67.5°	53.6	51.6	47.6	42.1	37.7	32.3	28.3	29.2	29.8
70°	44.6	43.2	38.7	33.2	27.8	22.3	19.8	20.4	20.4
72.5°	36.7	34.8	30.3	24.8	19.4	14.4	13.4	12.9	12.9
75°	28.8	26.9	22.3	16.9	11.9	8.4	7.5	7.5	7.5
77.5°	20.8	19.4	15.4	10.4	6.5	4.0	3.5	2.9	2.9
80°	14.4	12.9	9.4	5.4	2.5	1.5	1.5	1.5	1.5
82.5°	8.4	6.9	4.4	2.5	1.0	0.5	0.5	0.5	0.5
85°	4.0	2.9	2.0	1.0	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)