

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583395

Luminaire Tested: **HCC6W07D010MW-HM60525935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010MW-HM60525935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 852.6 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583395
CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583395

CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77					77			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23852	23852	23852
5°	24097	23877	23723
10°	24437	23808	23552
15°	25011	23655	23434
20°	25249	22956	23020
25°	24697	21800	22211
30°	23390	20244	20934
35°	21174	18511	19200
40°	18449	16724	17340
45°	15653	14808	15335
50°	13859	12938	13279
55°	12205	11068	11010
60°	10942	9319	8574
65°	9755	7472	6149
70°	8591	5402	3831
75°	7244	3262	2182
80°	5588	1421	884
85°	3208	377	377



TEST NUMBER: P583395
 CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.3	4.8
10°-20°	118.7	13.9
20°-30°	171.6	20.1
30°-40°	180.5	21.2
40°-50°	151.8	17.8
50°-60°	106.5	12.5
60°-70°	58.6	6.9
70°-80°	20.8	2.4
80°-90°	2.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.6	38.9
0°-40°	512.1	60.1
0°-60°	770.4	90.4
0°-90°	852.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	435	435	435	435	435	
5°	438	437	434	432	431	42
15°	441	433	417	412	413	124
25°	408	388	360	361	367	187
35°	316	298	277	282	287	196
45°	202	196	191	196	198	158
55°	128	121	116	116	115	115
65°	75	67	58	47	47	75
75°	34	27	15	10	10	37
85°	5	3	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P583395

CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	435.1	435.1	435.1	435.1	435.1	435.1	435.1	435.1	435.1
2.5°	435.1	435.1	434.5	434.5	433.4	433.4	432.8	432.8	432.8
5°	437.9	437.9	436.8	435.1	433.9	432.2	432.2	431.7	431.1
7.5°	439.6	439.0	437.3	435.1	432.2	429.4	428.3	428.8	428.3
10°	439.0	437.9	435.6	431.1	427.7	423.6	423.1	422.5	423.1
12.5°	440.2	438.5	433.9	428.3	422.5	418.0	417.4	417.4	418.0
15°	440.7	439.0	433.4	424.8	416.8	412.3	411.7	412.3	412.9
17.5°	439.0	436.8	428.3	416.8	407.8	403.1	403.1	404.3	405.4
20°	432.8	429.4	417.4	403.7	393.5	390.0	391.2	393.5	394.6
22.5°	421.4	417.4	403.7	388.3	377.5	374.7	377.5	380.3	381.5
25°	408.3	403.7	387.7	371.7	360.4	357.0	361.0	365.5	367.2
27.5°	390.7	385.4	370.6	352.4	341.0	339.3	343.9	349.0	350.1
30°	369.5	363.8	347.3	330.2	319.8	319.3	324.5	329.0	330.7
32.5°	343.9	338.8	324.5	307.4	298.2	298.2	303.3	307.4	309.1
35°	316.4	310.8	298.2	283.9	276.6	277.1	282.2	285.1	286.9
37.5°	283.9	282.2	272.6	260.6	255.5	256.6	260.6	262.9	264.6
40°	257.8	253.2	246.9	237.3	233.7	235.0	238.9	241.2	242.3
42.5°	229.2	226.4	221.3	214.4	212.1	213.8	217.3	219.0	218.4
45°	201.9	201.3	196.1	192.2	191.0	193.3	195.6	197.3	197.8
47.5°	181.8	179.6	175.0	172.2	171.1	173.3	175.6	176.7	176.7
50°	162.5	160.2	155.7	152.8	151.7	154.0	155.7	156.8	155.7
52.5°	143.1	140.8	136.9	133.5	132.9	134.0	134.6	135.2	136.3
55°	127.7	125.4	120.9	116.9	115.8	116.4	115.8	115.8	115.2
57.5°	113.0	110.6	106.0	101.5	99.8	99.3	97.6	97.0	96.4
60°	99.8	97.0	92.3	87.2	85.0	82.7	79.9	78.2	78.2
62.5°	87.2	84.4	79.3	74.7	71.3	67.3	62.8	60.4	60.4
65°	75.2	73.0	67.3	62.2	57.6	52.5	47.4	46.2	47.4
67.5°	63.9	61.6	55.9	50.8	45.1	38.7	34.2	34.2	35.3
70°	53.6	51.3	46.2	39.9	33.7	27.4	23.9	23.9	23.9
72.5°	44.0	41.6	35.9	30.3	23.9	17.7	16.0	16.5	16.0
75°	34.2	32.5	27.4	21.1	15.4	10.9	10.3	9.7	10.3
77.5°	25.6	23.9	19.4	13.7	8.5	6.2	5.7	5.7	5.7
80°	17.7	16.0	12.6	7.9	4.5	2.8	2.8	2.8	2.8
82.5°	10.9	9.2	6.8	4.0	1.7	1.7	1.7	1.7	1.7
85°	5.1	4.0	2.8	1.1	0.6	0.6	0.6	0.6	0.6
87.5°	1.1	1.1	0.6	0.6	0.0	0.6	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)