

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583698

Luminaire Tested: **HCC8W10D010SL-HM80520827-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583698  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010SL-HM80520827-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1156.3 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583698  
CATALOG NUMBER: HCC8W10D010SL-HM80520827-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583698  
 CATALOG NUMBER: HCC8W10D010SL-HM80520827-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80												
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73										
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70											
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66											
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63											
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60												
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56											
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	55	54	53											
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	67	66	65	64	63	62	61	60	59	58	57	56	55	54	53	52	51	50											
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	65	64	63	62	61	60	59	58	57	56	55	54	53	52	51	50	49	48											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	217670
5°	139618
10°	63069
15°	38054
20°	28999
25°	23419
30°	17162
35°	6211
40°	2319
45°	1055
50°	336
55°	86
60°	43
65°	51
70°	0
75°	0
80°	124
85°	248



TEST NUMBER: P583698  
 CATALOG NUMBER: HCC8W10D010SL-HM80520827-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.0	29.8
10°-20°	349.4	30.2
20°-30°	312.8	27.1
30°-40°	126.0	10.9
40°-50°	20.7	1.8
50°-60°	1.9	0.2
60°-70°	0.6	0.1
70°-80°	0.5	0.0
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1006.2	87.0
0°-40°	1132.2	97.9
0°-60°	1154.7	99.9
0°-90°	1156.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1156.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7059	
5°	4510	344
15°	1192	349
25°	688	313
35°	165	126
45°	24	21
55°	2	2
65°	1	1
75°	0	0
85°	1	1
90°	0	



TEST NUMBER: P583698  
CATALOG NUMBER: HCC8W10D010SL-HM80520827-81NDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7058.9
0.5°	7037.0
1°	6945.9
1.5°	6799.6
2°	6577.7
2.5°	6315.3
3°	5986.7
3.5°	5626.2
4°	5269.6
4.5°	4870.1
5°	4510.5
5.5°	4118.8
6°	3801.2
6.5°	3470.3
7°	3210.2
7.5°	2935.3
8°	2714.2
8.5°	2492.3
9°	2325.7
9.5°	2142.0
10°	2014.2
12.5°	1485.6
15°	1192.0
17.5°	1018.5
20°	883.7
22.5°	776.3
25°	688.3
27.5°	600.3
30°	482.0
32.5°	309.9
35°	165.0
37.5°	91.1
40°	57.6
42.5°	38.1
45°	24.2
47.5°	14.8
50°	7.0
52.5°	2.3
55°	1.6
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P583698  
CATALOG NUMBER: HCC8W10D010SL-HM80520827-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.7
70°		0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)