

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583702

Luminaire Tested: **HCC8W10D010SL-HM80520827-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010SL-HM80520827-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1108.9 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583702
CATALOG NUMBER: HCC8W10D010SL-HM80520827-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P583702

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17993	17993	17993
5°	18232	17916	17749
10°	18415	17735	17463
15°	18602	17360	17009
20°	18508	16719	16332
25°	18077	15716	15505
30°	17170	14592	14535
35°	15630	13311	13431
40°	13702	11919	12358
45°	11822	10597	11347
50°	10353	9307	10276
55°	9172	8000	9048
60°	8264	6722	7493
65°	7442	5399	5742
70°	6537	3931	3165
75°	5576	2049	834
80°	4297	550	124
85°	2760	0	0



TEST NUMBER: P583702
 CATALOG NUMBER: HCC8W10D010SL-HM80520827-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.1	5.0
10°-20°	154.8	14.0
20°-30°	219.7	19.8
30°-40°	231.2	20.9
40°-50°	196.7	17.7
50°-60°	142.1	12.8
60°-70°	80.9	7.3
70°-80°	25.5	2.3
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.5	38.7
0°-40°	660.7	59.6
0°-60°	999.5	90.1
0°-90°	1108.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1108.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	584	584	584	584	584	
5°	589	586	579	575	573	56
15°	583	568	544	534	533	164
25°	531	505	462	454	456	243
35°	415	391	354	351	357	258
45°	271	261	243	249	260	211
55°	171	158	149	157	168	154
65°	102	88	74	73	79	101
75°	47	36	17	8	7	50
85°	8	5	0	0	0	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583702

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5
2.5°	586.6	587.4	585.9	585.9	587.4	585.9	586.6	586.6	585.9	585.9	585.0
5°	589.0	588.1	588.1	588.1	589.0	587.4	586.6	587.4	585.9	585.9	585.9
7.5°	589.7	589.7	589.0	588.1	588.1	588.1	587.4	586.6	585.9	584.3	583.5
10°	588.1	588.1	589.0	587.4	587.4	585.9	585.9	584.3	584.3	582.7	580.3
12.5°	586.6	585.9	585.9	584.3	584.3	582.7	582.7	580.3	579.6	577.2	574.9
15°	582.7	581.9	580.3	579.6	578.8	578.0	576.5	575.6	573.4	570.2	567.9
17.5°	574.9	574.2	573.4	571.8	570.2	569.5	568.7	566.4	563.3	560.9	557.0
20°	564.0	563.3	563.3	560.9	560.1	557.7	557.0	553.9	551.6	546.9	543.8
22.5°	549.2	550.0	548.5	546.9	545.3	542.9	541.4	538.3	534.4	529.7	525.9
25°	531.3	532.1	530.6	529.0	526.6	525.0	523.5	518.8	514.9	509.5	504.8
27.5°	508.7	508.7	508.7	507.1	503.3	502.4	500.9	496.2	490.8	486.1	481.4
30°	482.2	481.4	481.4	479.1	477.6	474.4	472.1	468.2	464.3	458.8	453.4
32.5°	450.3	451.1	448.7	447.1	444.9	444.9	441.7	438.6	433.9	428.5	423.0
35°	415.2	416.0	414.4	413.6	409.8	409.0	408.2	404.4	401.2	397.3	391.0
37.5°	379.4	378.6	377.8	377.8	375.5	373.9	372.4	370.0	365.4	362.3	359.2
40°	340.4	340.4	340.4	339.7	338.8	337.3	336.6	335.0	331.9	328.7	326.5
42.5°	305.4	305.4	304.6	303.9	302.3	303.0	301.5	299.9	296.8	294.5	292.9
45°	271.1	271.1	271.1	271.9	270.3	267.9	267.9	266.5	264.9	263.4	261.0
47.5°	240.8	243.0	241.5	240.8	241.5	238.4	238.4	236.8	235.2	233.7	230.5
50°	215.8	215.8	215.8	214.2	213.5	213.5	211.1	209.5	208.8	207.2	204.1
52.5°	193.2	191.6	191.6	190.9	190.0	188.5	188.5	186.9	183.9	182.3	179.9
55°	170.6	170.6	169.8	169.0	168.3	167.4	166.7	164.3	162.9	160.5	158.2
57.5°	150.4	151.9	151.1	149.5	148.0	148.0	146.4	144.8	142.6	140.3	137.9
60°	134.0	133.2	133.2	132.5	130.9	130.1	129.3	126.9	124.6	122.4	120.0
62.5°	116.8	116.8	116.8	115.3	113.7	113.0	112.1	110.6	107.5	105.2	103.6
65°	102.0	101.3	100.5	99.8	98.9	97.4	96.6	95.1	92.7	90.4	88.0
67.5°	87.3	86.4	86.4	85.7	83.3	82.6	82.6	80.3	77.9	75.6	73.2
70°	72.5	72.5	72.5	70.9	70.1	69.4	68.5	67.0	64.7	62.3	60.0
72.5°	60.0	59.3	59.3	58.4	56.1	55.3	54.6	53.0	50.6	49.0	47.5
75°	46.8	46.8	45.9	45.2	44.4	43.6	42.8	41.2	38.9	36.7	35.8
77.5°	35.8	35.1	35.1	34.3	32.7	32.0	32.0	30.4	28.0	26.4	24.9
80°	24.2	24.9	24.2	23.3	22.6	21.8	21.0	20.3	18.8	17.2	15.6
82.5°	14.8	15.6	14.8	14.8	14.1	13.2	13.2	11.7	10.9	10.1	9.4
85°	7.8	7.8	7.8	7.8	7.0	7.0	7.0	6.3	5.4	4.7	4.7
87.5°	2.3	3.1	2.3	2.3	2.3	2.3	2.3	2.3	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583702

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5
2.5°	585.9	585.0	584.3	584.3	584.3	584.3	584.3	583.5	582.7	582.7	582.7
5°	584.3	584.3	584.3	583.5	582.7	582.7	581.2	580.3	579.6	578.8	578.0
7.5°	582.7	581.2	580.3	579.6	578.8	578.8	577.2	575.6	575.6	574.2	572.6
10°	578.0	577.2	575.6	574.2	573.4	572.6	571.1	568.7	567.9	566.4	564.8
12.5°	572.6	571.1	569.5	566.4	565.5	564.8	561.7	559.3	557.7	557.0	553.2
15°	565.5	562.4	560.1	556.2	555.4	553.9	551.6	549.2	546.1	543.8	542.2
17.5°	553.2	550.0	546.1	542.2	540.7	540.7	536.7	533.7	529.7	528.2	525.0
20°	538.3	534.4	531.3	526.6	524.3	521.9	519.6	514.9	511.8	509.5	505.6
22.5°	521.2	515.7	511.8	507.1	503.3	500.9	497.0	493.1	489.2	486.9	483.8
25°	499.3	494.6	488.5	483.8	481.4	478.3	473.6	469.7	465.9	461.9	460.4
27.5°	475.2	469.0	463.5	458.1	455.7	453.4	448.0	443.3	440.2	436.2	434.6
30°	448.7	442.5	436.2	431.5	429.2	425.4	422.3	416.7	412.9	409.8	405.9
32.5°	418.3	413.6	408.2	401.2	399.7	396.5	391.9	389.6	384.9	382.5	379.4
35°	385.6	382.5	377.1	371.5	369.3	367.7	363.8	359.2	356.0	353.6	352.1
37.5°	354.5	350.5	345.1	341.2	339.7	337.3	332.6	330.3	327.2	325.6	322.5
40°	320.9	317.1	313.1	310.8	308.4	307.0	303.9	301.5	298.3	296.1	295.2
42.5°	288.2	286.0	282.8	279.7	278.9	276.6	275.0	272.6	270.3	269.5	267.2
45°	258.7	256.3	253.1	250.0	249.3	247.7	246.9	244.6	243.0	243.0	243.0
47.5°	229.0	226.7	223.6	222.0	222.9	219.7	219.7	218.9	217.3	217.3	218.2
50°	202.5	199.4	198.7	197.1	195.6	194.0	194.7	192.4	192.4	194.0	193.2
52.5°	177.7	174.5	173.7	172.1	171.4	171.4	170.6	170.6	169.8	170.6	170.6
55°	155.1	152.7	151.1	149.5	148.8	148.8	148.8	148.0	147.2	148.8	149.5
57.5°	134.7	134.0	132.5	130.1	129.3	128.5	127.8	127.8	127.8	127.8	128.5
60°	116.8	115.3	113.7	111.4	111.4	110.6	109.9	109.0	109.0	109.0	109.0
62.5°	101.3	98.9	96.6	95.1	94.2	93.5	92.7	91.1	91.1	91.1	91.1
65°	85.7	83.3	81.9	80.3	78.7	78.7	77.2	76.3	74.8	74.0	72.5
67.5°	70.9	69.4	67.8	65.4	64.7	63.8	62.3	61.5	59.3	58.4	57.7
70°	57.7	55.3	53.7	52.2	51.4	49.9	48.3	46.8	45.2	43.6	42.1
72.5°	45.2	42.8	41.2	39.8	38.2	38.2	35.8	34.3	32.0	30.4	28.0
75°	33.5	31.1	29.6	27.3	26.4	25.7	23.3	21.8	19.5	17.2	15.6
77.5°	22.6	21.0	19.5	17.2	15.6	15.6	13.2	11.7	10.1	7.8	7.0
80°	14.1	12.5	10.9	9.4	9.4	7.8	7.0	5.4	3.8	3.1	2.3
82.5°	7.8	7.0	6.3	4.7	4.7	3.8	3.1	2.3	1.6	0.7	0.7
85°	3.8	3.1	2.3	2.3	1.6	1.6	1.6	0.7	0.7	0.0	0.0
87.5°	1.6	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583702

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5
2.5°	581.9	581.9	581.2	581.2	581.2	580.3	581.2	580.3	580.3	580.3	581.2
5°	578.8	577.2	577.2	576.5	576.5	575.6	576.5	575.6	574.9	574.2	574.9
7.5°	572.6	571.1	570.2	569.5	569.5	569.5	568.7	567.9	568.7	566.4	567.9
10°	564.0	563.3	561.7	560.9	560.1	560.9	560.1	558.6	558.6	558.6	557.7
12.5°	553.2	551.6	550.8	550.0	548.5	548.5	549.2	547.6	547.6	546.1	546.1
15°	539.8	538.3	536.7	536.7	535.1	535.1	534.4	534.4	533.7	532.8	532.8
17.5°	523.5	521.2	519.6	520.3	519.6	518.8	518.8	517.2	516.5	517.2	517.2
20°	504.0	502.4	500.9	501.7	500.2	499.3	500.2	497.7	498.6	498.6	498.6
22.5°	482.2	481.4	479.1	479.1	477.6	476.7	477.6	477.6	478.3	477.6	477.6
25°	458.1	456.5	455.0	455.0	454.1	453.4	454.1	455.0	454.1	455.0	455.0
27.5°	432.4	430.1	430.1	428.5	428.5	429.2	428.5	429.2	430.1	430.1	431.5
30°	404.4	403.5	402.8	401.9	401.9	402.8	402.8	402.8	403.5	405.1	405.1
32.5°	377.8	376.2	374.7	374.7	376.2	375.5	376.2	376.2	377.8	377.8	379.4
35°	349.1	349.1	347.5	348.2	348.2	348.2	348.2	349.8	351.3	352.1	353.6
37.5°	322.5	320.2	320.9	320.9	321.8	320.9	323.3	323.3	324.9	324.9	326.5
40°	293.6	293.6	294.5	293.6	294.5	294.5	296.1	297.6	298.3	299.9	300.7
42.5°	266.5	267.9	266.5	267.2	267.9	268.8	269.5	270.3	273.5	275.0	277.3
45°	241.5	242.3	243.0	243.9	243.0	244.6	245.4	246.9	249.3	250.0	250.9
47.5°	217.3	218.2	218.9	219.7	219.7	221.3	222.0	223.6	225.1	226.0	226.7
50°	194.0	195.6	196.3	196.3	197.1	198.7	200.3	200.3	201.8	204.1	204.9
52.5°	173.0	173.0	174.5	175.3	176.1	176.1	178.4	179.2	179.9	181.5	183.1
55°	149.5	151.9	152.7	152.7	154.2	155.8	156.6	157.3	157.3	160.5	160.5
57.5°	129.3	130.1	131.6	131.6	131.6	134.0	134.0	135.6	136.3	137.1	138.7
60°	109.0	110.6	110.6	111.4	110.6	112.1	113.0	114.6	115.3	116.1	116.8
62.5°	90.4	90.4	91.1	91.1	91.1	91.1	92.7	92.7	94.2	95.1	95.8
65°	72.5	72.5	72.5	72.5	72.5	72.5	72.5	72.5	73.2	73.2	74.8
67.5°	56.1	55.3	53.7	54.6	53.7	53.7	53.0	53.0	53.7	53.7	55.3
70°	40.5	39.8	38.2	38.2	37.4	36.7	35.8	35.1	34.3	34.3	34.3
72.5°	26.4	24.9	22.6	21.8	21.8	20.3	18.8	17.9	17.9	17.9	17.9
75°	13.2	11.7	10.1	9.4	9.4	7.8	8.5	7.8	7.8	7.8	7.8
77.5°	5.4	3.8	3.1	3.1	3.1	2.3	2.3	2.3	2.3	2.3	2.3
80°	1.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583702

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	583.5	583.5	583.5	583.5	583.5	583.5	583.5	583.5
2.5°	580.3	580.3	578.8	579.6	579.6	579.6	579.6	579.6
5°	573.4	574.2	573.4	574.2	574.2	573.4	573.4	573.4
7.5°	566.4	567.1	566.4	567.1	567.1	567.1	566.4	566.4
10°	557.7	557.7	557.7	557.7	557.7	557.0	557.7	557.7
12.5°	546.1	546.1	546.1	546.9	546.9	546.1	546.1	545.3
15°	533.7	532.1	532.8	533.7	532.8	532.8	532.8	532.8
17.5°	516.5	517.2	516.5	516.5	516.5	516.5	517.2	516.5
20°	498.6	498.6	499.3	498.6	498.6	498.6	498.6	497.7
22.5°	478.3	477.6	477.6	478.3	478.3	477.6	478.3	478.3
25°	455.7	456.5	455.7	455.7	456.5	456.5	456.5	455.7
27.5°	431.5	432.4	433.1	432.4	432.4	432.4	433.1	433.9
30°	406.6	408.2	406.6	406.6	408.2	407.5	408.2	408.2
32.5°	380.2	382.5	380.9	382.5	382.5	383.3	382.5	383.3
35°	353.6	356.0	356.0	356.0	356.8	357.6	357.6	356.8
37.5°	328.7	329.5	329.5	331.0	331.9	332.6	332.6	331.9
40°	303.0	304.6	305.4	305.4	305.4	307.0	308.4	307.0
42.5°	278.1	278.9	279.7	279.7	281.3	282.0	282.8	282.8
45°	254.0	255.5	256.3	257.1	257.8	259.4	258.7	260.2
47.5°	229.0	231.4	232.1	232.9	234.5	235.2	236.1	236.8
50°	206.4	207.9	207.9	209.5	211.9	211.9	213.5	214.2
52.5°	183.9	184.6	185.3	186.2	187.8	189.3	189.3	190.9
55°	162.0	162.9	162.9	163.6	164.3	167.4	168.3	168.3
57.5°	139.4	139.4	141.0	141.8	142.6	144.1	144.1	144.1
60°	117.7	118.4	118.4	119.2	120.0	121.5	122.4	121.5
62.5°	95.8	96.6	96.6	97.4	98.9	99.8	98.9	98.9
65°	75.6	76.3	76.3	77.2	78.7	78.7	77.9	78.7
67.5°	55.3	55.3	55.3	55.3	55.3	55.3	55.3	55.3
70°	35.1	34.3	33.5	34.3	34.3	34.3	33.5	35.1
72.5°	17.2	17.9	17.9	17.9	17.9	17.9	17.9	17.2
75°	7.8	7.8	7.0	7.0	7.0	7.8	7.8	7.0
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
80°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)