

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583711

Luminaire Tested: **HCC8W10D010SL-HM80520827-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010SL-HM80520827-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1102.7 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583711
CATALOG NUMBER: HCC8W10D010SL-HM80520827-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P583711

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	16904	16904	16904
5°	17523	16851	16269
10°	18020	16702	15609
15°	18423	16409	14918
20°	18452	15771	14311
25°	18097	14889	13807
30°	17166	13812	13199
35°	15596	12581	12607
40°	13634	11287	11883
45°	11822	10052	11072
50°	10353	8933	10084
55°	9209	7914	9123
60°	8307	7111	8024
65°	7501	6253	6990
70°	6744	5265	5193
75°	5945	4182	3896
80°	4972	3463	3729
85°	3856	3007	3326



TEST NUMBER: P583711
 CATALOG NUMBER: HCC8W10D010SL-HM80520827-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	4.7
10°-20°	145.7	13.2
20°-30°	208.2	18.9
30°-40°	221.2	20.1
40°-50°	190.5	17.3
50°-60°	142.4	12.9
60°-70°	90.8	8.2
70°-80°	41.3	3.7
80°-90°	10.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.6	36.8
0°-40°	626.8	56.8
0°-60°	959.7	87.0
0°-90°	1102.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1102.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	548	548	548	548	548	
5°	566	558	544	530	526	54
15°	577	558	514	479	467	163
25°	532	498	438	411	406	243
35°	414	386	334	326	335	258
45°	271	256	230	237	254	211
55°	171	157	147	160	170	154
65°	103	91	86	90	96	103
75°	50	43	35	32	33	53
85°	11	9	8	9	9	13
90°	0	0	0	0	0	



TEST NUMBER: P583711

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2
2.5°	558.4	556.9	557.6	556.9	557.6	557.6	556.0	556.0	556.0	556.0	553.8
5°	566.1	565.4	565.4	564.6	563.9	564.6	563.9	563.0	561.6	560.7	558.4
7.5°	570.8	570.8	570.8	570.8	570.1	569.3	568.5	567.0	565.4	563.9	562.3
10°	575.5	576.4	575.5	574.8	574.0	572.4	571.7	570.1	567.7	565.4	563.9
12.5°	577.9	577.9	577.1	577.1	575.5	574.8	572.4	570.1	567.7	565.4	561.6
15°	577.1	577.1	576.4	575.5	573.2	572.4	570.8	568.5	564.6	561.6	557.6
17.5°	572.4	571.7	570.1	570.1	567.0	566.1	564.6	561.6	557.6	552.9	548.2
20°	562.3	562.3	561.6	560.7	557.6	555.3	553.8	549.8	546.7	541.3	536.6
22.5°	548.2	549.8	548.2	546.7	542.8	542.1	539.7	535.0	530.3	524.2	518.7
25°	531.9	531.2	530.3	528.8	525.6	524.2	521.1	516.4	511.7	504.7	498.5
27.5°	510.8	507.7	507.7	504.7	502.3	500.0	498.5	493.8	487.5	482.1	474.3
30°	482.1	482.8	479.0	478.2	474.3	472.7	469.6	464.9	459.5	453.3	447.0
32.5°	450.9	448.6	448.6	445.5	442.3	440.1	439.2	433.8	429.1	422.9	416.6
35°	414.3	414.3	412.0	411.2	408.1	406.5	404.2	401.1	395.6	390.2	385.5
37.5°	378.5	376.9	376.1	374.7	372.3	370.0	370.0	364.4	363.7	357.5	351.2
40°	338.7	340.3	338.7	336.4	335.7	334.2	333.3	330.2	327.9	322.4	318.5
42.5°	305.3	303.7	303.7	302.9	299.9	299.9	298.3	296.8	292.8	291.2	286.6
45°	271.1	272.6	270.2	271.1	267.9	267.9	267.9	264.8	261.7	259.4	256.3
47.5°	241.5	242.2	242.2	239.9	239.1	239.1	237.5	236.0	233.7	230.5	228.1
50°	215.8	216.5	214.9	214.2	212.6	211.8	211.8	208.7	207.1	204.1	202.5
52.5°	192.3	192.3	191.6	191.6	189.2	189.2	187.6	185.3	183.8	182.2	178.4
55°	171.3	171.3	170.6	169.7	169.7	167.4	166.7	164.3	162.8	159.6	157.3
57.5°	151.1	151.8	151.1	150.2	149.5	148.8	147.2	144.8	143.3	141.0	139.4
60°	134.7	134.7	133.9	133.2	131.6	130.9	130.1	128.5	126.2	124.6	122.2
62.5°	119.1	118.4	117.6	116.8	115.3	115.3	113.7	112.1	109.9	108.3	106.7
65°	102.8	102.8	102.0	102.0	101.2	99.6	98.9	98.1	95.0	94.2	91.1
67.5°	88.0	88.8	87.3	87.3	85.7	85.7	84.9	82.6	81.7	80.2	78.6
70°	74.8	74.8	74.8	74.0	72.5	71.6	70.9	69.4	68.5	67.0	65.4
72.5°	61.5	61.5	60.7	60.7	60.0	59.1	58.4	56.9	56.9	55.3	53.7
75°	49.9	49.9	49.0	48.3	47.5	47.5	46.8	45.9	44.4	43.6	42.8
77.5°	38.1	38.1	38.1	37.4	36.7	36.7	36.7	35.1	33.5	33.5	32.7
80°	28.0	28.0	27.3	27.3	26.4	26.4	26.4	25.7	24.9	24.2	23.3
82.5°	18.8	18.8	18.8	18.8	17.9	17.9	17.9	17.2	16.3	16.3	16.3
85°	10.9	10.9	10.9	10.9	10.1	10.1	10.1	10.1	10.1	9.4	9.4
87.5°	4.7	3.8	4.7	3.8	4.7	3.8	4.7	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583711

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2
2.5°	554.5	553.8	552.9	552.2	552.2	551.4	549.8	549.1	548.2	547.5	547.5
5°	557.6	556.9	555.3	553.8	552.9	551.4	549.8	548.2	546.7	544.4	543.7
7.5°	560.0	557.6	556.0	552.9	552.2	550.6	548.2	545.9	542.8	539.7	537.4
10°	560.0	556.9	554.5	550.6	549.1	547.5	544.4	540.5	536.6	533.4	529.6
12.5°	558.4	554.5	550.6	546.7	544.4	542.1	537.4	533.4	528.8	524.2	521.1
15°	552.9	548.2	543.7	539.0	536.6	533.4	528.8	523.4	518.7	514.0	508.6
17.5°	542.8	538.1	532.7	527.2	524.2	521.8	514.8	510.8	503.9	499.2	494.5
20°	529.6	524.2	517.1	511.7	507.7	505.4	500.0	492.9	487.5	480.6	475.9
22.5°	512.4	505.4	498.5	492.9	489.1	486.0	479.0	471.9	467.3	461.1	455.6
25°	492.2	485.2	478.2	470.3	466.5	463.4	457.1	450.9	444.7	437.6	433.0
27.5°	468.1	460.2	454.0	447.0	443.2	438.5	431.4	425.3	419.0	414.3	408.1
30°	441.6	433.0	426.8	419.7	415.9	412.0	405.0	398.7	393.3	387.9	384.8
32.5°	409.6	403.4	397.1	390.2	387.0	384.8	377.7	371.5	365.3	360.6	358.2
35°	379.2	372.3	366.9	360.6	356.6	354.3	348.1	342.7	339.6	334.2	331.0
37.5°	347.4	341.8	335.7	329.5	327.1	324.8	320.1	314.7	310.0	306.0	304.5
40°	313.8	309.2	303.7	299.9	297.5	295.2	291.2	287.4	284.3	280.4	278.9
42.5°	281.9	278.9	274.2	269.5	267.1	266.4	261.7	258.6	257.0	255.4	253.9
45°	253.1	248.5	245.3	242.2	239.9	238.4	236.0	233.7	232.1	230.5	229.0
47.5°	225.1	221.2	218.0	215.8	213.4	212.6	211.1	208.7	207.1	207.1	207.1
50°	199.4	196.3	193.2	191.6	190.8	189.2	187.6	186.9	186.2	186.2	186.2
52.5°	176.8	173.7	171.3	169.7	169.7	168.3	166.7	165.9	165.9	165.9	165.9
55°	155.8	153.4	151.8	150.2	148.8	148.0	148.0	148.0	147.2	147.2	148.0
57.5°	137.0	135.5	133.2	131.6	130.9	130.9	130.1	129.3	130.1	130.9	131.6
60°	120.0	118.4	117.6	115.3	115.3	115.3	114.4	114.4	114.4	115.3	116.0
62.5°	104.3	103.6	102.0	101.2	100.5	100.5	99.6	99.6	99.6	99.6	100.5
65°	90.4	88.8	87.3	87.3	87.3	86.4	86.4	84.9	85.7	85.7	84.9
67.5°	77.0	75.5	74.8	74.0	73.2	73.2	72.5	71.6	70.9	70.9	70.9
70°	64.7	63.1	63.1	61.5	61.5	60.7	60.0	60.0	59.1	58.4	57.6
72.5°	52.2	51.4	50.6	49.9	49.9	49.9	49.0	48.3	47.5	46.8	45.2
75°	41.2	41.2	39.7	38.9	38.9	38.1	37.4	36.7	35.8	35.1	34.3
77.5°	32.0	31.1	29.6	28.8	28.8	28.8	28.0	27.3	26.4	25.7	24.9
80°	23.3	22.6	21.8	21.0	21.0	21.0	20.2	20.2	19.5	19.5	19.5
82.5°	15.6	15.6	14.8	14.8	14.8	14.8	14.1	14.1	14.1	14.1	14.1
85°	9.4	9.4	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583711

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2
2.5°	545.9	545.9	544.4	543.7	542.8	543.7	542.1	541.3	540.5	540.5	539.7
5°	541.3	540.5	537.4	536.6	535.9	535.0	533.4	531.9	530.3	529.6	528.8
7.5°	535.0	532.7	529.6	528.8	528.0	525.6	523.4	521.8	519.5	518.7	517.1
10°	526.5	523.4	521.1	518.7	517.1	514.8	512.4	510.1	507.0	506.3	503.9
12.5°	516.4	512.4	507.7	507.0	504.7	501.6	498.5	496.1	493.8	492.2	489.8
15°	503.9	500.0	495.3	492.9	490.7	488.3	484.4	481.3	479.0	476.6	474.3
17.5°	489.1	484.4	480.6	478.2	476.6	472.7	469.6	465.8	463.4	461.1	458.7
20°	471.2	467.3	461.8	459.5	458.7	455.6	451.7	450.1	447.0	444.7	443.2
22.5°	450.9	447.0	442.3	440.8	437.6	436.1	432.2	430.7	429.1	426.8	426.0
25°	428.4	424.4	420.6	419.7	417.5	415.9	413.5	411.2	411.2	408.9	408.9
27.5°	405.0	401.1	398.0	396.4	395.6	394.0	391.7	391.0	390.2	389.4	389.4
30°	380.1	375.4	373.8	373.1	372.3	370.7	370.0	368.4	369.1	370.0	369.1
32.5°	353.6	352.1	348.9	347.4	348.1	347.4	345.8	347.4	346.5	348.1	348.9
35°	327.9	326.3	324.8	324.8	323.2	323.2	323.2	323.9	325.5	326.3	327.9
37.5°	302.9	300.6	299.9	299.1	299.9	299.9	299.9	301.3	302.9	304.5	306.9
40°	276.5	274.9	274.9	274.9	274.9	277.3	276.5	278.0	279.6	281.9	284.3
42.5°	251.6	251.6	252.3	252.3	252.3	252.3	253.9	256.3	258.6	261.0	263.2
45°	228.1	228.1	228.1	229.7	229.7	230.5	233.7	235.2	236.8	239.1	241.5
47.5°	206.4	206.4	207.1	207.9	208.7	210.2	211.8	214.2	216.5	218.0	220.4
50°	186.2	186.9	188.5	190.0	190.0	190.8	193.2	194.7	196.3	198.6	199.4
52.5°	166.7	168.3	169.7	170.6	171.3	172.8	173.7	176.0	176.8	179.1	179.9
55°	148.8	149.5	151.8	152.7	152.7	154.2	155.8	157.3	159.6	159.6	161.2
57.5°	132.3	133.2	134.7	135.5	134.7	137.0	137.9	139.4	140.2	141.7	142.6
60°	116.0	117.6	118.4	118.4	119.1	120.0	121.5	121.5	123.1	124.6	124.6
62.5°	100.5	101.2	102.0	102.8	103.6	102.8	105.2	105.2	106.7	107.5	109.0
65°	85.7	86.4	86.4	87.3	87.3	88.0	88.0	88.8	89.5	91.1	92.0
67.5°	70.9	70.9	70.9	71.6	70.9	71.6	71.6	72.5	72.5	74.0	74.8
70°	57.6	56.9	56.1	56.1	56.1	56.1	55.3	56.1	56.1	56.9	56.9
72.5°	44.4	43.6	42.8	42.1	42.1	41.2	40.5	41.2	41.2	42.1	42.1
75°	33.5	32.0	32.0	32.0	31.1	31.1	31.1	32.0	32.0	32.0	32.7
77.5°	24.9	24.9	24.2	24.2	24.2	24.9	24.9	25.7	25.7	25.7	25.7
80°	18.8	19.5	19.5	19.5	19.5	20.2	20.2	20.2	20.2	21.0	21.0
82.5°	14.1	14.1	14.1	14.1	14.8	14.8	14.8	14.8	14.8	14.8	14.8
85°	8.5	9.4	9.4	8.5	9.4	9.4	9.4	9.4	9.4	9.4	9.4
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583711

CATALOG NUMBER: HCC8W10D010SL-HM80520827-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	548.2	548.2	548.2	548.2	548.2	548.2	548.2	548.2
2.5°	539.0	539.0	539.0	539.0	538.1	538.1	538.1	537.4
5°	527.2	527.2	527.2	525.6	526.5	526.5	524.9	525.6
7.5°	515.5	514.8	514.0	514.0	513.3	512.4	511.7	512.4
10°	502.3	500.0	500.0	499.2	499.2	497.6	497.6	498.5
12.5°	487.5	486.0	486.0	485.2	484.4	483.7	482.8	482.8
15°	472.7	471.2	470.3	469.6	468.9	467.3	468.1	467.3
17.5°	458.0	455.6	455.6	454.8	454.0	452.4	452.4	451.7
20°	440.8	440.1	438.5	439.2	438.5	436.9	436.1	436.1
22.5°	423.7	423.7	422.9	422.9	422.1	421.3	420.6	420.6
25°	407.4	406.5	407.4	407.4	405.0	405.0	405.0	405.8
27.5°	388.6	389.4	388.6	388.6	388.6	388.6	389.4	388.6
30°	370.0	370.0	370.0	370.7	372.3	371.5	371.5	370.7
32.5°	349.7	350.5	350.5	351.2	352.1	353.6	353.6	354.3
35°	329.5	331.0	331.8	331.0	333.3	333.3	334.9	334.9
37.5°	308.4	309.2	310.7	311.6	313.1	313.8	314.7	314.7
40°	285.8	289.0	289.7	290.5	292.8	292.8	293.6	295.2
42.5°	264.8	267.9	268.6	269.5	271.1	273.3	272.6	274.2
45°	244.5	246.9	247.6	248.5	250.7	251.6	251.6	253.9
47.5°	222.7	224.3	225.1	226.6	228.1	229.7	231.3	230.5
50°	201.0	203.3	204.8	205.7	207.9	208.7	209.5	210.2
52.5°	181.5	183.1	183.8	184.6	186.9	187.6	188.5	190.0
55°	162.8	163.6	165.2	164.3	166.7	167.4	168.3	169.7
57.5°	144.1	144.8	145.7	145.7	147.2	148.8	149.5	150.2
60°	126.2	127.8	128.5	128.5	128.5	130.1	130.1	130.1
62.5°	109.9	109.9	110.6	110.6	112.1	112.1	112.1	112.1
65°	92.7	93.5	94.2	94.2	95.8	95.0	96.5	95.8
67.5°	74.8	74.8	76.3	76.3	75.5	76.3	76.3	76.3
70°	56.9	56.9	57.6	57.6	57.6	57.6	57.6	57.6
72.5°	42.1	42.1	42.1	42.8	42.1	42.1	42.8	42.1
75°	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7
77.5°	25.7	25.7	26.4	26.4	26.4	26.4	26.4	26.4
80°	21.0	21.0	21.0	21.0	21.8	21.0	21.0	21.0
82.5°	15.6	14.8	15.6	14.8	15.6	15.6	15.6	15.6
85°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)