

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583771

Luminaire Tested: **HCC8S10D010MW-HM80520927-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010MW-HM80520927-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 875.1 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583771
CATALOG NUMBER: HCC8S10D010MW-HM80520927-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583771

CATALOG NUMBER: HCC8S10D010MW-HM80520927-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	14397	14397	14397
5°	14663	14332	13997
10°	14892	14081	13489
15°	15043	13731	12904
20°	14983	13202	12306
25°	14593	12439	11623
30°	13897	11529	10946
35°	12547	10525	10168
40°	11026	9444	9419
45°	9516	8303	8661
50°	8285	7282	7767
55°	7349	6328	6763
60°	6556	5347	5618
65°	5910	4341	4429
70°	5247	3255	2624
75°	4527	1894	1132
80°	3481	675	337
85°	2264	212	212



TEST NUMBER: P583771
 CATALOG NUMBER: HCC8S10D010MW-HM80520927-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.8	5.0
10°-20°	122.0	13.9
20°-30°	172.5	19.7
30°-40°	181.8	20.8
40°-50°	154.5	17.7
50°-60°	111.3	12.7
60°-70°	64.2	7.3
70°-80°	21.9	2.5
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.3	38.7
0°-40°	520.2	59.4
0°-60°	785.9	89.8
0°-90°	875.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	467	467	467	467	467	
5°	474	471	463	455	452	45
15°	471	457	430	411	404	133
25°	429	407	366	347	342	197
35°	333	314	280	270	270	208
45°	218	208	190	192	199	170
55°	137	126	118	122	126	123
65°	81	70	60	58	61	81
75°	38	28	16	10	10	40
85°	6	4	1	1	1	9
90°	0	0	0	0	0	



TEST NUMBER: P583771

CATALOG NUMBER: HCC8S10D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	466.9	466.9	466.9	466.9	466.9	466.9	466.9	466.9	466.9	466.9	466.9
2.5°	471.2	471.9	471.2	471.2	470.6	470.0	469.4	468.7	467.5	466.1	466.1
5°	473.7	475.0	473.7	473.7	471.9	470.6	469.4	467.5	464.9	463.0	463.0
7.5°	475.6	475.6	475.6	473.7	472.5	470.6	467.5	464.2	461.1	458.0	456.6
10°	475.6	475.6	475.0	472.5	471.2	467.5	464.2	459.9	455.4	451.0	449.7
12.5°	473.7	474.4	473.1	470.6	467.5	463.0	458.6	452.9	447.9	442.8	440.2
15°	471.2	470.6	469.4	466.1	462.4	456.6	452.2	445.9	439.0	432.6	430.1
17.5°	464.9	464.9	463.0	459.9	454.8	448.5	441.5	434.5	427.0	420.0	416.9
20°	456.6	456.6	454.1	450.4	445.3	437.0	429.5	421.3	412.4	405.4	402.3
22.5°	444.6	445.3	442.1	437.6	432.0	422.5	414.9	404.8	395.9	387.8	385.2
25°	428.9	430.1	427.0	422.5	414.9	406.8	397.3	387.8	377.7	369.4	365.6
27.5°	410.5	411.1	408.0	403.5	395.9	387.0	377.7	367.5	358.0	349.2	345.3
30°	390.3	387.8	386.4	380.8	372.5	364.9	354.2	345.9	335.8	328.3	323.8
32.5°	361.8	363.1	359.3	354.8	348.5	339.7	330.8	321.3	311.8	306.1	303.0
35°	333.3	334.6	332.7	328.3	321.3	313.7	304.8	297.9	289.7	282.7	279.6
37.5°	303.6	303.6	302.3	299.8	294.7	287.8	279.0	272.0	265.0	259.4	257.5
40°	273.9	272.6	272.0	270.1	265.6	259.4	253.6	248.0	241.0	237.2	234.6
42.5°	244.7	244.7	243.5	241.6	237.2	234.0	228.4	222.0	217.0	213.1	213.1
45°	218.2	218.9	217.0	215.6	213.1	208.1	203.0	198.6	194.1	191.6	190.4
47.5°	194.8	194.8	192.9	191.6	189.1	184.7	180.3	176.5	173.3	171.4	170.8
50°	172.7	172.7	172.7	169.5	166.4	163.2	160.0	155.7	153.7	152.4	151.8
52.5°	153.7	153.0	153.0	150.5	147.4	143.6	140.4	136.7	134.7	133.4	134.1
55°	136.7	136.7	135.9	132.8	129.7	125.8	122.7	119.6	118.3	117.1	117.7
56°	129.7	129.7	129.0	126.5	122.7	119.6	115.8	112.6	110.7	111.3	111.3
57°	124.6	123.3	123.3	120.2	117.1	112.6	109.4	106.3	105.1	104.3	104.3
58°	118.3	117.7	117.1	113.8	110.7	106.9	103.7	100.6	98.7	98.7	98.1
59°	111.9	111.9	110.7	108.2	105.1	101.2	98.1	94.8	93.0	92.3	92.3
60°	106.3	106.9	105.1	102.4	99.9	95.6	91.7	89.2	87.3	86.7	86.7
61°	101.2	101.2	99.9	96.8	93.6	90.4	86.7	83.5	82.2	81.0	81.0
62°	96.8	95.6	94.8	91.7	88.6	84.7	81.6	78.5	76.6	75.2	75.8
63°	91.1	90.4	89.2	86.7	83.5	79.7	75.8	73.3	71.5	69.6	70.2
64°	86.7	86.1	84.1	81.6	78.5	74.6	70.8	68.3	67.1	65.1	64.5
65°	81.0	80.3	79.7	76.6	73.3	69.6	66.5	63.8	62.0	60.7	59.5
66°	75.8	76.6	75.2	72.7	69.0	65.7	61.3	58.8	57.6	55.7	54.5
67°	71.5	71.5	70.2	67.7	63.8	60.7	57.6	54.5	52.5	50.6	50.0
67.5°	69.0	69.0	67.7	64.5	62.0	58.2	55.1	52.5	50.0	48.7	47.5
68°	66.5	66.5	65.7	63.2	60.1	56.3	53.1	50.0	47.5	45.6	45.0
69°	62.0	62.6	61.3	58.8	55.7	51.9	48.7	46.2	43.6	41.7	40.5
70°	58.2	57.6	56.3	53.7	50.6	48.1	45.0	41.7	39.2	36.7	36.1
71°	53.1	53.1	51.9	50.0	46.8	43.6	40.5	38.0	35.5	32.2	31.6
72°	49.3	49.3	48.1	45.6	43.0	39.9	36.7	33.5	31.6	28.5	27.2
72.5°	46.8	47.5	46.2	43.6	41.1	37.3	34.7	32.2	29.1	26.6	25.2
73°	45.6	45.0	44.2	41.7	38.6	36.1	32.9	30.4	27.2	24.6	23.4



TEST NUMBER: P583771
 CATALOG NUMBER: HCC8S10D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	28.5	28.5	27.9	25.2	22.7	20.2	17.7	15.1	12.6	10.1	8.9
80°	19.6	20.2	19.0	17.7	15.9	13.3	10.7	8.9	6.4	5.0	3.8
82.5°	12.6	12.6	12.0	10.7	9.5	7.6	6.4	4.4	3.1	2.5	1.9
85°	6.4	7.0	6.4	5.6	4.4	3.8	3.1	1.9	1.3	0.6	0.6
87.5°	2.5	2.5	2.5	1.9	1.9	1.3	0.6	0.6	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583771

CATALOG NUMBER: HCC8S10D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	466.9	466.9	466.9	466.9	466.9	466.9	466.9	466.9	466.9	466.9
2.5°	464.9	464.9	463.6	463.0	462.4	461.7	461.1	460.5	460.5	461.1
5°	461.1	459.9	457.4	456.6	454.8	454.1	452.9	452.2	452.9	452.2
7.5°	455.4	452.9	449.7	448.5	445.9	444.6	442.8	442.8	441.5	442.1
10°	447.9	444.0	440.2	437.6	435.8	433.9	432.6	431.4	430.8	430.8
12.5°	438.4	433.9	430.1	426.3	423.1	421.9	419.4	419.4	418.1	417.5
15°	427.6	421.9	417.5	413.6	411.1	408.6	406.8	405.4	404.2	404.2
17.5°	413.6	408.6	404.2	399.8	395.9	394.0	392.2	390.3	390.3	389.0
20°	398.5	392.8	389.0	384.5	381.4	378.3	375.7	375.7	374.4	375.0
22.5°	381.4	374.4	370.7	367.5	364.3	361.8	359.3	359.3	358.7	358.0
25°	362.4	356.8	352.3	348.5	346.7	344.1	343.4	342.2	341.6	341.6
27.5°	342.2	337.8	332.1	330.2	327.7	326.3	326.3	325.7	324.5	325.1
30°	320.7	315.6	312.5	311.2	308.7	308.7	308.1	306.8	306.8	307.4
32.5°	299.8	294.7	292.2	291.6	289.1	289.1	288.5	289.1	289.1	289.7
35°	277.1	272.6	272.0	270.1	269.5	269.5	269.5	270.7	272.0	270.1
37.5°	255.5	252.4	250.5	249.9	250.5	250.5	251.1	253.0	252.4	251.7
40°	233.4	230.9	229.6	229.6	230.9	232.1	232.1	234.0	234.6	234.0
42.5°	211.3	209.4	209.4	210.0	211.3	211.9	213.8	215.6	216.4	217.0
45°	190.4	190.4	190.4	191.0	191.6	192.9	195.4	197.4	198.0	198.6
47.5°	170.2	169.5	171.4	172.0	173.9	174.5	176.5	179.0	179.6	180.3
50°	151.2	152.4	153.0	154.9	156.3	156.3	158.8	160.0	161.9	161.9
52.5°	133.4	135.3	135.9	137.9	138.5	139.2	140.4	142.3	143.6	143.6
55°	117.7	118.3	119.6	120.2	122.1	122.7	123.9	124.6	126.5	125.8
56°	110.7	111.9	112.6	113.8	115.2	115.8	117.1	117.7	118.9	119.6
57°	104.3	105.1	106.9	107.6	108.8	108.8	109.4	111.3	111.3	111.9
58°	98.1	99.3	99.9	100.6	101.8	102.4	103.7	104.3	105.1	104.3
59°	92.3	93.0	93.6	93.6	94.8	94.8	96.8	98.1	98.7	98.7
60°	86.7	86.7	87.3	87.9	89.2	89.8	89.8	91.1	91.1	91.1
61°	81.0	81.0	81.6	82.2	82.8	82.8	84.1	84.1	84.7	85.3
62°	75.8	75.2	75.2	75.8	75.8	77.2	77.8	78.5	79.1	78.5
63°	70.2	69.6	69.6	69.6	69.6	70.8	70.8	71.5	72.7	72.1
64°	63.8	63.8	63.8	63.8	64.5	64.5	65.7	66.5	67.1	67.7
65°	59.5	58.2	57.6	57.6	58.2	58.8	59.5	60.1	60.7	60.7
66°	54.5	53.1	52.5	52.5	52.5	52.5	53.7	53.7	55.1	55.1
67°	48.7	47.5	46.8	46.2	46.2	46.2	48.1	47.5	47.5	47.5
67.5°	46.8	45.0	44.2	43.6	43.0	44.2	43.6	44.2	44.2	43.6
68°	44.2	43.0	41.7	40.5	40.5	40.5	41.1	41.7	41.1	40.5
69°	39.2	38.6	36.7	35.5	34.7	35.5	34.7	35.5	34.7	35.5
70°	34.7	32.9	31.0	30.4	29.7	29.7	29.7	29.1	29.7	29.1
71°	30.4	28.5	26.6	25.2	24.6	24.6	24.0	24.6	24.0	24.6
72°	26.0	24.0	21.5	20.2	20.2	20.2	20.2	19.6	20.2	19.6
72.5°	24.0	21.5	19.6	18.4	17.7	17.7	17.7	17.7	17.1	17.7
73°	22.1	19.6	17.1	16.5	16.5	16.5	15.9	15.1	15.9	15.9



TEST NUMBER: P583771
 CATALOG NUMBER: HCC8S10D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	7.6	5.6	5.0	5.0	5.0	5.0	5.0	5.0	4.4	4.4
80°	3.1	2.5	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	41.1	41.1	39.9	38.0	34.7	31.6	29.1	26.6	23.4	20.2	19.0
75°	38.0	37.3	36.1	34.1	31.6	28.5	26.0	22.7	20.2	17.1	15.9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	18.4	15.1	13.9	12.6	12.6	12.6	12.0	12.0	12.0	12.6
75°	14.5	12.0	10.7	9.5	10.1	9.5	10.1	9.5	9.5	9.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)