

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583287

Luminaire Tested: **HCC6W07D010MW-HM60525827-61RWWH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583287  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W07D010MW-HM60525827-61RWWH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 878.4 lumens  
Efficiency: N/A  
Efficacy: 109.8 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583287  
CATALOG NUMBER: HCC6W07D010MW-HM60525827-61RWWH

### Luminous Intensity Polar Plot





TEST NUMBER: P583287

CATALOG NUMBER: HCC6W07D010MW-HM60525827-61RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	24576	24576	24576
5°	24829	24604	24439
10°	25183	24526	24270
15°	25772	24376	24137
20°	26013	23650	23715
25°	25447	22459	22882
30°	24099	20864	21573
35°	21824	19066	19776
40°	19007	17239	17869
45°	16126	15257	15800
50°	14285	13322	13680
55°	12587	11402	11335
60°	11271	9604	8815
65°	10053	7705	6317
70°	8848	5562	3959
75°	7456	3368	2224
80°	5746	1452	916
85°	3334	377	377



TEST NUMBER: P583287  
 CATALOG NUMBER: HCC6W07D010MW-HM60525827-61RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.6	4.8
10°-20°	122.3	13.9
20°-30°	176.8	20.1
30°-40°	186.0	21.2
40°-50°	156.4	17.8
50°-60°	109.8	12.5
60°-70°	60.4	6.9
70°-80°	21.4	2.4
80°-90°	2.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.6	38.9
0°-40°	527.6	60.1
0°-60°	793.8	90.4
0°-90°	878.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	878.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	448	448	448	448	448	
5°	451	450	447	445	444	43
15°	454	446	430	424	425	128
25°	421	400	371	372	378	192
35°	326	307	285	291	296	202
45°	208	202	197	202	204	163
55°	132	124	119	119	119	118
65°	78	69	59	49	49	77
75°	35	28	16	10	10	38
85°	5	3	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P583287

CATALOG NUMBER: HCC6W07D010MW-HM60525827-61RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3
2.5°	448.3	448.3	447.6	447.6	446.5	446.5	445.9	445.9	445.9
5°	451.2	451.2	450.0	448.3	447.1	445.4	445.4	444.7	444.1
7.5°	453.0	452.4	450.6	448.3	445.4	442.4	441.2	441.8	441.2
10°	452.4	451.2	448.9	444.1	440.6	436.5	436.0	435.3	436.0
12.5°	453.5	451.8	447.1	441.2	435.3	430.7	430.1	430.1	430.7
15°	454.1	452.4	446.5	437.7	429.5	424.8	424.2	424.8	425.3
17.5°	452.4	450.0	441.2	429.5	420.1	415.4	415.4	416.6	417.7
20°	445.9	442.4	430.1	415.9	405.4	401.9	403.0	405.4	406.5
22.5°	434.2	430.1	415.9	400.1	389.0	386.0	389.0	391.9	393.0
25°	420.7	415.9	399.5	383.1	371.3	367.8	371.9	376.6	378.3
27.5°	402.4	397.1	381.9	363.1	351.3	349.5	354.3	359.6	360.7
30°	380.7	374.8	357.8	340.1	329.6	329.0	334.3	339.0	340.8
32.5°	354.3	349.0	334.3	316.7	307.3	307.3	312.6	316.7	318.5
35°	326.1	320.2	307.3	292.5	284.9	285.5	290.8	293.8	295.5
37.5°	292.5	290.8	280.9	268.5	263.2	264.3	268.5	270.9	272.6
40°	265.6	260.8	254.4	244.4	240.9	242.0	246.2	248.5	249.7
42.5°	236.2	233.3	228.0	220.9	218.6	220.4	223.9	225.6	225.0
45°	208.0	207.3	202.1	198.0	196.8	199.2	201.6	203.3	203.8
47.5°	187.4	185.0	180.4	177.4	176.3	178.6	180.9	182.2	182.2
50°	167.5	165.1	160.4	157.5	156.2	158.6	160.4	161.6	160.4
52.5°	147.5	145.1	141.1	137.4	136.9	138.1	138.7	139.2	140.4
55°	131.7	129.3	124.5	120.4	119.3	119.9	119.3	119.3	118.6
57.5°	116.4	114.0	109.3	104.6	102.8	102.2	100.5	99.9	99.3
60°	102.8	99.9	95.2	89.8	87.6	85.2	82.3	80.4	80.4
62.5°	89.8	86.9	81.7	76.9	73.4	69.3	64.6	62.3	62.3
65°	77.5	75.2	69.3	64.0	59.4	54.0	48.7	47.6	48.7
67.5°	65.8	63.4	57.6	52.3	46.5	40.0	35.2	35.2	36.5
70°	55.2	52.9	47.6	41.1	34.7	28.2	24.7	24.7	24.7
72.5°	45.2	42.9	37.0	31.2	24.7	18.2	16.4	17.0	16.4
75°	35.2	33.5	28.2	21.8	15.9	11.2	10.5	10.0	10.5
77.5°	26.4	24.7	19.9	14.0	8.8	6.5	5.9	5.9	5.9
80°	18.2	16.4	12.9	8.3	4.6	2.9	2.9	2.9	2.9
82.5°	11.2	9.4	7.0	4.1	1.8	1.8	1.8	1.8	1.8
85°	5.3	4.1	2.9	1.1	0.6	0.6	0.6	0.6	0.6
87.5°	1.1	1.1	0.6	0.6	0.0	0.6	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)