

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583304

Luminaire Tested: **HCC6S07D010MW-HM60525830-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010MW-HM60525830-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 941.6 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583304
CATALOG NUMBER: HCC6S07D010MW-HM60525830-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583304

CATALOG NUMBER: HCC6S07D010MW-HM60525830-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25563	25563	25563
5°	25699	25836	25836
10°	26419	25957	25857
15°	27259	26107	26107
20°	27577	25511	26101
25°	27020	24231	25374
30°	25561	22522	23839
35°	23135	20592	21609
40°	20123	18635	19351
45°	17196	16614	17196
50°	15095	14550	15138
55°	13170	12262	12750
60°	11644	10186	10054
65°	10325	8042	6888
70°	9120	5658	4151
75°	7752	3219	2012
80°	5809	1010	600
85°	3208	440	440



TEST NUMBER: P583304
 CATALOG NUMBER: HCC6S07D010MW-HM60525830-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	4.8
10°-20°	130.9	13.9
20°-30°	191.2	20.3
30°-40°	200.5	21.3
40°-50°	168.9	17.9
50°-60°	118.3	12.6
60°-70°	63.4	6.7
70°-80°	21.3	2.3
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.8	39.0
0°-40°	567.3	60.2
0°-60°	854.5	90.8
0°-90°	941.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	941.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	466	466	466	466	466	
5°	467	469	470	470	470	45
15°	480	474	460	458	460	135
25°	447	428	401	408	420	205
35°	346	328	308	317	323	215
45°	222	218	214	220	222	173
55°	138	133	128	131	133	124
65°	80	73	62	51	53	79
75°	37	28	15	10	10	39
85°	5	2	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P583304

CATALOG NUMBER: HCC6S07D010MW-HM60525830-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3
2.5°	463.2	463.2	464.5	465.8	467.0	467.0	467.6	468.3	467.6
5°	467.0	467.0	468.9	469.5	469.5	468.9	469.5	469.5	469.5
7.5°	472.7	471.4	472.0	470.8	469.5	468.9	468.3	468.3	468.3
10°	474.6	473.4	472.0	469.5	466.3	464.5	463.9	464.5	464.5
12.5°	477.1	475.9	472.7	467.6	463.9	460.7	460.0	461.4	461.4
15°	480.3	479.0	473.9	465.8	460.0	456.9	457.5	458.8	460.0
17.5°	480.3	477.8	469.5	458.8	451.8	448.7	451.2	454.3	456.3
20°	472.7	470.2	458.8	445.5	437.3	435.4	439.8	445.5	447.4
22.5°	462.6	457.5	444.2	428.5	419.5	419.5	425.9	432.9	435.4
25°	446.7	443.0	427.8	409.5	400.6	400.1	407.7	417.1	419.5
27.5°	429.1	424.1	407.7	388.6	379.2	379.8	388.1	397.5	400.1
30°	403.8	397.5	383.0	364.6	355.8	358.3	366.5	373.4	376.6
32.5°	375.4	369.7	356.4	339.3	331.7	334.3	341.3	347.6	350.1
35°	345.7	339.3	328.0	312.8	307.7	310.3	316.6	321.7	322.9
37.5°	312.1	307.7	299.6	287.6	283.7	286.9	292.0	295.1	296.4
40°	281.2	277.5	270.4	261.6	260.4	262.9	268.0	269.9	270.4
42.5°	250.8	247.7	243.3	237.0	237.0	239.5	243.9	245.2	245.9
45°	221.8	219.9	218.0	213.0	214.3	217.4	219.9	221.8	221.8
47.5°	196.6	197.1	194.6	190.8	192.2	195.2	197.1	199.1	199.1
50°	177.0	175.0	172.6	168.7	170.6	173.1	175.7	177.0	177.5
52.5°	154.2	153.5	151.7	147.3	148.5	149.8	152.3	154.2	154.9
55°	137.8	135.8	133.4	128.3	128.3	129.5	130.9	132.1	133.4
57.5°	121.9	120.1	116.2	110.6	109.9	109.9	109.3	110.6	112.5
60°	106.2	105.5	99.8	94.8	92.9	91.0	88.5	89.1	91.7
62.5°	92.2	91.0	86.0	79.6	75.8	72.6	69.6	68.9	71.4
65°	79.6	78.4	72.6	66.4	62.0	56.2	51.2	51.2	53.1
67.5°	68.2	65.7	60.6	53.7	48.0	41.1	36.0	37.3	38.0
70°	56.9	55.0	49.3	42.4	35.3	28.4	25.3	25.9	25.9
72.5°	46.8	44.2	38.5	31.6	24.7	18.4	17.1	16.4	16.4
75°	36.6	34.1	28.4	21.5	15.2	10.8	9.5	9.5	9.5
77.5°	26.5	24.7	19.6	13.3	8.3	5.1	4.4	3.7	3.7
80°	18.4	16.4	12.0	6.9	3.2	1.9	1.9	1.9	1.9
82.5°	10.8	8.8	5.7	3.2	1.2	0.7	0.7	0.7	0.7
85°	5.1	3.7	2.5	1.2	0.7	0.7	0.7	0.7	0.7
87.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)