

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583813

Luminaire Tested: **HCC8W10D010MW-HM80520935-81WWWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583813  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W10D010MW-HM80520935-81WWWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1047.2 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583813  
CATALOG NUMBER: HCC8W10D010MW-HM80520935-81WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P583813

CATALOG NUMBER: HCC8W10D010MW-HM80520935-81WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	16053	16053	16053
5°	16644	16003	15452
10°	17112	15863	14820
15°	17494	15582	14168
20°	17520	14974	13589
25°	17186	14144	13113
30°	16297	13114	12537
35°	14809	11941	11971
40°	12950	10716	11283
45°	11221	9546	10514
50°	9825	8477	9580
55°	8752	7516	8666
60°	7888	6753	7610
65°	7121	5939	6640
70°	6401	4995	4932
75°	5647	3967	3693
80°	4724	3285	3552
85°	3644	2901	3149



TEST NUMBER: P583813

CATALOG NUMBER: HCC8W10D010MW-HM80520935-81WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.1	4.7
10°-20°	138.3	13.2
20°-30°	197.7	18.9
30°-40°	210.1	20.1
40°-50°	180.9	17.3
50°-60°	135.2	12.9
60°-70°	86.3	8.2
70°-80°	39.2	3.7
80°-90°	10.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.2	36.8
0°-40°	595.2	56.8
0°-60°	911.3	87.0
0°-90°	1047.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1047.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	521	521	521	521	521	
5°	538	530	517	504	499	52
15°	548	530	488	455	444	154
25°	505	473	416	390	385	231
35°	393	366	317	309	318	245
45°	257	243	219	225	241	200
55°	163	149	140	152	161	146
65°	98	86	81	85	91	97
75°	47	41	33	30	31	50
85°	10	9	8	9	9	12
90°	0	0	0	0	0	



TEST NUMBER: P583813

CATALOG NUMBER: HCC8W10D010MW-HM80520935-81WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6
2.5°	530.2	528.8	529.5	528.8	529.5	529.5	528.0	528.0	528.0	528.0	525.9
5°	537.7	536.9	536.9	536.2	535.5	536.2	535.5	534.6	533.2	532.5	530.2
7.5°	542.1	542.1	542.1	542.1	541.4	540.7	539.8	538.4	536.9	535.5	533.9
10°	546.5	547.3	546.5	545.8	545.0	543.5	542.8	541.4	539.1	536.9	535.5
12.5°	548.7	548.7	548.0	548.0	546.5	545.8	543.5	541.4	539.1	536.9	533.2
15°	548.0	548.0	547.3	546.5	544.3	543.5	542.1	539.8	536.2	533.2	529.5
17.5°	543.5	542.8	541.4	541.4	538.4	537.7	536.2	533.2	529.5	525.0	520.6
20°	533.9	533.9	533.2	532.5	529.5	527.3	525.9	522.1	519.1	514.0	509.5
22.5°	520.6	522.1	520.6	519.1	515.4	514.7	512.5	508.1	503.6	497.7	492.6
25°	505.1	504.4	503.6	502.2	499.2	497.7	494.7	490.3	485.8	479.2	473.3
27.5°	485.1	482.2	482.2	479.2	477.0	474.8	473.3	468.9	463.0	457.7	450.4
30°	457.7	458.6	454.8	454.1	450.4	448.9	445.9	441.5	436.3	430.4	424.5
32.5°	428.2	426.0	426.0	423.0	420.1	417.8	417.1	411.9	407.5	401.6	395.7
35°	393.4	393.4	391.3	390.5	387.5	386.1	383.8	380.9	375.7	370.5	366.1
37.5°	359.4	358.0	357.2	355.7	353.5	351.3	351.3	346.1	345.3	339.4	333.6
40°	321.7	323.2	321.7	319.5	318.8	317.2	316.5	313.6	311.3	306.1	302.4
42.5°	289.9	288.5	288.5	287.6	284.8	284.8	283.2	281.7	278.0	276.6	272.1
45°	257.3	258.8	256.6	257.3	254.5	254.5	254.5	251.5	248.5	246.3	243.3
47.5°	229.2	229.9	229.9	227.8	227.1	227.1	225.6	224.1	221.9	218.9	216.7
50°	204.8	205.5	204.1	203.4	201.9	201.2	201.2	198.2	196.8	193.8	192.3
52.5°	182.7	182.7	182.0	182.0	179.7	179.7	178.3	176.0	174.5	173.1	169.4
55°	162.8	162.8	161.9	161.2	161.2	159.0	158.3	156.0	154.6	151.6	149.4
57.5°	143.5	144.2	143.5	142.7	142.0	141.2	139.8	137.5	136.1	133.9	132.3
60°	127.9	127.9	127.2	126.5	125.0	124.3	123.4	122.0	119.8	118.3	116.1
62.5°	113.1	112.4	111.7	110.9	109.5	109.5	107.9	106.5	104.3	102.8	101.3
65°	97.6	97.6	96.9	96.9	96.2	94.7	93.9	93.2	90.3	89.4	86.5
67.5°	83.5	84.3	82.8	82.8	81.4	81.4	80.7	78.4	77.6	76.2	74.6
70°	71.0	71.0	71.0	70.3	68.8	68.0	67.3	65.9	65.0	63.6	62.1
72.5°	58.4	58.4	57.7	57.7	57.0	56.3	55.4	54.0	54.0	52.5	51.1
75°	47.4	47.4	46.6	45.8	45.1	45.1	44.4	43.6	42.2	41.5	40.6
77.5°	36.2	36.2	36.2	35.5	34.7	34.7	34.7	33.3	31.9	31.9	31.0
80°	26.6	26.6	25.8	25.8	25.1	25.1	25.1	24.4	23.7	23.0	22.2
82.5°	17.8	17.8	17.8	17.8	17.1	17.1	17.1	16.2	15.5	15.5	15.5
85°	10.3	10.3	10.3	10.3	9.6	9.6	9.6	9.6	9.6	8.9	8.9
87.5°	4.4	3.7	4.4	3.7	4.4	3.7	4.4	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583813

CATALOG NUMBER: HCC8W10D010MW-HM80520935-81WWWB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6
2.5°	526.6	525.9	525.0	524.3	524.3	523.6	522.1	521.4	520.6	519.9	519.9
5°	529.5	528.8	527.3	525.9	525.0	523.6	522.1	520.6	519.1	517.0	516.3
7.5°	531.8	529.5	528.0	525.0	524.3	522.9	520.6	518.4	515.4	512.5	510.2
10°	531.8	528.8	526.6	522.9	521.4	519.9	517.0	513.3	509.5	506.6	502.9
12.5°	530.2	526.6	522.9	519.1	517.0	514.7	510.2	506.6	502.2	497.7	494.7
15°	525.0	520.6	516.3	511.8	509.5	506.6	502.2	497.0	492.6	488.1	483.0
17.5°	515.4	511.0	505.8	500.6	497.7	495.5	488.9	485.1	478.5	474.1	469.6
20°	502.9	497.7	491.0	485.8	482.2	480.0	474.8	468.2	463.0	456.3	451.8
22.5°	486.6	480.0	473.3	468.2	464.5	461.4	454.8	448.2	443.8	437.8	432.6
25°	467.3	460.7	454.1	446.7	442.9	440.1	434.2	428.2	422.3	415.7	411.2
27.5°	444.5	437.0	431.2	424.5	420.8	416.4	409.8	403.8	397.9	393.4	387.5
30°	419.4	411.2	405.3	398.6	395.0	391.3	384.5	378.6	373.5	368.3	365.3
32.5°	389.0	383.1	377.2	370.5	367.6	365.3	358.7	352.8	346.9	342.4	340.2
35°	360.1	353.5	348.3	342.4	338.7	336.4	330.6	325.4	322.5	317.2	314.3
37.5°	329.8	324.7	318.8	312.9	310.6	308.4	304.0	298.8	294.4	290.6	289.2
40°	298.1	293.6	288.5	284.8	282.5	280.3	276.6	272.9	270.0	266.2	264.8
42.5°	267.7	264.8	260.4	255.9	253.6	252.9	248.5	245.6	244.0	242.6	241.1
45°	240.4	236.0	232.9	229.9	227.8	226.3	224.1	221.9	220.3	218.9	217.4
47.5°	213.7	210.0	207.1	204.8	202.7	201.9	200.4	198.2	196.8	196.8	196.8
50°	189.3	186.3	183.4	182.0	181.1	179.7	178.3	177.5	176.7	176.7	176.7
52.5°	167.9	164.9	162.8	161.2	161.2	159.7	158.3	157.6	157.6	157.6	157.6
55°	148.0	145.7	144.2	142.7	141.2	140.5	140.5	140.5	139.8	139.8	140.5
57.5°	130.2	128.7	126.5	125.0	124.3	124.3	123.4	122.7	123.4	124.3	125.0
60°	113.9	112.4	111.7	109.5	109.5	109.5	108.7	108.7	108.7	109.5	110.2
62.5°	99.0	98.3	96.9	96.2	95.4	95.4	94.7	94.7	94.7	94.7	95.4
65°	85.8	84.3	82.8	82.8	82.8	82.1	82.1	80.7	81.4	81.4	80.7
67.5°	73.2	71.8	71.0	70.3	69.5	69.5	68.8	68.0	67.3	67.3	67.3
70°	61.4	59.9	59.9	58.4	58.4	57.7	57.0	57.0	56.3	55.4	54.7
72.5°	49.5	48.8	48.1	47.4	47.4	47.4	46.6	45.8	45.1	44.4	42.9
75°	39.2	39.2	37.7	37.0	37.0	36.2	35.5	34.7	34.0	33.3	32.6
77.5°	30.3	29.6	28.1	27.4	27.4	27.4	26.6	25.8	25.1	24.4	23.7
80°	22.2	21.4	20.7	20.0	20.0	20.0	19.2	19.2	18.5	18.5	18.5
82.5°	14.8	14.8	14.1	14.1	14.1	14.1	13.3	13.3	13.3	13.3	13.3
85°	8.9	8.9	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583813

CATALOG NUMBER: HCC8W10D010MW-HM80520935-81WWWB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6
2.5°	518.4	518.4	517.0	516.3	515.4	516.3	514.7	514.0	513.3	513.3	512.5
5°	514.0	513.3	510.2	509.5	508.8	508.1	506.6	505.1	503.6	502.9	502.2
7.5°	508.1	505.8	502.9	502.2	501.4	499.2	497.0	495.5	493.3	492.6	491.0
10°	499.9	497.0	494.7	492.6	491.0	488.9	486.6	484.4	481.4	480.7	478.5
12.5°	490.3	486.6	482.2	481.4	479.2	476.2	473.3	471.1	468.9	467.3	465.2
15°	478.5	474.8	470.3	468.2	465.9	463.7	460.0	457.0	454.8	452.6	450.4
17.5°	464.5	460.0	456.3	454.1	452.6	448.9	445.9	442.2	440.1	437.8	435.6
20°	447.4	443.8	438.6	436.3	435.6	432.6	429.0	427.4	424.5	422.3	420.8
22.5°	428.2	424.5	420.1	418.5	415.7	414.1	410.5	408.9	407.5	405.3	404.5
25°	406.8	403.0	399.3	398.6	396.4	395.0	392.7	390.5	390.5	388.2	388.2
27.5°	384.5	380.9	377.9	376.5	375.7	374.2	372.0	371.3	370.5	369.7	369.7
30°	360.8	356.5	355.0	354.2	353.5	352.1	351.3	349.8	350.5	351.3	350.5
32.5°	335.7	334.3	331.3	329.8	330.6	329.8	328.4	329.8	329.1	330.6	331.3
35°	311.3	309.9	308.4	308.4	306.9	306.9	306.9	307.7	309.2	309.9	311.3
37.5°	287.6	285.5	284.8	284.0	284.8	284.8	284.8	286.2	287.6	289.2	291.4
40°	262.5	261.1	261.1	261.1	261.1	263.2	262.5	264.0	265.5	267.7	270.0
42.5°	238.8	238.8	239.6	239.6	239.6	239.6	241.1	243.3	245.6	247.7	250.0
45°	216.7	216.7	216.7	218.2	218.2	218.9	221.9	223.3	224.8	227.1	229.2
47.5°	195.9	195.9	196.8	197.5	198.2	199.7	201.2	203.4	205.5	207.1	209.3
50°	176.7	177.5	179.0	180.4	180.4	181.1	183.4	184.9	186.3	188.6	189.3
52.5°	158.3	159.7	161.2	161.9	162.8	164.2	164.9	167.1	167.9	170.1	170.8
55°	141.2	142.0	144.2	145.0	145.0	146.4	148.0	149.4	151.6	151.6	153.1
57.5°	125.7	126.5	127.9	128.7	127.9	130.2	130.9	132.3	133.1	134.6	135.3
60°	110.2	111.7	112.4	112.4	113.1	113.9	115.4	115.4	116.8	118.3	118.3
62.5°	95.4	96.2	96.9	97.6	98.3	97.6	99.9	99.9	101.3	102.0	103.5
65°	81.4	82.1	82.1	82.8	82.8	83.5	83.5	84.3	85.1	86.5	87.3
67.5°	67.3	67.3	67.3	68.0	67.3	68.0	68.0	68.8	68.8	70.3	71.0
70°	54.7	54.0	53.2	53.2	53.2	53.2	52.5	53.2	53.2	54.0	54.0
72.5°	42.2	41.5	40.6	39.9	39.9	39.2	38.5	39.2	39.2	39.9	39.9
75°	31.9	30.3	30.3	30.3	29.6	29.6	29.6	30.3	30.3	30.3	31.0
77.5°	23.7	23.7	23.0	23.0	23.0	23.7	23.7	24.4	24.4	24.4	24.4
80°	17.8	18.5	18.5	18.5	18.5	19.2	19.2	19.2	19.2	20.0	20.0
82.5°	13.3	13.3	13.3	13.3	14.1	14.1	14.1	14.1	14.1	14.1	14.1
85°	8.2	8.9	8.9	8.2	8.9	8.9	8.9	8.9	8.9	8.9	8.9
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P583813

CATALOG NUMBER: HCC8W10D010MW-HM80520935-81WWWB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6
2.5°	511.8	511.8	511.8	511.8	511.0	511.0	511.0	510.2
5°	500.6	500.6	500.6	499.2	499.9	499.9	498.5	499.2
7.5°	489.6	488.9	488.1	488.1	487.4	486.6	485.8	486.6
10°	477.0	474.8	474.8	474.1	474.1	472.6	472.6	473.3
12.5°	463.0	461.4	461.4	460.7	460.0	459.3	458.6	458.6
15°	448.9	447.4	446.7	445.9	445.2	443.8	444.5	443.8
17.5°	434.9	432.6	432.6	431.9	431.2	429.7	429.7	429.0
20°	418.5	417.8	416.4	417.1	416.4	414.9	414.1	414.1
22.5°	402.3	402.3	401.6	401.6	400.9	400.1	399.3	399.3
25°	386.8	386.1	386.8	386.8	384.5	384.5	384.5	385.4
27.5°	369.0	369.7	369.0	369.0	369.0	369.0	369.7	369.0
30°	351.3	351.3	351.3	352.1	353.5	352.8	352.8	352.1
32.5°	332.1	332.8	332.8	333.6	334.3	335.7	335.7	336.4
35°	312.9	314.3	315.0	314.3	316.5	316.5	318.0	318.0
37.5°	292.8	293.6	295.1	295.8	297.3	298.1	298.8	298.8
40°	271.4	274.4	275.1	275.9	278.0	278.0	278.9	280.3
42.5°	251.5	254.5	255.2	255.9	257.3	259.6	258.8	260.4
45°	232.2	234.4	235.2	236.0	238.1	238.8	238.8	241.1
47.5°	211.6	213.0	213.7	215.2	216.7	218.2	219.6	218.9
50°	190.8	193.0	194.5	195.2	197.5	198.2	198.9	199.7
52.5°	172.4	173.8	174.5	175.3	177.5	178.3	179.0	180.4
55°	154.6	155.3	156.7	156.0	158.3	159.0	159.7	161.2
57.5°	136.8	137.5	138.4	138.4	139.8	141.2	142.0	142.7
60°	119.8	121.3	122.0	122.0	122.0	123.4	123.4	123.4
62.5°	104.3	104.3	105.1	105.1	106.5	106.5	106.5	106.5
65°	88.0	88.7	89.4	89.4	91.0	90.3	91.7	91.0
67.5°	71.0	71.0	72.5	72.5	71.8	72.5	72.5	72.5
70°	54.0	54.0	54.7	54.7	54.7	54.7	54.7	54.7
72.5°	39.9	39.9	39.9	40.6	39.9	39.9	40.6	39.9
75°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0
77.5°	24.4	24.4	25.1	25.1	25.1	25.1	25.1	25.1
80°	20.0	20.0	20.0	20.0	20.7	20.0	20.0	20.0
82.5°	14.8	14.1	14.8	14.1	14.8	14.8	14.8	14.8
85°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)