

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583824

Luminaire Tested: **HCC8S10D010MW-HM80520940-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010MW-HM80520940-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1279.2 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583824
CATALOG NUMBER: HCC8S10D010MW-HM80520940-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P583824
 CATALOG NUMBER: HCC8S10D010MW-HM80520940-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	98	97	96	95	94	92	92	92	84																
	1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	90	93	90	88	90	88	86	84																
	2	106	101	96	93	104	99	95	92	96	92	90	86	83	79	84	81	78	77	77	75	75	75	75	75	75	75	75	75																
	3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	75	75	75	75	75	75	75	75	75																
	4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70	70	70	70	70	70	70	70																
	5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64	64	64	64	64	64	64	64																
	6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59	59	59	59	59	59	59	59																
	7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54	54	54	54	54	54	54	54																
	8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50	50	50	50	50	50	50	50																
	9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46	46	46	46	46	46	46	46																
	10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43	43	43	43	43	43	43	43																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30691
5°	29865
10°	29640
15°	29198
20°	28313
25°	27257
30°	25462
35°	21073
40°	12720
45°	8569
50°	6174
55°	3521
60°	1548
65°	555
70°	207
75°	83
80°	0
85°	0



TEST NUMBER: P583824
 CATALOG NUMBER: HCC8S10D010MW-HM80520940-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	7.2
10°-20°	257.0	20.1
20°-30°	366.7	28.7
30°-40°	333.9	26.1
40°-50°	157.5	12.3
50°-60°	62.0	4.8
60°-70°	9.9	0.8
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.4	55.9
0°-40°	1049.3	82.0
0°-60°	1268.7	99.2
0°-90°	1279.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1279.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	995	
5°	965	92
15°	915	257
25°	801	367
35°	560	334
45°	196	157
55°	66	62
65°	8	10
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583824
CATALOG NUMBER: HCC8S10D010MW-HM80520940-81WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	995.3
2.5°	982.4
5°	964.8
7.5°	955.0
10°	946.6
12.5°	932.9
15°	914.6
17.5°	891.8
20°	862.8
22.5°	832.4
25°	801.1
27.5°	763.0
30°	715.1
32.5°	650.3
35°	559.8
37.5°	432.6
40°	316.0
42.5°	242.9
45°	196.5
47.5°	161.4
50°	128.7
52.5°	96.8
55°	65.5
57.5°	41.1
60°	25.1
62.5°	15.3
65°	7.6
67.5°	3.8
70°	2.3
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)