

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583820

Luminaire Tested: **HCC8S10D010MW-HM80520940-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010MW-HM80520940-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1132.3 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583820
CATALOG NUMBER: HCC8S10D010MW-HM80520940-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583820
 CATALOG NUMBER: HCC8S10D010MW-HM80520940-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89																			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71																			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64																			
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58																			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49																			
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45																			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42																			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26581
5°	26231
10°	25272
15°	24281
20°	23611
25°	22902
30°	20552
35°	13469
40°	7447
45°	6210
50°	5661
55°	5403
60°	5026
65°	4553
70°	4120
75°	3729
80°	3374
85°	3220



TEST NUMBER: P583820
 CATALOG NUMBER: HCC8S10D010MW-HM80520940-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.6	7.0
10°-20°	214.6	19.0
20°-30°	305.4	27.0
30°-40°	226.0	20.0
40°-50°	112.0	9.9
50°-60°	89.4	7.9
60°-70°	62.0	5.5
70°-80°	33.4	3.0
80°-90°	9.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.6	53.0
0°-40°	825.7	72.9
0°-60°	1027.0	90.7
0°-90°	1132.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	862	
5°	847	80
15°	761	215
25°	673	305
35°	358	226
45°	142	112
55°	100	89
65°	62	62
75°	31	33
85°	9	10
90°	0	



TEST NUMBER: P583820
CATALOG NUMBER: HCC8S10D010MW-HM80520940-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	862.0
2.5°	858.1
5°	847.4
7.5°	830.7
10°	807.1
12.5°	782.7
15°	760.6
17.5°	739.4
20°	719.5
22.5°	699.7
25°	673.1
27.5°	634.3
30°	577.2
32.5°	489.6
35°	357.8
37.5°	244.4
40°	185.0
42.5°	158.4
45°	142.4
47.5°	129.5
50°	118.0
52.5°	108.1
55°	100.5
57.5°	91.4
60°	81.5
62.5°	71.5
65°	62.4
67.5°	53.2
70°	45.7
72.5°	38.1
75°	31.3
77.5°	25.1
80°	19.0
82.5°	13.7
85°	9.1
87.5°	3.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)