

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583330

Luminaire Tested: **HCC6S07D010SL-HM60525835-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010SL-HM60525835-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 888.6 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583330
CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583330

CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	26149	26149	26149
5°	27311	26073	24873
10°	28056	25623	23374
15°	28752	25074	21901
20°	28878	23936	20115
25°	28272	22411	18449
30°	26821	20604	16901
35°	24360	18518	15165
40°	21225	16495	13647
45°	18366	14436	12001
50°	16042	12426	10516
55°	14174	10924	9022
60°	12740	9583	7817
65°	11402	8328	7588
70°	10194	7101	7101
75°	8832	5973	6672
80°	7072	5083	6093
85°	4843	4403	5284



TEST NUMBER: P583330
 CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.8	5.0
10°-20°	124.6	14.0
20°-30°	173.7	19.5
30°-40°	179.0	20.1
40°-50°	148.3	16.7
50°-60°	106.6	12.0
60°-70°	67.9	7.6
70°-80°	34.9	3.9
80°-90°	8.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.1	38.6
0°-40°	522.1	58.8
0°-60°	777.0	87.4
0°-90°	888.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	888.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	477	477	477	477	477	
5°	496	488	474	458	452	48
15°	507	487	442	401	386	143
25°	467	435	370	323	305	214
35°	364	334	277	240	227	226
45°	237	220	186	162	155	183
55°	148	136	114	101	94	134
65°	88	78	64	56	58	88
75°	42	36	28	30	32	44
85°	8	7	7	8	8	10
90°	0	0	0	0	0	



TEST NUMBER: P583330

CATALOG NUMBER: HCC6S07D010SL-HM60525835-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0
2.5°	486.1	484.1	481.5	478.9	475.1	470.6	466.8	465.4	463.5
5°	496.3	493.8	488.5	482.2	473.8	465.4	458.4	453.9	452.0
7.5°	502.7	499.5	492.4	481.5	469.3	457.2	446.9	440.4	437.9
10°	504.0	500.8	491.2	476.4	460.3	443.7	430.8	423.1	419.9
12.5°	505.9	501.5	489.2	471.9	451.4	432.1	416.0	406.4	403.2
15°	506.6	501.5	487.3	466.1	441.8	418.6	401.3	389.8	385.9
17.5°	504.0	498.2	481.5	455.8	428.3	403.8	383.3	371.1	366.0
20°	495.0	488.5	469.3	440.4	410.3	384.5	363.4	350.6	344.8
22.5°	483.5	475.1	453.3	422.5	391.0	364.0	342.8	330.0	324.3
25°	467.4	459.7	435.3	402.6	370.5	342.2	322.9	309.4	305.0
27.5°	448.8	439.8	414.8	382.0	349.3	321.0	302.4	290.2	284.4
30°	423.7	415.4	390.3	357.6	325.5	299.2	280.0	269.7	267.0
32.5°	394.2	387.1	362.8	332.0	301.2	276.7	260.7	249.7	247.2
35°	364.0	355.6	334.5	305.6	276.7	254.9	240.1	230.5	226.6
37.5°	331.3	323.6	305.6	280.0	254.2	233.7	220.8	212.6	208.7
40°	296.6	290.8	274.2	253.6	230.5	212.6	201.6	194.5	190.7
42.5°	264.6	258.8	247.2	228.0	208.7	192.6	183.0	176.5	173.3
45°	236.9	231.8	220.3	203.5	186.2	172.7	162.5	157.9	154.8
47.5°	209.3	206.8	196.5	181.1	165.0	153.4	146.4	141.3	138.7
50°	188.1	184.9	175.3	159.2	145.7	136.8	130.3	125.9	123.3
52.5°	166.3	163.0	154.1	140.6	129.7	121.3	114.9	111.0	108.5
55°	148.3	145.7	136.1	124.0	114.3	107.2	101.4	97.0	94.4
57.5°	131.7	129.0	120.1	108.5	100.2	93.7	88.6	84.7	81.6
60°	116.2	114.3	105.3	94.4	87.4	80.9	76.4	73.2	71.3
62.5°	102.8	98.9	91.2	81.6	75.1	70.0	65.5	63.6	64.8
65°	87.9	86.0	78.3	70.0	64.2	59.0	55.9	57.1	58.5
67.5°	75.8	73.2	66.7	59.0	53.9	50.1	48.2	50.8	51.3
70°	63.6	61.0	55.2	48.8	44.3	41.7	41.7	43.6	44.3
72.5°	52.0	50.1	45.0	39.8	36.6	34.7	35.9	37.3	37.8
75°	41.7	39.8	35.9	31.5	28.2	28.2	29.6	30.8	31.5
77.5°	32.1	30.8	27.0	23.8	22.4	22.4	23.8	24.4	25.0
80°	22.4	21.2	19.3	17.3	16.1	17.3	18.6	18.6	19.3
82.5°	14.7	14.2	12.8	11.6	11.6	12.2	12.8	13.5	13.5
85°	7.7	7.7	7.0	6.5	7.0	7.7	7.7	8.4	8.4
87.5°	2.6	2.6	2.6	2.6	3.2	3.2	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)