

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593028

Luminaire Tested: **HCC6S07D010MB-HM60525850-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593028
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010MB-HM60525850-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 967.6 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593028
CATALOG NUMBER: HCC6S07D010MB-HM60525850-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593028

CATALOG NUMBER: HCC6S07D010MB-HM60525850-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89	89	89	89	89	89	89	89	89	89	89																
	2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78	78	78	78	78	78	78	78	78	78	78																
	3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69	69	69	69	69	69	69	69	69	69	69																
	4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62	62	62	62	62	62	62	62	62	62	62																
	5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56	56	56	56	56	56	56	56	56	56	56																
	6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51	51	51	51	51	51	51	51	51	51	51																
	7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46	46	46	46	46	46	46	46	46	46	46																
	8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42	42	42	42	42	42	42	42	42	42	42																
	9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	39	39	39	39	39	39	39	39	39	39																
	10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36	36	36	36	36	36	36	36	36	36	36																

AVERAGE LUMINANCE (cd/sqm):

	0°	
0°	33018	
5°	33001	
10°	32681	
15°	32344	
20°	31427	
25°	30099	
30°	27935	
35°	24039	
40°	17547	
45°	12025	
50°	9663	
55°	8420	
60°	7773	
65°	7394	
70°	6908	
75°	6460	
80°	5872	
85°	4969	



TEST NUMBER: P593028
 CATALOG NUMBER: HCC6S07D010MB-HM60525850-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	5.9
10°-20°	160.0	16.5
20°-30°	227.6	23.5
30°-40°	219.1	22.6
40°-50°	126.1	13.0
50°-60°	79.9	8.3
60°-70°	56.5	5.8
70°-80°	32.3	3.3
80°-90°	9.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.5	45.9
0°-40°	663.6	68.6
0°-60°	869.6	89.9
0°-90°	967.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	967.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	602	
5°	600	57
15°	570	160
25°	498	228
35°	359	219
45°	155	126
55°	88	80
65°	57	57
75°	30	32
85°	8	9
90°	0	



TEST NUMBER: P593028
CATALOG NUMBER: HCC6S07D010MB-HM60525850-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	602.3
2.5°	599.7
5°	599.7
7.5°	595.7
10°	587.1
12.5°	578.5
15°	569.9
17.5°	556.6
20°	538.7
22.5°	518.8
25°	497.6
27.5°	471.8
30°	441.3
32.5°	404.1
35°	359.2
37.5°	304.1
40°	245.2
42.5°	193.5
45°	155.1
47.5°	130.5
50°	113.3
52.5°	99.4
55°	88.1
57.5°	78.2
60°	70.9
62.5°	64.2
65°	57.0
67.5°	50.3
70°	43.1
72.5°	36.5
75°	30.5
77.5°	24.5
80°	18.6
82.5°	13.3
85°	7.9
87.5°	3.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)