

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583843

Luminaire Tested: **HCC8S15D010MB-HM80520827-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583843  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S15D010MB-HM80520827-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1642.0 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583843  
CATALOG NUMBER: HCC8S15D010MB-HM80520827-81WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583843

CATALOG NUMBER: HCC8S15D010MB-HM80520827-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	32828
5°	32787
10°	32464
15°	32074
20°	31775
25°	31421
30°	29650
35°	24141
40°	13340
45°	8901
50°	7896
55°	7414
60°	7321
65°	7253
70°	6555
75°	5862
80°	5114
85°	4529



TEST NUMBER: P583843  
 CATALOG NUMBER: HCC8S15D010MB-HM80520827-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.4	6.1
10°-20°	283.7	17.3
20°-30°	421.5	25.7
30°-40°	379.6	23.1
40°-50°	168.3	10.2
50°-60°	124.6	7.6
60°-70°	96.9	5.9
70°-80°	52.6	3.2
80°-90°	14.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	805.6	49.1
0°-40°	1185.2	72.2
0°-60°	1478.2	90.0
0°-90°	1642.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1642.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1065	
5°	1059	100
15°	1005	284
25°	924	422
35°	641	380
45°	204	168
55°	138	125
65°	99	97
75°	49	53
85°	13	14
90°	0	



TEST NUMBER: P583843  
CATALOG NUMBER: HCC8S15D010MB-HM80520827-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1064.6
2.5°	1062.4
5°	1059.2
7.5°	1050.6
10°	1036.8
12.5°	1020.8
15°	1004.7
17.5°	988.7
20°	968.3
22.5°	948.1
25°	923.5
27.5°	886.0
30°	832.7
32.5°	755.7
35°	641.3
37.5°	478.9
40°	331.4
42.5°	244.7
45°	204.1
47.5°	180.6
50°	164.6
52.5°	149.7
55°	137.9
57.5°	128.2
60°	118.7
62.5°	110.1
65°	99.4
67.5°	86.5
70°	72.7
72.5°	61.0
75°	49.2
77.5°	38.4
80°	28.8
82.5°	20.4
85°	12.8
87.5°	5.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)