

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583365

Luminaire Tested: **HCC6S07D010SL-HM60525927-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583365
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010SL-HM60525927-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 628.7 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583365
CATALOG NUMBER: HCC6S07D010SL-HM60525927-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583365

CATALOG NUMBER: HCC6S07D010SL-HM60525927-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	19341	19341	19341
5°	19717	19304	18864
10°	20385	19060	18258
15°	21010	18723	17685
20°	21334	17945	16761
25°	20953	16713	15606
30°	19914	15230	14325
35°	17902	13619	12923
40°	15443	11937	11536
45°	13079	10265	10001
50°	11215	8673	8588
55°	9720	7302	7015
60°	8486	5921	5011
65°	7472	4566	2763
70°	6443	3013	1346
75°	5465	1461	530
80°	4230	631	316
85°	2516	314	314



TEST NUMBER: P583365

CATALOG NUMBER: HCC6S07D010SL-HM60525927-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.3	5.3
10°-20°	94.1	15.0
20°-30°	132.6	21.1
30°-40°	135.5	21.5
40°-50°	109.2	17.4
50°-60°	73.3	11.7
60°-70°	37.1	5.9
70°-80°	11.8	1.9
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	260.0	41.4
0°-40°	395.5	62.9
0°-60°	577.9	91.9
0°-90°	628.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	628.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	353	353	353	353	353	
5°	358	356	351	345	343	34
15°	370	355	330	315	312	105
25°	346	319	276	260	258	159
35°	268	243	204	192	193	166
45°	169	155	132	128	129	131
55°	102	90	76	73	73	92
65°	58	48	35	23	21	57
75°	26	18	7	2	2	28
85°	4	2	0	0	0	5
90°	0	0	0	0	0	



TEST NUMBER: P583365

CATALOG NUMBER: HCC6S07D010SL-HM60525927-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	352.8	352.8	352.8	352.8	352.8	352.8	352.8	352.8	352.8
2.5°	354.3	353.8	353.3	352.2	350.8	349.3	348.3	347.4	346.8
5°	358.3	357.2	355.8	353.8	350.8	347.4	345.3	343.4	342.8
7.5°	363.7	361.8	357.8	353.3	348.3	343.4	339.9	337.9	336.4
10°	366.2	362.7	357.2	349.9	342.4	336.4	332.0	329.0	328.0
12.5°	368.2	364.3	356.2	346.4	336.4	328.5	323.5	321.1	320.1
15°	370.2	366.2	355.3	342.4	329.9	320.5	315.1	312.6	311.6
17.5°	370.2	364.7	351.8	335.5	320.5	309.1	303.6	301.2	300.7
20°	365.7	359.7	343.9	324.5	307.6	294.7	289.8	288.2	287.3
22.5°	357.2	350.3	332.4	310.7	292.3	279.9	274.4	273.4	272.4
25°	346.4	339.4	319.1	295.7	276.3	264.0	259.5	258.6	258.0
27.5°	332.4	325.1	303.6	279.9	259.0	247.1	243.1	243.1	242.7
30°	314.6	306.1	285.3	261.5	240.6	229.8	226.7	226.7	226.3
32.5°	292.8	284.3	265.5	242.7	222.7	211.4	208.9	209.9	209.4
35°	267.5	260.5	243.1	220.8	203.5	193.1	192.0	193.1	193.1
37.5°	242.1	235.7	220.8	201.4	185.1	175.6	175.6	177.1	176.6
40°	215.8	210.9	197.0	180.1	166.8	160.3	159.3	160.8	161.2
42.5°	191.0	187.1	175.2	161.2	149.3	142.9	144.3	145.4	145.9
45°	168.7	164.7	155.3	140.9	132.4	128.0	128.0	129.5	129.0
47.5°	148.9	145.9	136.4	122.6	115.1	113.2	114.1	115.1	115.1
50°	131.5	127.0	118.1	107.2	101.7	99.3	100.3	100.7	100.7
52.5°	115.1	112.2	103.2	93.2	88.4	86.8	86.8	87.4	87.4
55°	101.7	98.2	90.3	80.3	76.4	74.4	73.0	72.4	73.4
57.5°	88.8	85.9	78.4	69.0	64.5	62.5	59.6	58.6	59.6
60°	77.4	74.9	67.5	58.6	54.0	50.1	46.7	44.6	45.7
62.5°	67.5	64.5	57.1	49.6	44.6	40.2	34.8	31.7	33.2
65°	57.6	55.1	47.6	40.2	35.2	29.8	23.3	21.3	21.3
67.5°	48.6	46.1	39.2	32.7	26.7	20.4	14.4	13.9	14.4
70°	40.2	37.7	31.7	25.3	18.8	12.3	8.4	8.4	8.4
72.5°	33.2	30.3	24.8	18.4	11.9	6.5	4.4	5.0	5.0
75°	25.8	23.3	18.4	12.3	6.9	2.9	2.5	2.5	2.5
77.5°	19.4	17.3	12.9	7.9	3.5	1.0	1.0	1.0	1.0
80°	13.4	11.4	8.4	5.0	2.0	1.0	1.0	1.0	1.0
82.5°	7.9	6.9	5.0	2.5	1.0	0.5	0.5	0.5	0.5
85°	4.0	3.5	2.0	1.0	0.5	0.5	0.5	0.5	0.5
87.5°	1.0	1.0	0.5	0.5	0.0	0.5	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)