

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583876

Luminaire Tested: **HCC8S15D010BZ-HM80520835-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010BZ-HM80520835-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1759.9 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583876
CATALOG NUMBER: HCC8S15D010BZ-HM80520835-81WDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583876

CATALOG NUMBER: HCC8S15D010BZ-HM80520835-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																																				
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																																				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																																				
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																																				
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																																				
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57																																				
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52																																				
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																																				
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44																																				
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40291
5°	39380
10°	38172
15°	37399
20°	37068
25°	36511
30°	34588
35°	28738
40°	16923
45°	11194
50°	8808
55°	6484
60°	4502
65°	2743
70°	1199
75°	536
80°	391
85°	0



TEST NUMBER: P583876
 CATALOG NUMBER: HCC8S15D010BZ-HM80520835-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.8	6.8
10°-20°	331.2	18.8
20°-30°	490.7	27.9
30°-40°	453.5	25.8
40°-50°	209.1	11.9
50°-60°	110.0	6.2
60°-70°	38.9	2.2
70°-80°	6.1	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	941.7	53.5
0°-40°	1395.2	79.3
0°-60°	1714.3	97.4
0°-90°	1759.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1759.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1307	
5°	1272	120
15°	1172	331
25°	1073	491
35°	763	453
45°	257	209
55°	121	110
65°	38	39
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P583876

CATALOG NUMBER: HCC8S15D010BZ-HM80520835-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1306.6
2.5°	1295.5
5°	1272.2
7.5°	1246.8
10°	1219.1
12.5°	1192.6
15°	1171.5
17.5°	1152.7
20°	1129.6
22.5°	1104.0
25°	1073.1
27.5°	1031.1
30°	971.4
32.5°	886.2
35°	763.4
37.5°	586.4
40°	420.4
42.5°	315.3
45°	256.7
47.5°	218.0
50°	183.6
52.5°	150.5
55°	120.6
57.5°	95.2
60°	73.0
62.5°	55.3
65°	37.6
67.5°	22.2
70°	13.3
72.5°	7.7
75°	4.5
77.5°	3.4
80°	2.2
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)