

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583402

Luminaire Tested: **HCC6S07D010SL-HM60525935-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S07D010SL-HM60525935-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 789.2 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583402
CATALOG NUMBER: HCC6S07D010SL-HM60525935-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583402

CATALOG NUMBER: HCC6S07D010SL-HM60525935-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23227	23227	23227
5°	24263	23156	22089
10°	24916	22762	20763
15°	25534	22270	19450
20°	25646	21259	17863
25°	25108	19900	16386
30°	23826	18300	15021
35°	21643	16443	13472
40°	18850	14649	12123
45°	16312	12823	10652
50°	14251	11036	9330
55°	12597	9701	8009
60°	11315	8497	6940
65°	10144	7394	6732
70°	9040	6299	6299
75°	7837	5295	5931
80°	6282	4514	5398
85°	4277	3900	4655



TEST NUMBER: P583402
 CATALOG NUMBER: HCC6S07D010SL-HM60525935-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.8	5.0
10°-20°	110.7	14.0
20°-30°	154.3	19.5
30°-40°	158.9	20.1
40°-50°	131.7	16.7
50°-60°	94.7	12.0
60°-70°	60.3	7.6
70°-80°	31.0	3.9
80°-90°	7.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.8	38.6
0°-40°	463.7	58.8
0°-60°	690.1	87.4
0°-90°	789.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	789.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	424	424	424	424	424	
5°	441	434	421	407	401	42
15°	450	433	392	356	343	127
25°	415	387	329	287	271	190
35°	323	297	246	213	201	201
45°	210	196	165	144	137	163
55°	132	121	102	90	84	119
65°	78	70	57	50	52	78
75°	37	32	25	26	28	40
85°	7	6	6	7	7	9
90°	0	0	0	0	0	



TEST NUMBER: P583402

CATALOG NUMBER: HCC6S07D010SL-HM60525935-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	423.7	423.7	423.7	423.7	423.7	423.7	423.7	423.7	423.7
2.5°	431.7	430.0	427.7	425.4	421.9	418.0	414.6	413.4	411.7
5°	440.9	438.5	433.9	428.3	420.8	413.4	407.2	403.1	401.4
7.5°	446.5	443.7	437.3	427.7	416.8	406.1	396.9	391.2	389.0
10°	447.6	444.8	436.2	423.1	408.9	394.1	382.6	375.8	373.0
12.5°	449.3	445.4	434.5	419.1	400.9	383.7	369.5	361.0	358.1
15°	449.9	445.4	432.8	414.0	392.4	371.9	356.4	346.1	342.7
17.5°	447.6	442.5	427.7	404.8	380.3	358.7	340.5	329.6	325.1
20°	439.6	433.9	416.8	391.2	364.4	341.6	322.8	311.3	306.2
22.5°	429.4	421.9	402.6	375.2	347.3	323.4	304.6	293.1	288.0
25°	415.1	408.3	386.6	357.6	329.0	304.0	286.9	274.9	270.9
27.5°	398.6	390.7	368.3	339.3	310.2	285.2	268.6	257.8	252.7
30°	376.4	368.9	346.7	317.6	289.1	265.7	248.6	239.5	237.3
32.5°	350.1	343.9	322.2	294.8	267.4	245.7	231.5	221.8	219.6
35°	323.4	315.9	297.1	271.5	245.7	226.4	213.2	204.7	201.3
37.5°	294.2	287.4	271.5	248.6	225.8	207.6	196.1	188.8	185.4
40°	263.4	258.3	243.5	225.2	204.7	188.8	179.0	172.8	169.4
42.5°	235.0	229.8	219.6	202.5	185.4	171.1	162.5	156.8	154.0
45°	210.4	205.9	195.6	180.7	165.4	153.4	144.2	140.3	137.4
47.5°	185.9	183.7	174.5	160.8	146.5	136.3	130.1	125.4	123.2
50°	167.1	164.3	155.7	141.4	129.4	121.5	115.8	111.7	109.4
52.5°	147.7	144.8	136.9	124.9	115.2	107.7	102.1	98.7	96.4
55°	131.8	129.4	120.9	110.0	101.5	95.3	90.1	86.1	83.8
57.5°	116.9	114.7	106.6	96.4	88.9	83.3	78.7	75.2	72.4
60°	103.2	101.5	93.5	83.8	77.5	71.8	67.9	65.0	63.3
62.5°	91.2	87.8	81.0	72.4	66.7	62.2	58.1	56.4	57.6
65°	78.2	76.4	69.6	62.2	57.0	52.5	49.6	50.8	51.9
67.5°	67.3	65.0	59.3	52.5	47.9	44.5	42.7	45.1	45.7
70°	56.4	54.2	49.1	43.4	39.3	37.0	37.0	38.7	39.3
72.5°	46.2	44.5	39.9	35.3	32.5	30.8	32.0	33.1	33.7
75°	37.0	35.3	32.0	28.0	25.0	25.0	26.3	27.4	28.0
77.5°	28.6	27.4	23.9	21.1	19.9	19.9	21.1	21.6	22.2
80°	19.9	18.8	17.1	15.4	14.3	15.4	16.5	16.5	17.1
82.5°	13.1	12.6	11.4	10.3	10.3	10.9	11.4	12.0	12.0
85°	6.8	6.8	6.2	5.7	6.2	6.8	6.8	7.4	7.4
87.5°	2.3	2.3	2.3	2.3	2.8	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)