

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583394

Luminaire Tested: **HCC6W07D010MW-HM60525935-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W07D010MW-HM60525935-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 849.7 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583394
CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583394

CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23074	23074	23074
5°	23195	23316	23316
10°	23842	23430	23335
15°	24597	23559	23559
20°	24887	23020	23557
25°	24389	21866	22901
30°	23067	20326	21516
35°	20873	18585	19501
40°	18163	16817	17461
45°	15521	14986	15521
50°	13611	13134	13663
55°	11880	11068	11498
60°	10515	9188	9067
65°	9314	7251	6213
70°	8223	5129	3735
75°	7011	2902	1822
80°	5209	884	537
85°	2830	377	377



TEST NUMBER: P583394
 CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	4.8
10°-20°	118.1	13.9
20°-30°	172.5	20.3
30°-40°	180.9	21.3
40°-50°	152.4	17.9
50°-60°	106.8	12.6
60°-70°	57.3	6.7
70°-80°	19.2	2.3
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.0	39.0
0°-40°	511.9	60.2
0°-60°	771.1	90.8
0°-90°	849.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	849.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	421	421	421	421	421	
5°	422	423	424	424	424	41
15°	433	428	415	413	415	122
25°	403	386	362	368	379	185
35°	312	296	278	286	291	194
45°	200	197	193	198	200	156
55°	124	120	116	118	120	112
65°	72	66	56	46	48	72
75°	33	26	14	9	9	35
85°	4	2	1	1	1	6
90°	0	0	0	0	0	



TEST NUMBER: P583394

CATALOG NUMBER: HCC6W07D010MW-HM60525935-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	420.9	420.9	420.9	420.9	420.9	420.9	420.9	420.9	420.9
2.5°	418.0	418.0	419.2	420.3	421.5	421.5	422.0	422.6	422.0
5°	421.5	421.5	423.2	423.7	423.7	423.2	423.7	423.7	423.7
7.5°	426.6	425.4	426.0	424.9	423.7	423.2	422.6	422.6	422.6
10°	428.3	427.1	426.0	423.7	420.9	419.2	418.6	419.2	419.2
12.5°	430.5	429.4	426.6	422.0	418.6	415.7	415.1	416.3	416.3
15°	433.4	432.2	427.7	420.3	415.1	412.3	412.9	414.0	415.1
17.5°	433.4	431.1	423.7	414.0	407.8	404.9	407.2	410.0	411.7
20°	426.6	424.3	414.0	402.1	394.6	392.9	396.9	402.1	403.8
22.5°	417.4	412.9	400.9	386.7	378.6	378.6	384.4	390.7	392.9
25°	403.2	399.7	386.1	369.6	361.5	361.0	367.9	376.4	378.6
27.5°	387.3	382.6	367.9	350.8	342.2	342.7	350.2	358.7	361.0
30°	364.4	358.7	345.6	329.0	321.1	323.4	330.7	337.1	339.9
32.5°	338.8	333.7	321.7	306.2	299.5	301.7	307.9	313.6	316.0
35°	311.9	306.2	295.9	282.3	277.7	280.0	285.7	290.3	291.4
37.5°	281.8	277.7	270.3	259.5	256.1	258.9	263.4	266.4	267.5
40°	253.8	250.4	244.0	236.1	235.0	237.3	241.8	243.5	244.0
42.5°	226.4	223.5	219.6	213.9	213.9	216.2	220.1	221.3	221.8
45°	200.2	198.5	196.8	192.2	193.3	196.1	198.5	200.2	200.2
47.5°	177.3	177.9	175.6	172.2	173.3	176.2	177.9	179.7	179.7
50°	159.6	157.9	155.7	152.3	154.0	156.2	158.5	159.6	160.2
52.5°	139.1	138.6	136.9	132.9	134.0	135.2	137.4	139.1	139.7
55°	124.3	122.6	120.3	115.8	115.8	116.9	118.1	119.2	120.3
57.5°	110.0	108.3	104.9	99.8	99.3	99.3	98.7	99.8	101.5
60°	95.9	95.3	90.1	85.5	83.8	82.1	79.9	80.4	82.7
62.5°	83.3	82.1	77.6	71.8	68.4	65.6	62.8	62.2	64.5
65°	71.8	70.7	65.6	59.9	55.9	50.8	46.2	46.2	47.9
67.5°	61.6	59.3	54.7	48.5	43.4	37.0	32.5	33.7	34.2
70°	51.3	49.6	44.5	38.2	32.0	25.7	22.8	23.3	23.3
72.5°	42.1	39.9	34.8	28.6	22.2	16.5	15.4	14.8	14.8
75°	33.1	30.8	25.7	19.4	13.7	9.7	8.6	8.6	8.6
77.5°	23.9	22.2	17.7	12.0	7.4	4.5	4.0	3.4	3.4
80°	16.5	14.8	10.9	6.2	2.8	1.7	1.7	1.7	1.7
82.5°	9.7	7.9	5.1	2.8	1.1	0.6	0.6	0.6	0.6
85°	4.5	3.4	2.3	1.1	0.6	0.6	0.6	0.6	0.6
87.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)