

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583393

Luminaire Tested: **HCC6S07D010MB-HM60525935-61PSMDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583393  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S07D010MB-HM60525935-61PSMDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 807.5 lumens  
Efficiency: N/A  
Efficacy: 100.9 lumens/watt  
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583393  
CATALOG NUMBER: HCC6S07D010MB-HM60525935-61PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583393  
 CATALOG NUMBER: HCC6S07D010MB-HM60525935-61PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78																			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69																			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51																			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43																			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39																			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	28863
5°	28786
10°	28356
15°	27906
20°	26987
25°	25707
30°	23466
35°	18892
40°	12738
45°	9288
50°	8034
55°	7254
60°	6885
65°	6512
70°	6123
75°	5804
80°	5398
85°	4969



TEST NUMBER: P583393  
 CATALOG NUMBER: HCC6S07D010MB-HM60525935-61PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.5	6.1
10°-20°	138.1	17.1
20°-30°	194.0	24.0
30°-40°	172.7	21.4
40°-50°	96.5	12.0
50°-60°	68.8	8.5
60°-70°	50.0	6.2
70°-80°	28.9	3.6
80°-90°	9.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.6	47.3
0°-40°	554.3	68.6
0°-60°	719.6	89.1
0°-90°	807.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	526	
5°	523	50
15°	492	138
25°	425	194
35°	282	173
45°	120	97
55°	76	69
65°	50	50
75°	27	29
85°	8	9
90°	0	



TEST NUMBER: P583393  
CATALOG NUMBER: HCC6S07D010MB-HM60525935-61PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	526.5
2.5°	524.2
5°	523.1
7.5°	518.5
10°	509.4
12.5°	500.8
15°	491.7
17.5°	479.1
20°	462.6
22.5°	444.4
25°	425.0
27.5°	401.0
30°	370.7
32.5°	332.0
35°	282.3
37.5°	226.5
40°	178.0
42.5°	142.1
45°	119.8
47.5°	104.9
50°	94.2
52.5°	84.4
55°	75.9
57.5°	69.0
60°	62.8
62.5°	57.0
65°	50.2
67.5°	44.5
70°	38.2
72.5°	32.5
75°	27.4
77.5°	22.2
80°	17.1
82.5°	12.6
85°	7.9
87.5°	4.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)