

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583907

Luminaire Tested: **HCC8S15D010MW-HM80520927-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010MW-HM80520927-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1201.2 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583907
CATALOG NUMBER: HCC8S15D010MW-HM80520927-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P583907

CATALOG NUMBER: HCC8S15D010MW-HM80520927-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	19760	19760	19760
5°	20129	19671	19216
10°	20447	19329	18515
15°	20649	18848	17711
20°	20569	18124	16897
25°	20027	17077	15954
30°	19075	15827	15026
35°	17222	14448	13958
40°	15135	12966	12934
45°	13065	11399	11892
50°	11370	9993	10664
55°	10080	8682	9290
60°	8998	7333	7715
65°	8106	5954	6085
70°	7204	4463	3597
75°	6207	2585	1549
80°	4777	923	479
85°	3078	283	283



TEST NUMBER: P583907
 CATALOG NUMBER: HCC8S15D010MW-HM80520927-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.2	5.0
10°-20°	167.5	13.9
20°-30°	236.8	19.7
30°-40°	249.6	20.8
40°-50°	212.1	17.7
50°-60°	152.7	12.7
60°-70°	88.1	7.3
70°-80°	30.1	2.5
80°-90°	4.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	464.5	38.7
0°-40°	714.0	59.4
0°-60°	1078.9	89.8
0°-90°	1201.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1201.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	641	641	641	641	641	
5°	650	646	636	624	621	62
15°	647	627	590	564	555	182
25°	589	558	502	476	469	270
35°	458	431	384	370	371	285
45°	300	286	261	263	273	233
55°	188	173	162	168	173	169
65°	111	96	82	80	83	111
75°	52	39	22	14	13	55
85°	9	5	1	1	1	12
90°	0	0	0	0	0	



TEST NUMBER: P583907

CATALOG NUMBER: HCC8S15D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	640.8	640.8	640.8	640.8	640.8	640.8	640.8	640.8	640.8	640.8	640.8
2.5°	646.8	647.7	646.8	646.8	646.0	645.2	644.2	643.3	641.7	639.9	639.9
5°	650.3	652.0	650.3	650.3	647.7	646.0	644.2	641.7	638.2	635.5	635.5
7.5°	653.0	653.0	653.0	650.3	648.5	646.0	641.7	637.3	633.0	628.6	626.8
10°	653.0	653.0	652.0	648.5	646.8	641.7	637.3	631.2	625.2	619.1	617.3
12.5°	650.3	651.2	649.5	646.0	641.7	635.5	629.5	621.7	614.7	607.8	604.3
15°	646.8	646.0	644.2	639.9	634.7	626.8	620.8	612.1	602.6	593.9	590.4
17.5°	638.2	638.2	635.5	631.2	624.3	615.6	606.0	596.5	586.1	576.5	572.1
20°	626.8	626.8	623.5	618.2	611.3	600.0	589.6	578.3	566.1	556.6	552.3
22.5°	610.3	611.3	607.0	600.8	593.0	580.0	569.6	555.7	543.6	532.2	528.8
25°	588.6	590.4	586.1	580.0	569.6	558.3	545.3	532.2	518.4	507.1	501.9
27.5°	563.5	564.4	560.1	553.9	543.6	531.4	518.4	504.4	491.4	479.2	474.0
30°	535.7	532.2	530.6	522.7	511.4	501.0	486.2	474.9	461.0	450.7	444.5
32.5°	496.7	498.4	493.2	487.1	478.4	466.2	454.0	441.0	428.0	420.2	415.8
35°	457.5	459.3	456.7	450.7	441.0	430.7	418.5	409.0	397.7	388.1	383.8
37.5°	416.8	416.8	415.0	411.5	404.6	395.0	382.9	373.3	363.8	356.0	353.4
40°	376.0	374.3	373.3	370.8	364.6	356.0	348.1	340.4	330.8	325.6	322.1
42.5°	336.1	336.1	334.3	331.6	325.6	321.3	313.4	304.7	297.8	292.6	292.6
45°	299.6	300.4	297.8	296.1	292.6	285.7	278.7	272.7	266.5	263.1	261.4
47.5°	267.4	267.4	264.9	263.1	259.6	253.5	247.5	242.2	237.9	235.3	234.4
50°	237.0	237.0	237.0	232.7	228.3	224.0	219.7	213.6	211.0	209.3	208.3
52.5°	211.0	210.2	210.2	206.7	202.3	197.1	192.8	187.5	185.0	183.2	184.1
55°	187.5	187.5	186.7	182.3	178.0	172.8	168.5	164.1	162.3	160.6	161.5
56°	178.0	178.0	177.1	173.6	168.5	164.1	158.9	154.6	152.0	152.8	152.8
57°	171.0	169.3	169.3	165.0	160.6	154.6	150.3	145.9	144.1	143.3	143.3
58°	162.3	161.5	160.6	156.3	152.0	146.8	142.4	138.1	135.4	135.4	134.6
59°	153.6	153.6	152.0	148.5	144.1	138.9	134.6	130.3	127.6	126.8	126.8
60°	145.9	146.8	144.1	140.6	137.1	131.1	125.9	122.4	119.8	118.9	118.9
61°	138.9	138.9	137.1	132.8	128.5	124.1	118.9	114.6	112.9	111.1	111.1
62°	132.8	131.1	130.3	125.9	121.6	116.4	112.1	107.6	105.1	103.3	104.2
63°	125.1	124.1	122.4	118.9	114.6	109.4	104.2	100.7	98.1	95.6	96.4
64°	118.9	118.1	115.4	112.1	107.6	102.4	97.2	93.7	92.1	89.4	88.6
65°	111.1	110.3	109.4	105.1	100.7	95.6	91.2	87.7	85.1	83.4	81.6
66°	104.2	105.1	103.3	99.9	94.6	90.3	84.2	80.7	79.0	76.4	74.7
67°	98.1	98.1	96.4	92.9	87.7	83.4	79.0	74.7	72.1	69.4	68.6
67.5°	94.6	94.6	92.9	88.6	85.1	79.9	75.6	72.1	68.6	66.9	65.1
68°	91.2	91.2	90.3	86.9	82.5	77.2	72.9	68.6	65.1	62.5	61.7
69°	85.1	85.9	84.2	80.7	76.4	71.2	66.9	63.4	59.9	57.4	55.6
70°	79.9	79.0	77.2	73.7	69.4	66.0	61.7	57.4	53.9	50.4	49.5
71°	72.9	72.9	71.2	68.6	64.2	59.9	55.6	52.1	48.7	44.2	43.4
72°	67.7	67.7	66.0	62.5	59.0	54.7	50.4	46.0	43.4	39.0	37.4
72.5°	64.2	65.1	63.4	59.9	56.4	51.2	47.7	44.2	39.9	36.5	34.7
73°	62.5	61.7	60.7	57.4	53.0	49.5	45.2	41.7	37.4	33.9	32.2



TEST NUMBER: P583907
 CATALOG NUMBER: HCC8S15D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	39.0	39.0	38.2	34.7	31.2	27.8	24.3	20.8	17.4	13.9	12.2
80°	26.9	27.8	26.0	24.3	21.7	18.2	14.7	12.2	8.7	7.0	5.2
82.5°	17.4	17.4	16.5	14.7	13.0	10.4	8.7	6.0	4.3	3.5	2.7
85°	8.7	9.5	8.7	7.8	6.0	5.2	4.3	2.7	1.7	0.8	0.8
87.5°	3.5	3.5	3.5	2.7	2.7	1.7	0.8	0.8	0.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583907

CATALOG NUMBER: HCC8S15D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	640.8	640.8	640.8	640.8	640.8	640.8	640.8	640.8	640.8	640.8
2.5°	638.2	638.2	636.5	635.5	634.7	633.8	633.0	632.1	632.1	633.0
5°	633.0	631.2	627.8	626.8	624.3	623.5	621.7	620.8	621.7	620.8
7.5°	625.2	621.7	617.3	615.6	612.1	610.3	607.8	607.8	606.0	607.0
10°	614.7	609.5	604.3	600.8	598.3	595.6	593.9	592.1	591.3	591.3
12.5°	601.7	595.6	590.4	585.1	580.8	579.1	575.6	575.6	573.9	573.1
15°	587.0	579.1	573.1	567.8	564.4	560.9	558.3	556.6	554.8	554.8
17.5°	567.8	560.9	554.8	548.8	543.6	540.9	538.3	535.7	535.7	533.9
20°	546.9	539.2	533.9	527.9	523.6	519.2	515.7	515.7	514.1	514.9
22.5°	523.6	514.1	508.8	504.4	500.1	496.7	493.2	493.2	492.4	491.4
25°	497.5	489.7	483.6	478.4	475.9	472.4	471.5	469.7	468.9	468.9
27.5°	469.7	463.7	455.9	453.2	449.7	448.0	448.0	447.2	445.4	446.3
30°	440.2	433.3	429.0	427.2	423.7	423.7	422.8	421.1	421.1	422.0
32.5°	411.5	404.6	401.1	400.3	396.8	396.8	396.0	396.8	396.8	397.7
35°	380.3	374.3	373.3	370.8	369.9	369.9	369.9	371.6	373.3	370.8
37.5°	350.8	346.4	343.8	342.9	343.8	343.8	344.8	347.3	346.4	345.6
40°	320.4	316.9	315.2	315.2	316.9	318.6	318.6	321.3	322.1	321.3
42.5°	290.0	287.4	287.4	288.2	290.0	290.9	293.4	296.1	296.9	297.8
45°	261.4	261.4	261.4	262.2	263.1	264.9	268.2	270.9	271.7	272.7
47.5°	233.5	232.7	235.3	236.2	238.8	239.7	242.2	245.7	246.5	247.5
50°	207.5	209.3	210.2	212.7	214.5	214.5	218.0	219.7	222.3	222.3
52.5°	183.2	185.8	186.7	189.3	190.1	191.0	192.8	195.3	197.1	197.1
55°	161.5	162.3	164.1	165.0	167.6	168.5	170.1	171.0	173.6	172.8
56°	152.0	153.6	154.6	156.3	158.0	158.9	160.6	161.5	163.3	164.1
57°	143.3	144.1	146.8	147.6	149.3	149.3	150.3	152.8	152.8	153.6
58°	134.6	136.3	137.1	138.1	139.8	140.6	142.4	143.3	144.1	143.3
59°	126.8	127.6	128.5	128.5	130.3	130.3	132.8	134.6	135.4	135.4
60°	118.9	118.9	119.8	120.7	122.4	123.3	123.3	125.1	125.1	125.1
61°	111.1	111.1	112.1	112.9	113.8	113.8	115.4	115.4	116.4	117.2
62°	104.2	103.3	103.3	104.2	104.2	105.9	106.8	107.6	108.6	107.6
63°	96.4	95.6	95.6	95.6	95.6	97.2	97.2	98.1	99.9	98.9
64°	87.7	87.7	87.7	87.7	88.6	88.6	90.3	91.2	92.1	92.9
65°	81.6	79.9	79.0	79.0	79.9	80.7	81.6	82.5	83.4	83.4
66°	74.7	72.9	72.1	72.1	72.1	72.1	73.7	73.7	75.6	75.6
67°	66.9	65.1	64.2	63.4	63.4	63.4	66.0	65.1	65.1	65.1
67.5°	64.2	61.7	60.7	59.9	59.0	60.7	59.9	60.7	60.7	59.9
68°	60.7	59.0	57.4	55.6	55.6	55.6	56.4	57.4	56.4	55.6
69°	53.9	53.0	50.4	48.7	47.7	48.7	47.7	48.7	47.7	48.7
70°	47.7	45.2	42.5	41.7	40.8	40.8	40.8	39.9	40.8	39.9
71°	41.7	39.0	36.5	34.7	33.9	33.9	33.0	33.9	33.0	33.9
72°	35.5	33.0	29.5	27.8	27.8	27.8	27.8	26.9	27.8	26.9
72.5°	33.0	29.5	26.9	25.2	24.3	24.3	24.3	24.3	23.5	24.3
73°	30.4	26.9	23.5	22.5	22.5	22.5	21.7	20.8	21.7	21.7



TEST NUMBER: P583907
CATALOG NUMBER: HCC8S15D010MW-HM80520927-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	10.4	7.8	7.0	7.0	7.0	7.0	7.0	7.0	6.0	6.0
80°	4.3	3.5	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	56.4	56.4	54.7	52.1	47.7	43.4	39.9	36.5	32.2	27.8	26.0
75°	52.1	51.2	49.5	46.9	43.4	39.0	35.5	31.2	27.8	23.5	21.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	25.2	20.8	19.2	17.4	17.4	17.4	16.5	16.5	16.5	17.4
75°	20.0	16.5	14.7	13.0	13.9	13.0	13.9	13.0	13.0	13.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)