

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583920

Luminaire Tested: **HCC8W15D010MB-HM80520930-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583920  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010MB-HM80520930-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1301.6 lumens  
Efficiency: N/A  
Efficacy: 93.0 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583920  
CATALOG NUMBER: HCC8W15D010MB-HM80520930-81NDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583920

CATALOG NUMBER: HCC8W15D010MB-HM80520930-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	114	112	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	94	93	92	91	90	89	89	89	89																
	2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89	89	89	89	89	89	89	89	89															
	3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84	84	84	84	84	84	84	84	84															
	4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80	80	80	80	80	80	80	80	80															
	5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75	75	75	75	75	75	75	75	75															
	6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72	72	72	72	72	72	72	72	72															
	7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68	68	68	68	68	68	68	68	68															
	8	84	76	70	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65	65	65	65	65	65	65	65	65															
	9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62	62	62	62	62	62	62	62	62															
	10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59	59	59	59	59	59	59	59	59															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	103564
5°	87739
10°	63660
15°	47806
20°	37718
25°	30424
30°	22546
35°	9136
40°	3852
45°	2067
50°	926
55°	468
60°	296
65°	212
70°	171
75°	119
80°	178
85°	354



TEST NUMBER: P583920  
 CATALOG NUMBER: HCC8W15D010MB-HM80520930-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	243.4	18.7
10°-20°	420.6	32.3
20°-30°	406.6	31.2
30°-40°	178.6	13.7
40°-50°	38.6	3.0
50°-60°	8.6	0.7
60°-70°	3.0	0.2
70°-80°	1.2	0.1
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1070.6	82.3
0°-40°	1249.2	96.0
0°-60°	1296.5	99.6
0°-90°	1301.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1301.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3358	
5°	2834	243
15°	1498	421
25°	894	407
35°	243	179
45°	47	39
55°	9	9
65°	3	3
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P583920  
CATALOG NUMBER: HCC8W15D010MB-HM80520930-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3358.5
1°	3333.3
2°	3264.7
3°	3141.0
4°	2993.0
5°	2834.5
6°	2661.4
7°	2487.4
8°	2324.1
9°	2172.3
10°	2033.1
11°	1901.6
12°	1783.6
13°	1676.3
14°	1581.6
15°	1497.5
17.5°	1309.0
20°	1149.4
22.5°	1009.3
25°	894.2
27.5°	777.2
30°	633.2
32.5°	430.2
35°	242.7
37.5°	143.0
40°	95.7
42.5°	67.7
45°	47.4
47.5°	31.0
50°	19.3
52.5°	11.6
55°	8.7
57.5°	6.7
60°	4.8
62.5°	3.9
65°	2.9
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P583920  
CATALOG NUMBER: HCC8W15D010MB-HM80520930-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°		1.0
87.5°		1.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)