

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583703

Luminaire Tested: **HCC8W10D010MB-HM80520827-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010MB-HM80520827-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1077.8 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583703
CATALOG NUMBER: HCC8W10D010MB-HM80520827-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583703

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17728	17728	17728
5°	18062	17650	17241
10°	18346	17344	16614
15°	18526	16910	15889
20°	18455	16260	15157
25°	17972	15321	14314
30°	17116	14200	13481
35°	15457	12965	12520
40°	13578	11637	11601
45°	11722	10226	10667
50°	10199	8966	9566
55°	9048	7785	8338
60°	8073	6580	6914
65°	7282	5341	5458
70°	6455	4003	3228
75°	5576	2323	1394
80°	4297	835	408
85°	2760	248	248



TEST NUMBER: P583703
 CATALOG NUMBER: HCC8W10D010MB-HM80520827-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	5.0
10°-20°	150.2	13.9
20°-30°	212.5	19.7
30°-40°	223.9	20.8
40°-50°	190.3	17.7
50°-60°	137.0	12.7
60°-70°	79.1	7.3
70°-80°	27.1	2.5
80°-90°	3.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	416.7	38.7
0°-40°	640.6	59.4
0°-60°	968.0	89.8
0°-90°	1077.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1077.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	575	575	575	575	575	
5°	584	580	570	560	557	56
15°	580	562	530	506	498	163
25°	528	501	450	427	421	242
35°	411	386	344	332	333	256
45°	269	256	234	236	245	209
55°	168	155	145	150	155	151
65°	100	86	73	72	75	99
75°	47	35	20	12	12	49
85°	8	5	1	1	1	10
90°	0	0	0	0	0	



TEST NUMBER: P583703

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	574.9	574.9	574.9	574.9	574.9	574.9	574.9	574.9	574.9	574.9	574.9
2.5°	580.3	581.2	580.3	580.3	579.6	578.8	578.0	577.3	575.8	574.2	574.2
5°	583.5	585.0	583.5	583.5	581.2	579.6	578.0	575.8	572.6	570.2	570.2
7.5°	585.9	585.9	585.9	583.5	581.9	579.6	575.8	571.8	567.9	564.0	562.4
10°	585.9	585.9	585.0	581.9	580.3	575.8	571.8	566.4	560.9	555.4	553.9
12.5°	583.5	584.3	582.7	579.6	575.8	570.2	564.8	557.8	551.6	545.3	542.2
15°	580.3	579.6	578.0	574.2	569.5	562.4	557.0	549.2	540.7	532.8	529.7
17.5°	572.6	572.6	570.2	566.4	560.1	552.3	543.8	535.3	525.9	517.2	513.4
20°	562.4	562.4	559.3	554.7	548.5	538.3	529.0	518.8	508.0	499.3	495.5
22.5°	547.6	548.5	544.5	539.1	532.1	520.3	511.1	498.6	487.7	477.6	474.4
25°	528.2	529.7	525.9	520.3	511.1	500.9	489.2	477.6	465.1	455.0	450.3
27.5°	505.6	506.4	502.4	497.0	487.7	476.7	465.1	452.7	440.9	430.1	425.4
30°	480.7	477.6	476.0	469.0	458.8	449.5	436.2	426.1	413.6	404.4	398.8
32.5°	445.6	447.1	442.5	437.0	429.2	418.3	407.5	395.7	384.0	377.1	373.1
35°	410.6	412.2	409.8	404.4	395.7	386.4	375.5	367.0	356.8	348.2	344.4
37.5°	373.9	373.9	372.4	369.3	363.0	354.5	343.5	335.0	326.5	319.4	317.1
40°	337.3	335.7	335.0	332.6	327.2	319.4	312.4	305.4	296.8	292.1	289.1
42.5°	301.5	301.5	299.9	297.6	292.1	288.2	281.3	273.5	267.2	262.5	262.5
45°	268.8	269.5	267.2	265.6	262.5	256.3	250.0	244.6	239.2	236.1	234.5
47.5°	239.9	239.9	237.6	236.1	232.9	227.4	222.0	217.3	213.5	211.1	210.4
50°	212.6	212.6	212.6	208.8	204.9	201.0	197.1	191.6	189.3	187.8	186.9
52.5°	189.3	188.5	188.5	185.5	181.5	176.8	173.0	168.3	165.9	164.4	165.2
55°	168.3	168.3	167.4	163.6	159.7	155.1	151.1	147.2	145.7	144.1	144.8
56°	159.7	159.7	158.9	155.8	151.1	147.2	142.6	138.7	136.3	137.1	137.1
57°	153.5	151.9	151.9	148.0	144.1	138.7	134.7	130.9	129.3	128.5	128.5
58°	145.7	144.8	144.1	140.3	136.3	131.6	127.8	123.9	121.5	121.5	120.8
59°	137.9	137.9	136.3	133.2	129.3	124.6	120.8	116.8	114.6	113.7	113.7
60°	130.9	131.6	129.3	126.2	123.1	117.7	113.0	109.9	107.5	106.7	106.7
61°	124.6	124.6	123.1	119.2	115.3	111.4	106.7	102.9	101.3	99.8	99.8
62°	119.2	117.7	116.8	113.0	109.0	104.3	100.5	96.6	94.2	92.7	93.5
63°	112.1	111.4	109.9	106.7	102.9	98.2	93.5	90.4	88.0	85.7	86.4
64°	106.7	105.9	103.6	100.5	96.6	92.0	87.3	84.1	82.6	80.3	79.5
65°	99.8	98.9	98.2	94.2	90.4	85.7	81.9	78.7	76.3	74.8	73.2
66°	93.5	94.2	92.7	89.5	84.9	81.0	75.6	72.5	70.9	68.5	67.0
67°	88.0	88.0	86.4	83.3	78.7	74.8	70.9	67.0	64.7	62.3	61.5
67.5°	84.9	84.9	83.3	79.5	76.3	71.6	67.8	64.7	61.5	60.0	58.4
68°	81.9	81.9	81.0	77.9	74.0	69.4	65.4	61.5	58.4	56.1	55.3
69°	76.3	77.2	75.6	72.5	68.5	63.8	60.0	56.9	53.7	51.4	49.9
70°	71.6	70.9	69.4	66.2	62.3	59.3	55.3	51.4	48.3	45.2	44.4
71°	65.4	65.4	63.8	61.5	57.7	53.7	49.9	46.8	43.6	39.8	38.9
72°	60.8	60.8	59.3	56.1	53.0	49.0	45.2	41.3	38.9	35.1	33.5
72.5°	57.7	58.4	56.9	53.7	50.6	45.9	42.8	39.8	35.8	32.7	31.1
73°	56.1	55.3	54.6	51.4	47.5	44.4	40.5	37.4	33.5	30.4	28.8



TEST NUMBER: P583703
 CATALOG NUMBER: HCC8W10D010MB-HM80520827-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	35.1	35.1	34.3	31.1	28.0	24.9	21.8	18.8	15.6	12.5	10.9
80°	24.2	24.9	23.3	21.8	19.5	16.3	13.2	10.9	7.8	6.3	4.7
82.5°	15.6	15.6	14.8	13.2	11.7	9.4	7.8	5.4	3.8	3.1	2.3
85°	7.8	8.5	7.8	7.0	5.4	4.7	3.8	2.3	1.6	0.7	0.7
87.5°	3.1	3.1	3.1	2.3	2.3	1.6	0.7	0.7	0.7	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583703

CATALOG NUMBER: HCC8W10D010MB-HM80520827-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	574.9	574.9	574.9	574.9	574.9	574.9	574.9	574.9	574.9	574.9
2.5°	572.6	572.6	571.1	570.2	569.5	568.7	567.9	567.1	567.1	567.9
5°	567.9	566.4	563.3	562.4	560.1	559.3	557.8	557.0	557.8	557.0
7.5°	560.9	557.8	553.9	552.3	549.2	547.6	545.3	545.3	543.8	544.5
10°	551.6	546.9	542.2	539.1	536.8	534.4	532.8	531.3	530.6	530.6
12.5°	539.8	534.4	529.7	525.0	521.2	519.6	516.5	516.5	514.9	514.2
15°	526.6	519.6	514.2	509.5	506.4	503.3	500.9	499.3	497.7	497.7
17.5°	509.5	503.3	497.7	492.3	487.7	485.4	483.0	480.7	480.7	479.1
20°	490.8	483.8	479.1	473.7	469.7	465.9	462.8	462.8	461.2	461.9
22.5°	469.7	461.2	456.5	452.7	448.7	445.6	442.5	442.5	441.7	440.9
25°	446.4	439.3	433.9	429.2	427.0	423.8	423.0	421.4	420.7	420.7
27.5°	421.4	416.0	409.0	406.6	403.5	401.9	401.9	401.2	399.7	400.4
30°	395.0	388.7	384.9	383.3	380.2	380.2	379.4	377.8	377.8	378.6
32.5°	369.3	363.0	359.9	359.2	356.0	356.0	355.2	356.0	356.0	356.8
35°	341.2	335.7	335.0	332.6	331.9	331.9	331.9	333.4	335.0	332.6
37.5°	314.7	310.8	308.6	307.7	308.6	308.6	309.3	311.6	310.8	310.1
40°	287.5	284.4	282.8	282.8	284.4	286.0	286.0	288.2	289.1	288.2
42.5°	260.2	257.8	257.8	258.7	260.2	261.0	263.4	265.6	266.5	267.2
45°	234.5	234.5	234.5	235.2	236.1	237.6	240.8	243.0	243.9	244.6
47.5°	209.5	208.8	211.1	211.9	214.2	215.0	217.3	220.4	221.3	222.0
50°	186.2	187.8	188.5	190.9	192.4	192.4	195.6	197.1	199.4	199.4
52.5°	164.4	166.7	167.4	169.8	170.6	171.4	173.0	175.3	176.8	176.8
55°	144.8	145.7	147.2	148.0	150.4	151.1	152.7	153.5	155.8	155.1
56°	136.3	137.9	138.7	140.3	141.8	142.6	144.1	144.8	146.4	147.2
57°	128.5	129.3	131.6	132.5	134.0	134.0	134.7	137.1	137.1	137.9
58°	120.8	122.4	123.1	123.9	125.4	126.2	127.8	128.5	129.3	128.5
59°	113.7	114.6	115.3	115.3	116.8	116.8	119.2	120.8	121.5	121.5
60°	106.7	106.7	107.5	108.3	109.9	110.6	110.6	112.1	112.1	112.1
61°	99.8	99.8	100.5	101.3	102.0	102.0	103.6	103.6	104.3	105.2
62°	93.5	92.7	92.7	93.5	93.5	95.1	95.8	96.6	97.4	96.6
63°	86.4	85.7	85.7	85.7	85.7	87.3	87.3	88.0	89.5	88.8
64°	78.7	78.7	78.7	78.7	79.5	79.5	81.0	81.9	82.6	83.3
65°	73.2	71.6	70.9	70.9	71.6	72.5	73.2	74.0	74.8	74.8
66°	67.0	65.4	64.7	64.7	64.7	64.7	66.2	66.2	67.8	67.8
67°	60.0	58.4	57.7	56.9	56.9	56.9	59.3	58.4	58.4	58.4
67.5°	57.7	55.3	54.6	53.7	53.0	54.6	53.7	54.6	54.6	53.7
68°	54.6	53.0	51.4	49.9	49.9	49.9	50.6	51.4	50.6	49.9
69°	48.3	47.5	45.2	43.6	42.8	43.6	42.8	43.6	42.8	43.6
70°	42.8	40.5	38.2	37.4	36.7	36.7	36.7	35.8	36.7	35.8
71°	37.4	35.1	32.7	31.1	30.4	30.4	29.6	30.4	29.6	30.4
72°	32.0	29.6	26.4	24.9	24.9	24.9	24.9	24.2	24.9	24.2
72.5°	29.6	26.4	24.2	22.6	21.8	21.8	21.8	21.8	21.0	21.8
73°	27.3	24.2	21.0	20.3	20.3	20.3	19.5	18.8	19.5	19.5



TEST NUMBER: P583703
CATALOG NUMBER: HCC8W10D010MB-HM80520827-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	9.4	7.0	6.3	6.3	6.3	6.3	6.3	6.3	5.4	5.4
80°	3.8	3.1	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	50.6	50.6	49.0	46.8	42.8	38.9	35.8	32.7	28.8	24.9	23.3
75°	46.8	45.9	44.4	42.1	38.9	35.1	32.0	28.0	24.9	21.0	19.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	22.6	18.8	17.2	15.6	15.6	15.6	14.8	14.8	14.8	15.6
75°	17.9	14.8	13.2	11.7	12.5	11.7	12.5	11.7	11.7	11.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)