

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583720

Luminaire Tested: **HCC8W10D010MW-HM80520830-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W10D010MW-HM80520830-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1071.9 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583720
CATALOG NUMBER: HCC8W10D010MW-HM80520830-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P583720

CATALOG NUMBER: HCC8W10D010MW-HM80520830-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77			77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59			59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35			35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17632	17632	17632
5°	17963	17554	17149
10°	18242	17250	16523
15°	18427	16818	15806
20°	18357	16171	15075
25°	17873	15239	14236
30°	17020	14125	13409
35°	15370	12889	12453
40°	13505	11569	11541
45°	11657	10170	10610
50°	10151	8918	9513
55°	8994	7747	8290
60°	8030	6543	6876
65°	7238	5312	5429
70°	6428	3976	3219
75°	5540	2311	1394
80°	4262	835	408
85°	2724	248	248



TEST NUMBER: P583720
 CATALOG NUMBER: HCC8W10D010MW-HM80520830-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	5.0
10°-20°	149.4	13.9
20°-30°	211.3	19.7
30°-40°	222.7	20.8
40°-50°	189.3	17.7
50°-60°	136.3	12.7
60°-70°	78.6	7.3
70°-80°	26.9	2.5
80°-90°	3.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.5	38.7
0°-40°	637.2	59.4
0°-60°	962.7	89.8
0°-90°	1071.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1071.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	572	572	572	572	572	
5°	580	576	567	557	554	55
15°	577	559	527	504	495	163
25°	525	498	448	424	418	241
35°	408	384	342	330	331	254
45°	267	255	233	235	243	208
55°	167	154	144	150	154	151
65°	99	85	73	71	74	99
75°	46	35	19	12	12	49
85°	8	5	1	1	1	10
90°	0	0	0	0	0	



TEST NUMBER: P583720

CATALOG NUMBER: HCC8W10D010MW-HM80520830-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	571.8	571.8	571.8	571.8	571.8	571.8	571.8	571.8	571.8	571.8	571.8
2.5°	577.2	578.0	577.2	577.2	576.5	575.6	574.9	574.2	572.6	571.1	571.1
5°	580.3	581.9	580.3	580.3	578.0	576.5	574.9	572.6	569.5	567.1	567.1
7.5°	582.6	582.6	582.6	580.3	578.8	576.5	572.6	568.7	564.8	561.0	559.4
10°	582.6	582.6	581.9	578.8	577.2	572.6	568.7	563.3	557.8	552.4	550.9
12.5°	580.3	581.2	579.6	576.5	572.6	567.1	561.7	554.7	548.6	542.3	539.2
15°	577.2	576.5	574.9	571.1	566.4	559.4	554.0	546.2	537.8	530.0	526.8
17.5°	569.5	569.5	567.1	563.3	557.1	549.3	540.8	532.2	523.0	514.5	510.6
20°	559.4	559.4	556.3	551.7	545.5	535.4	526.1	516.0	505.2	496.7	492.8
22.5°	544.7	545.5	541.6	536.2	529.2	517.6	508.3	495.8	485.0	474.9	471.9
25°	525.3	526.8	523.0	517.6	508.3	498.2	486.6	474.9	462.5	452.4	447.9
27.5°	502.8	503.6	499.8	494.4	485.0	474.2	462.5	450.1	438.5	427.7	423.1
30°	478.0	474.9	473.5	466.5	456.4	447.0	433.9	423.8	411.4	402.1	396.7
32.5°	443.2	444.7	440.1	434.6	427.0	416.1	405.2	393.7	382.0	375.0	371.2
35°	408.3	409.9	407.6	402.1	393.7	384.3	373.5	364.9	354.8	346.3	342.4
37.5°	371.9	371.9	370.3	367.2	361.1	352.5	341.7	333.2	324.7	317.7	315.4
40°	335.5	333.9	333.2	330.8	325.4	317.7	310.7	303.7	295.2	290.5	287.4
42.5°	299.9	299.9	298.3	295.9	290.5	286.7	279.7	272.0	265.8	261.1	261.1
45°	267.3	268.0	265.8	264.2	261.1	254.9	248.7	243.3	237.9	234.8	233.2
47.5°	238.6	238.6	236.3	234.8	231.6	226.2	220.8	216.1	212.3	210.0	209.1
50°	211.6	211.6	211.6	207.7	203.7	199.9	196.0	190.6	188.2	186.7	185.9
52.5°	188.2	187.5	187.5	184.4	180.5	175.9	172.0	167.3	165.0	163.5	164.3
55°	167.3	167.3	166.6	162.8	158.8	154.2	150.4	146.4	144.8	143.4	144.1
56°	158.8	158.8	158.1	154.9	150.4	146.4	141.8	137.9	135.6	136.4	136.4
57°	152.7	151.1	151.1	147.2	143.4	137.9	134.0	130.2	128.6	127.9	127.9
58°	144.8	144.1	143.4	139.4	135.6	130.9	127.1	123.2	120.9	120.9	120.1
59°	137.1	137.1	135.6	132.5	128.6	123.9	120.1	116.2	113.9	113.1	113.1
60°	130.2	130.9	128.6	125.5	122.4	117.0	112.4	109.3	107.0	106.1	106.1
61°	123.9	123.9	122.4	118.5	114.7	110.8	106.1	102.3	100.7	99.2	99.2
62°	118.5	117.0	116.2	112.4	108.4	103.9	100.0	96.0	93.8	92.2	93.0
63°	111.5	110.8	109.3	106.1	102.3	97.6	93.0	89.9	87.5	85.2	86.1
64°	106.1	105.4	103.0	100.0	96.0	91.5	86.8	83.7	82.1	79.8	79.0
65°	99.2	98.4	97.6	93.8	89.9	85.2	81.4	78.3	76.0	74.4	72.8
66°	93.0	93.8	92.2	89.1	84.5	80.5	75.1	72.0	70.6	68.2	66.6
67°	87.5	87.5	86.1	82.9	78.3	74.4	70.6	66.6	64.3	62.0	61.2
67.5°	84.5	84.5	82.9	79.0	76.0	71.3	67.4	64.3	61.2	59.6	58.1
68°	81.4	81.4	80.5	77.5	73.6	69.0	65.0	61.2	58.1	55.8	55.1
69°	76.0	76.7	75.1	72.0	68.2	63.6	59.6	56.6	53.5	51.1	49.6
70°	71.3	70.6	69.0	65.9	62.0	58.9	55.1	51.1	48.1	45.0	44.1
71°	65.0	65.0	63.6	61.2	57.3	53.5	49.6	46.5	43.4	39.5	38.7
72°	60.5	60.5	58.9	55.8	52.6	48.8	45.0	41.1	38.7	34.9	33.3
72.5°	57.3	58.1	56.6	53.5	50.4	45.7	42.7	39.5	35.7	32.6	31.0
73°	55.8	55.1	54.2	51.1	47.2	44.1	40.3	37.1	33.3	30.2	28.7



TEST NUMBER: P583720
 CATALOG NUMBER: HCC8W10D010MW-HM80520830-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	34.9	34.9	34.1	31.0	27.9	24.8	21.6	18.6	15.5	12.4	10.8
80°	24.0	24.8	23.2	21.6	19.4	16.2	13.2	10.8	7.7	6.3	4.7
82.5°	15.5	15.5	14.7	13.2	11.7	9.3	7.7	5.4	3.8	3.1	2.3
85°	7.7	8.5	7.7	7.0	5.4	4.7	3.8	2.3	1.6	0.7	0.7
87.5°	3.1	3.1	3.1	2.3	2.3	1.6	0.7	0.7	0.7	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583720

CATALOG NUMBER: HCC8W10D010MW-HM80520830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	571.8	571.8	571.8	571.8	571.8	571.8	571.8	571.8	571.8	571.8
2.5°	569.5	569.5	567.9	567.1	566.4	565.7	564.8	564.1	564.1	564.8
5°	564.8	563.3	560.1	559.4	557.1	556.3	554.7	554.0	554.7	554.0
7.5°	557.8	554.7	550.9	549.3	546.2	544.7	542.3	542.3	540.8	541.6
10°	548.6	543.9	539.2	536.2	533.8	531.5	530.0	528.4	527.7	527.7
12.5°	536.9	531.5	526.8	522.3	518.3	516.9	513.7	513.7	512.2	511.3
15°	523.8	516.9	511.3	506.8	503.6	500.5	498.2	496.7	495.1	495.1
17.5°	506.8	500.5	495.1	489.7	485.0	482.7	480.4	478.0	478.0	476.5
20°	488.1	481.2	476.5	471.1	467.2	463.4	460.2	460.2	458.7	459.4
22.5°	467.2	458.7	454.0	450.1	446.3	443.2	440.1	440.1	439.3	438.5
25°	444.0	437.0	431.5	427.0	424.5	421.5	420.7	419.1	418.4	418.4
27.5°	419.1	413.7	406.8	404.5	401.3	399.8	399.8	399.1	397.5	398.2
30°	392.8	386.7	382.7	381.2	378.1	378.1	377.3	375.7	375.7	376.6
32.5°	367.2	361.1	358.0	357.2	354.1	354.1	353.3	354.1	354.1	354.8
35°	339.3	333.9	333.2	330.8	330.1	330.1	330.1	331.6	333.2	330.8
37.5°	313.0	309.2	306.9	306.0	306.9	306.9	307.6	309.9	309.2	308.4
40°	286.0	282.8	281.3	281.3	282.8	284.4	284.4	286.7	287.4	286.7
42.5°	258.8	256.5	256.5	257.2	258.8	259.5	261.9	264.2	265.0	265.8
45°	233.2	233.2	233.2	234.0	234.8	236.3	239.4	241.7	242.6	243.3
47.5°	208.4	207.7	210.0	210.7	213.1	213.8	216.1	219.2	220.1	220.8
50°	185.2	186.7	187.5	189.8	191.4	191.4	194.5	196.0	198.3	198.3
52.5°	163.5	165.8	166.6	168.9	169.7	170.4	172.0	174.3	175.9	175.9
55°	144.1	144.8	146.4	147.2	149.5	150.4	151.8	152.7	154.9	154.2
56°	135.6	137.1	137.9	139.4	141.0	141.8	143.4	144.1	145.7	146.4
57°	127.9	128.6	130.9	131.7	133.3	133.3	134.0	136.4	136.4	137.1
58°	120.1	121.6	122.4	123.2	124.8	125.5	127.1	127.9	128.6	127.9
59°	113.1	113.9	114.7	114.7	116.2	116.2	118.5	120.1	120.9	120.9
60°	106.1	106.1	107.0	107.7	109.3	110.0	110.0	111.5	111.5	111.5
61°	99.2	99.2	100.0	100.7	101.4	101.4	103.0	103.0	103.9	104.6
62°	93.0	92.2	92.2	93.0	93.0	94.5	95.3	96.0	96.9	96.0
63°	86.1	85.2	85.2	85.2	85.2	86.8	86.8	87.5	89.1	88.3
64°	78.3	78.3	78.3	78.3	79.0	79.0	80.5	81.4	82.1	82.9
65°	72.8	71.3	70.6	70.6	71.3	72.0	72.8	73.6	74.4	74.4
66°	66.6	65.0	64.3	64.3	64.3	64.3	65.9	65.9	67.4	67.4
67°	59.6	58.1	57.3	56.6	56.6	56.6	58.9	58.1	58.1	58.1
67.5°	57.3	55.1	54.2	53.5	52.6	54.2	53.5	54.2	54.2	53.5
68°	54.2	52.6	51.1	49.6	49.6	49.6	50.4	51.1	50.4	49.6
69°	48.1	47.2	45.0	43.4	42.7	43.4	42.7	43.4	42.7	43.4
70°	42.7	40.3	38.0	37.1	36.4	36.4	36.4	35.7	36.4	35.7
71°	37.1	34.9	32.6	31.0	30.2	30.2	29.4	30.2	29.4	30.2
72°	31.7	29.4	26.3	24.8	24.8	24.8	24.8	24.0	24.8	24.0
72.5°	29.4	26.3	24.0	22.5	21.6	21.6	21.6	21.6	20.9	21.6
73°	27.2	24.0	20.9	20.2	20.2	20.2	19.4	18.6	19.4	19.4



TEST NUMBER: P583720
CATALOG NUMBER: HCC8W10D010MW-HM80520830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	9.3	7.0	6.3	6.3	6.3	6.3	6.3	6.3	5.4	5.4
80°	3.8	3.1	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
82.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	50.4	50.4	48.8	46.5	42.7	38.7	35.7	32.6	28.7	24.8	23.2
75°	46.5	45.7	44.1	41.8	38.7	34.9	31.7	27.9	24.8	20.9	19.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	22.5	18.6	17.1	15.5	15.5	15.5	14.7	14.7	14.7	15.5
75°	17.8	14.7	13.2	11.7	12.4	11.7	12.4	11.7	11.7	11.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)