

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583947

Luminaire Tested: **HCC8S15D010BZ-HM80520935-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010BZ-HM80520935-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1264.8 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583947
CATALOG NUMBER: HCC8S15D010BZ-HM80520935-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583947

CATALOG NUMBER: HCC8S15D010BZ-HM80520935-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20938	20938	20938
5°	21804	20894	20015
10°	22532	20628	19038
15°	23103	20154	18050
20°	23148	19322	17153
25°	22759	18097	16264
30°	21538	16700	15507
35°	19643	15016	14557
40°	17080	13235	13441
45°	14653	11465	12306
50°	12516	9887	11053
55°	10967	8510	9607
60°	9763	7259	8079
65°	8668	5925	6443
70°	7691	4391	3660
75°	6398	2299	1096
80°	5043	728	178
85°	3573	354	0



TEST NUMBER: P583947
 CATALOG NUMBER: HCC8S15D010BZ-HM80520935-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.0	5.1
10°-20°	179.3	14.2
20°-30°	253.8	20.1
30°-40°	265.6	21.0
40°-50°	221.5	17.5
50°-60°	157.1	12.4
60°-70°	90.5	7.2
70°-80°	29.1	2.3
80°-90°	4.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	497.1	39.3
0°-40°	762.7	60.3
0°-60°	1141.3	90.2
0°-90°	1264.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1264.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	679	679	679	679	679	
5°	704	695	675	655	647	68
15°	724	694	631	582	565	203
25°	669	619	532	489	478	305
35°	522	476	399	378	387	323
45°	336	309	263	266	282	260
55°	204	183	158	166	179	184
65°	119	99	81	81	88	119
75°	54	40	19	9	9	58
85°	10	5	1	0	0	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583947

CATALOG NUMBER: HCC8S15D010BZ-HM80520935-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0
2.5°	693.2	692.3	691.2	692.3	691.2	692.3	691.2	691.2	690.2	689.1	689.1
5°	704.4	703.4	703.4	703.4	702.4	701.4	701.4	700.3	698.3	697.3	695.3
7.5°	711.6	712.5	712.5	712.5	710.5	710.5	708.4	706.5	704.4	702.4	699.4
10°	719.6	719.6	718.7	717.6	715.5	714.6	713.6	711.6	708.4	704.4	701.4
12.5°	722.6	722.6	721.7	719.6	718.7	717.6	716.6	713.6	709.5	704.4	700.3
15°	723.7	721.7	720.7	719.6	717.6	714.6	714.6	710.5	705.4	699.4	694.3
17.5°	715.5	716.6	714.6	712.5	709.5	707.5	704.4	701.4	695.3	688.2	683.1
20°	705.4	704.4	703.4	700.3	696.2	695.3	692.3	687.2	682.0	674.0	666.8
22.5°	689.1	688.2	686.1	684.1	680.1	678.1	675.0	668.9	661.8	653.7	645.5
25°	668.9	666.8	663.8	659.7	656.7	654.7	650.6	644.6	636.4	627.3	619.1
27.5°	636.4	639.5	637.4	631.3	628.3	624.2	623.2	615.2	608.0	598.9	589.7
30°	604.9	604.9	601.9	598.9	593.8	590.7	586.7	580.6	573.5	562.4	555.3
32.5°	565.4	564.3	560.3	559.2	555.3	549.1	548.2	540.0	532.9	524.8	515.6
35°	521.8	519.7	515.6	512.6	510.6	507.5	504.4	497.3	490.2	482.1	476.1
37.5°	472.0	472.0	470.9	465.9	463.8	461.9	458.7	451.6	447.7	439.5	433.4
40°	424.3	423.3	420.2	419.2	417.2	414.2	412.1	408.0	402.0	395.8	389.8
42.5°	377.5	378.6	374.5	375.6	371.5	369.5	368.5	362.3	359.3	353.2	348.1
45°	336.0	335.0	332.9	331.9	329.9	327.9	325.8	322.8	317.6	311.6	308.6
47.5°	297.4	294.4	294.4	293.3	292.3	288.2	287.3	284.3	281.1	275.1	271.0
50°	260.9	260.9	260.9	259.8	256.8	255.8	253.8	250.8	247.6	243.7	237.5
52.5°	231.5	231.5	231.5	230.4	226.3	225.3	224.4	220.3	216.2	213.2	209.1
55°	204.0	205.1	204.0	202.0	198.9	198.9	195.9	193.9	189.8	186.8	182.7
57.5°	180.6	180.6	178.7	177.6	175.6	174.6	172.6	170.5	165.4	162.4	157.4
60°	158.3	157.4	157.4	155.3	153.3	151.2	150.3	147.1	145.2	140.0	136.0
62.5°	138.1	138.1	136.0	136.0	131.9	131.9	131.0	127.9	124.8	119.8	117.7
65°	118.8	118.8	117.7	116.8	113.6	112.7	111.7	108.6	105.6	102.5	99.4
67.5°	101.5	101.5	99.4	98.4	96.4	95.4	93.4	91.3	88.3	85.3	82.2
70°	85.3	84.2	83.3	82.2	80.1	79.2	77.1	75.1	72.1	70.0	67.0
72.5°	69.0	69.0	68.0	66.0	64.9	64.0	62.9	60.9	57.8	54.8	52.8
75°	53.7	53.7	53.7	51.8	49.8	48.7	48.7	46.6	44.7	41.6	39.6
77.5°	41.6	40.6	39.6	39.6	37.6	36.5	35.5	34.5	31.5	30.5	28.4
80°	28.4	29.4	28.4	27.4	26.4	25.4	25.4	23.4	22.3	20.2	18.3
82.5°	19.3	18.3	18.3	17.2	17.2	16.3	16.3	14.2	13.3	12.2	11.2
85°	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1	7.1	6.1	5.1
87.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583947

CATALOG NUMBER: HCC8S15D010BZ-HM80520935-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0
2.5°	688.2	686.1	685.2	685.2	684.1	683.1	682.0	681.1	679.0	679.0	677.0
5°	693.2	691.2	690.2	687.2	685.2	685.2	681.1	680.1	677.0	675.0	673.0
7.5°	697.3	693.2	690.2	687.2	685.2	683.1	679.0	675.0	670.9	666.8	664.8
10°	697.3	693.2	688.2	683.1	681.1	679.0	674.0	667.9	662.8	658.8	653.7
12.5°	695.3	689.1	683.1	679.0	675.0	671.9	665.9	659.7	653.7	645.5	641.5
15°	689.1	681.1	675.0	667.9	664.8	659.7	654.7	645.5	638.4	631.3	626.2
17.5°	677.0	666.8	659.7	652.6	647.6	644.6	636.4	628.3	620.2	612.0	606.0
20°	658.8	649.6	641.5	632.4	628.3	624.2	614.1	606.0	597.8	588.8	582.6
22.5°	636.4	627.3	616.1	609.0	602.9	597.8	588.8	579.6	571.4	563.3	555.3
25°	609.0	599.8	589.7	578.5	574.5	569.4	559.2	550.1	541.0	531.9	524.8
27.5°	579.6	567.4	559.2	547.1	543.0	537.9	526.8	516.6	508.5	501.4	493.3
30°	544.1	534.9	523.7	512.6	508.5	503.4	494.3	485.1	477.1	469.0	460.8
32.5°	505.5	496.3	485.1	477.1	470.9	466.9	457.8	449.7	441.5	433.4	426.3
35°	464.9	454.8	446.6	438.5	433.4	428.4	419.2	412.1	406.0	398.9	391.7
37.5°	423.3	416.2	408.0	398.9	393.8	389.8	382.7	374.5	369.5	363.4	358.2
40°	382.7	374.5	367.4	359.3	355.2	352.2	345.1	339.0	333.9	328.8	325.8
42.5°	341.0	333.9	326.8	321.7	318.7	315.7	310.6	303.5	300.4	295.3	292.3
45°	302.5	296.4	291.2	284.3	282.2	280.2	274.0	269.0	265.9	262.9	260.9
47.5°	265.9	261.8	255.8	251.7	248.7	246.7	242.6	238.5	235.5	233.4	231.5
50°	234.5	229.4	225.3	221.2	219.2	216.2	212.1	210.2	208.1	206.1	206.1
52.5°	205.1	199.9	195.9	192.8	190.9	188.8	185.7	184.7	182.7	182.7	181.7
55°	177.6	174.6	170.5	166.4	165.4	164.5	162.4	160.4	159.3	158.3	159.3
57.5°	154.2	151.2	147.1	144.1	143.2	142.1	141.1	139.1	138.1	138.1	138.1
60°	132.9	129.9	126.9	123.9	123.9	121.8	120.7	119.8	118.8	117.7	117.7
62.5°	113.6	110.6	107.6	105.6	104.6	103.5	101.5	100.5	99.4	99.4	98.4
65°	96.4	92.4	91.3	88.3	87.2	86.3	85.3	83.3	82.2	81.2	80.1
67.5°	79.2	77.1	74.1	72.1	71.1	70.0	69.0	67.0	66.0	64.9	62.9
70°	64.0	61.9	59.9	57.8	56.9	55.8	53.7	51.8	50.7	48.7	45.7
72.5°	49.8	47.7	45.7	43.6	42.7	41.6	39.6	37.6	35.5	33.5	31.5
75°	37.6	35.5	32.5	30.5	29.4	29.4	26.4	24.3	22.3	19.3	17.2
77.5°	26.4	23.4	22.3	20.2	19.3	17.2	15.2	13.3	11.2	10.1	8.1
80°	17.2	15.2	13.3	12.2	11.2	10.1	9.2	7.1	5.1	4.1	3.0
82.5°	10.1	9.2	8.1	7.1	6.1	5.1	4.1	4.1	3.0	2.0	1.0
85°	5.1	4.1	3.0	3.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0
87.5°	2.0	1.0	1.0	1.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583947

CATALOG NUMBER: HCC8S15D010BZ-HM80520935-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0
2.5°	676.0	675.0	674.0	673.0	673.0	670.9	670.9	669.9	667.9	666.8	666.8
5°	669.9	666.8	664.8	663.8	662.8	659.7	658.8	656.7	654.7	652.6	651.7
7.5°	660.8	655.6	653.7	652.6	649.6	646.6	644.6	641.5	638.4	635.4	634.4
10°	649.6	644.6	639.5	637.4	634.4	632.4	628.3	624.2	621.2	618.2	615.2
12.5°	635.4	629.3	624.2	622.1	619.1	615.2	609.0	607.0	601.9	599.8	595.8
15°	619.1	612.0	607.0	603.9	600.9	594.8	590.7	586.7	581.7	579.6	575.5
17.5°	598.9	590.7	585.6	582.6	580.6	575.5	569.4	564.3	559.2	557.2	554.2
20°	574.5	569.4	562.4	559.2	557.2	551.2	545.0	543.0	539.0	534.9	531.9
22.5°	547.1	542.0	534.9	531.9	530.8	525.7	520.7	517.7	514.7	511.5	508.5
25°	518.6	512.6	506.5	504.4	502.5	498.4	494.3	492.2	489.2	487.2	485.1
27.5°	488.3	482.1	477.1	474.0	472.0	469.0	466.9	464.9	462.8	460.8	459.8
30°	455.7	449.7	445.6	443.6	441.5	440.5	437.4	436.5	435.5	433.4	434.4
32.5°	423.3	418.1	414.2	411.0	411.0	409.1	408.0	408.0	407.0	407.0	407.0
35°	387.8	384.6	381.6	380.7	379.6	378.6	377.5	378.6	377.5	378.6	379.6
37.5°	355.2	352.2	350.2	349.2	348.1	349.2	348.1	348.1	349.2	351.1	352.2
40°	321.7	319.7	317.6	318.7	317.6	317.6	317.6	320.8	321.7	322.8	323.8
42.5°	290.3	288.2	287.3	287.3	288.2	287.3	289.3	290.3	292.3	295.3	297.4
45°	259.8	258.8	258.8	259.8	258.8	260.9	260.9	262.9	265.9	268.0	270.0
47.5°	231.5	231.5	231.5	232.4	232.4	233.4	235.5	236.5	238.5	240.5	242.6
50°	205.1	206.1	207.0	207.0	207.0	209.1	211.1	212.1	213.2	214.1	217.3
52.5°	181.7	182.7	182.7	183.8	184.7	185.7	186.8	188.8	189.8	191.8	192.8
55°	159.3	159.3	161.3	162.4	162.4	162.4	164.5	164.5	166.4	167.5	169.5
57.5°	138.1	139.1	139.1	140.0	140.0	141.1	142.1	143.2	144.1	145.2	146.2
60°	117.7	117.7	117.7	118.8	119.8	120.7	119.8	121.8	121.8	123.9	124.8
62.5°	98.4	99.4	99.4	99.4	99.4	99.4	99.4	100.5	101.5	102.5	103.5
65°	80.1	80.1	80.1	79.2	80.1	79.2	80.1	81.2	81.2	82.2	83.3
67.5°	61.9	61.9	59.9	59.9	60.9	60.9	60.9	60.9	59.9	61.9	61.9
70°	44.7	43.6	42.7	41.6	41.6	40.6	40.6	39.6	39.6	39.6	39.6
72.5°	29.4	27.4	25.4	24.3	23.4	23.4	21.3	20.2	21.3	21.3	21.3
75°	15.2	13.3	12.2	11.2	10.1	10.1	9.2	9.2	9.2	9.2	9.2
77.5°	6.1	5.1	4.1	4.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0
80°	2.0	2.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	1.0	0.0	0.0	1.0	0.0	1.0	1.0	1.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583947

CATALOG NUMBER: HCC8S15D010BZ-HM80520935-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	679.0	679.0	679.0	679.0	679.0	679.0	679.0	679.0
2.5°	665.9	665.9	664.8	665.9	663.8	664.8	663.8	663.8
5°	650.6	648.5	648.5	648.5	647.6	647.6	646.6	646.6
7.5°	632.4	631.3	630.3	629.3	628.3	627.3	627.3	627.3
10°	614.1	612.0	612.0	611.1	609.0	608.0	608.0	608.0
12.5°	592.7	591.8	590.7	590.7	586.7	587.7	586.7	586.7
15°	572.5	571.4	571.4	568.4	566.4	566.4	566.4	565.4
17.5°	551.2	550.1	549.1	547.1	545.0	545.0	544.1	545.0
20°	528.9	527.8	525.7	525.7	524.8	523.7	521.8	522.7
22.5°	506.5	504.4	503.4	503.4	502.5	502.5	500.4	500.4
25°	483.1	482.1	481.2	482.1	480.1	480.1	478.0	478.0
27.5°	458.7	457.8	457.8	457.8	456.7	457.8	456.7	456.7
30°	434.4	434.4	433.4	433.4	434.4	433.4	434.4	435.5
32.5°	408.0	408.0	409.1	409.1	410.1	410.1	410.1	410.1
35°	380.7	382.7	382.7	383.7	384.6	385.7	385.7	386.7
37.5°	355.2	356.3	357.3	358.2	360.3	360.3	360.3	360.3
40°	327.9	328.8	330.9	329.9	333.9	335.0	333.9	333.9
42.5°	299.4	301.5	302.5	304.5	305.5	307.5	308.6	308.6
45°	273.1	274.0	276.1	278.1	279.1	282.2	282.2	282.2
47.5°	245.6	247.6	248.7	250.8	251.7	254.7	255.8	254.7
50°	219.2	221.2	223.3	223.3	226.3	227.4	229.4	230.4
52.5°	193.9	194.8	196.9	198.0	199.9	202.0	203.0	204.0
55°	169.5	170.5	172.6	172.6	175.6	176.7	178.7	178.7
57.5°	147.1	148.2	150.3	149.2	151.2	153.3	153.3	152.2
60°	125.8	125.8	125.8	127.9	128.9	129.9	131.0	131.0
62.5°	103.5	105.6	106.5	106.5	107.6	108.6	108.6	107.6
65°	83.3	85.3	86.3	86.3	87.2	87.2	87.2	88.3
67.5°	62.9	62.9	62.9	64.0	62.9	62.9	62.9	62.9
70°	39.6	39.6	39.6	39.6	38.6	39.6	39.6	40.6
72.5°	21.3	21.3	21.3	21.3	21.3	21.3	21.3	21.3
75°	9.2	9.2	9.2	10.1	9.2	9.2	9.2	9.2
77.5°	4.1	3.0	4.1	4.1	3.0	3.0	3.0	3.0
80°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	0.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)