

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583718

Luminaire Tested: **HCC8S10D010MW-HM80520830-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S10D010MW-HM80520830-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1151.7 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583718
CATALOG NUMBER: HCC8S10D010MW-HM80520830-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583718
 CATALOG NUMBER: HCC8S10D010MW-HM80520830-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89	89	89	89	89	89	89	89	89	89	89	89															
	2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79	79	79	79	79	79	79	79	79	79	79	79															
	3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71	71	71	71	71	71	71	71	71	71	71															
	4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64	64	64	64	64	64	64	64	64	64	64	64	64														
	5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58	58	58	58	58	58	58	58	58	58	58															
	6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53	53	53	53	53	53	53	53	53	53	53															
	7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49	49	49	49	49	49	49	49	49	49	49	49	49														
	8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45	45	45	45	45	45	45	45	45	45	45	45	45														
	9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42	42	42	42	42	42	42	42	42	42														
	10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39	39	39	39	39	39	39	39	39	39	39	39	39														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27034
5°	26682
10°	25707
15°	24700
20°	24018
25°	23296
30°	20905
35°	13702
40°	7576
45°	6315
50°	5762
55°	5500
60°	5106
65°	4633
70°	4192
75°	3777
80°	3445
85°	3290



TEST NUMBER: P583718
 CATALOG NUMBER: HCC8S10D010MW-HM80520830-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	7.0
10°-20°	218.3	19.0
20°-30°	310.7	27.0
30°-40°	229.9	20.0
40°-50°	113.9	9.9
50°-60°	90.9	7.9
60°-70°	63.1	5.5
70°-80°	34.0	3.0
80°-90°	10.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	609.9	53.0
0°-40°	839.9	72.9
0°-60°	1044.6	90.7
0°-90°	1151.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1151.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	877	
5°	862	81
15°	774	218
25°	685	311
35°	364	230
45°	145	114
55°	102	91
65°	64	63
75°	32	34
85°	9	10
90°	0	



TEST NUMBER: P583718
CATALOG NUMBER: HCC8S10D010MW-HM80520830-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	876.7
2.5°	872.9
5°	862.0
7.5°	845.0
10°	821.0
12.5°	796.2
15°	773.7
17.5°	752.0
20°	731.9
22.5°	711.7
25°	684.7
27.5°	645.1
30°	587.1
32.5°	498.0
35°	364.0
37.5°	248.6
40°	188.2
42.5°	161.1
45°	144.8
47.5°	131.6
50°	120.1
52.5°	110.0
55°	102.3
57.5°	92.9
60°	82.8
62.5°	72.8
65°	63.5
67.5°	54.2
70°	46.5
72.5°	38.7
75°	31.7
77.5°	25.6
80°	19.4
82.5°	13.9
85°	9.3
87.5°	3.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)