

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583941

Luminaire Tested: **HCC8S15D010MW-HM80520935-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010MW-HM80520935-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1404.9 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583941
CATALOG NUMBER: HCC8S15D010MW-HM80520935-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583941

CATALOG NUMBER: HCC8S15D010MW-HM80520935-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88				
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77				77				
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67				
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59				
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47				
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35				35				
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23109	23109	23109
5°	23544	23011	22473
10°	23910	22607	21652
15°	24151	22047	20716
20°	24057	21195	19758
25°	23426	19972	18659
30°	22311	18515	17575
35°	20143	16898	16323
40°	17700	15168	15123
45°	15276	13331	13903
50°	13303	11696	12468
55°	11790	10150	10865
60°	10521	8585	9023
65°	9485	6961	7114
70°	8421	5211	4219
75°	7268	3026	1811
80°	5594	1083	533
85°	3573	354	354



TEST NUMBER: P583941
 CATALOG NUMBER: HCC8S15D010MW-HM80520935-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.4	5.0
10°-20°	195.8	13.9
20°-30°	277.0	19.7
30°-40°	291.9	20.8
40°-50°	248.1	17.7
50°-60°	178.6	12.7
60°-70°	103.0	7.3
70°-80°	35.3	2.5
80°-90°	4.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.2	38.7
0°-40°	835.1	59.4
0°-60°	1261.8	89.8
0°-90°	1404.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1404.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	749	749	749	749	749	
5°	761	756	743	730	726	73
15°	756	733	691	660	649	213
25°	688	653	587	556	548	316
35°	535	504	449	433	434	333
45°	350	334	306	308	319	272
55°	219	202	189	196	202	197
65°	130	112	95	93	98	129
75°	61	46	25	16	15	64
85°	10	6	1	1	1	14
90°	0	0	0	0	0	



TEST NUMBER: P583941

CATALOG NUMBER: HCC8S15D010MW-HM80520935-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4
2.5°	756.5	757.6	756.5	756.5	755.5	754.5	753.5	752.5	750.5	748.4	748.4
5°	760.6	762.6	760.6	760.6	757.6	755.5	753.5	750.5	746.4	743.4	743.4
7.5°	763.6	763.6	763.6	760.6	758.5	755.5	750.5	745.4	740.2	735.2	733.1
10°	763.6	763.6	762.6	758.5	756.5	750.5	745.4	738.3	731.2	724.1	722.0
12.5°	760.6	761.6	759.6	755.5	750.5	743.4	736.3	727.1	718.9	710.8	706.7
15°	756.5	755.5	753.5	748.4	742.3	733.1	726.0	715.9	704.8	694.6	690.6
17.5°	746.4	746.4	743.4	738.3	730.1	720.0	708.8	697.7	685.4	674.3	669.3
20°	733.1	733.1	729.1	723.0	714.9	701.7	689.5	676.4	662.1	650.9	645.9
22.5°	713.8	714.9	709.9	702.8	693.6	678.3	666.1	649.9	635.6	622.5	618.4
25°	688.5	690.6	685.4	678.3	666.1	653.0	637.7	622.5	606.2	593.1	587.0
27.5°	659.0	660.1	655.0	647.9	635.6	621.4	606.2	590.0	574.8	560.6	554.4
30°	626.6	622.5	620.5	611.3	598.2	586.0	568.6	555.5	539.2	527.1	520.0
32.5°	580.8	582.9	576.8	569.7	559.5	545.3	531.0	515.9	500.7	491.5	486.5
35°	535.1	537.2	534.2	527.1	515.9	503.7	489.5	478.3	465.1	453.9	448.9
37.5°	487.4	487.4	485.4	481.4	473.2	462.0	447.8	436.7	425.5	416.3	413.3
40°	439.7	437.7	436.7	433.6	426.4	416.3	407.2	398.0	386.9	380.8	376.8
42.5°	393.0	393.0	390.9	387.9	380.8	375.7	366.6	356.4	348.4	342.2	342.2
45°	350.3	351.4	348.4	346.3	342.2	334.1	326.0	318.8	311.7	307.6	305.7
47.5°	312.8	312.8	309.7	307.6	303.7	296.6	289.4	283.3	278.2	275.2	274.1
50°	277.3	277.3	277.3	272.2	267.0	262.0	256.9	249.8	246.8	244.7	243.8
52.5°	246.8	245.7	245.7	241.7	236.7	230.5	225.5	219.3	216.3	214.2	215.3
55°	219.3	219.3	218.3	213.3	208.2	202.1	197.0	192.0	189.9	187.9	188.8
56°	208.2	208.2	207.1	203.0	197.0	192.0	185.8	180.8	177.7	178.7	178.7
57°	200.0	198.0	198.0	192.9	187.9	180.8	175.7	170.6	168.6	167.5	167.5
58°	189.9	188.8	187.9	182.8	177.7	171.6	166.5	161.5	158.5	158.5	157.4
59°	179.8	179.8	177.7	173.6	168.6	162.4	157.4	152.3	149.3	148.2	148.2
60°	170.6	171.6	168.6	164.5	160.5	153.4	147.3	143.2	140.1	139.2	139.2
61°	162.4	162.4	160.5	155.3	150.3	145.2	139.2	134.0	132.1	130.0	130.0
62°	155.3	153.4	152.3	147.3	142.2	136.0	131.0	125.9	122.9	120.9	121.8
63°	146.3	145.2	143.2	139.2	134.0	128.0	121.8	117.8	114.7	111.7	112.7
64°	139.2	138.1	135.1	131.0	125.9	119.8	113.8	109.7	107.6	104.6	103.6
65°	130.0	128.9	128.0	122.9	117.8	111.7	106.6	102.5	99.5	97.5	95.4
66°	121.8	122.9	120.9	116.8	110.7	105.6	98.4	94.5	92.4	89.4	87.4
67°	114.7	114.7	112.7	108.7	102.5	97.5	92.4	87.4	84.2	81.2	80.3
67.5°	110.7	110.7	108.7	103.6	99.5	93.4	88.3	84.2	80.3	78.2	76.2
68°	106.6	106.6	105.6	101.6	96.5	90.4	85.3	80.3	76.2	73.1	72.1
69°	99.5	100.5	98.4	94.5	89.4	83.3	78.2	74.1	70.0	67.0	64.9
70°	93.4	92.4	90.4	86.3	81.2	77.1	72.1	67.0	62.9	58.9	57.8
71°	85.3	85.3	83.3	80.3	75.2	70.0	64.9	61.0	56.9	51.8	50.7
72°	79.2	79.2	77.1	73.1	69.0	64.0	58.9	53.9	50.7	45.7	43.6
72.5°	75.2	76.2	74.1	70.0	66.0	59.9	55.8	51.8	46.8	42.7	40.6
73°	73.1	72.1	71.1	67.0	61.9	57.8	52.8	48.8	43.6	39.6	37.6



TEST NUMBER: P583941
 CATALOG NUMBER: HCC8S15D010MW-HM80520935-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	45.7	45.7	44.7	40.6	36.5	32.5	28.4	24.3	20.4	16.3	14.2
80°	31.5	32.5	30.5	28.4	25.4	21.3	17.2	14.2	10.1	8.1	6.1
82.5°	20.4	20.4	19.3	17.2	15.2	12.2	10.1	7.1	5.1	4.1	3.0
85°	10.1	11.2	10.1	9.2	7.1	6.1	5.1	3.0	2.0	1.0	1.0
87.5°	4.1	4.1	4.1	3.0	3.0	2.0	1.0	1.0	1.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583941

CATALOG NUMBER: HCC8S15D010MW-HM80520935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4
2.5°	746.4	746.4	744.3	743.4	742.3	741.3	740.2	739.3	739.3	740.2
5°	740.2	738.3	734.2	733.1	730.1	729.1	727.1	726.0	727.1	726.0
7.5°	731.2	727.1	722.0	720.0	715.9	713.8	710.8	710.8	708.8	709.9
10°	718.9	712.9	706.7	702.8	699.6	696.6	694.6	692.5	691.5	691.5
12.5°	703.7	696.6	690.6	684.4	679.4	677.3	673.2	673.2	671.2	670.2
15°	686.5	677.3	670.2	664.1	660.1	656.0	653.0	650.9	648.9	648.9
17.5°	664.1	656.0	648.9	641.8	635.6	632.6	629.6	626.6	626.6	624.6
20°	639.7	630.6	624.6	617.4	612.4	607.2	603.2	603.2	601.2	602.1
22.5°	612.4	601.2	595.0	590.0	584.9	580.8	576.8	576.8	575.7	574.8
25°	581.9	572.7	565.6	559.5	556.5	552.4	551.4	549.4	548.4	548.4
27.5°	549.4	542.2	533.1	530.1	526.0	523.9	523.9	523.0	520.9	522.0
30°	514.9	506.7	501.6	499.6	495.5	495.5	494.5	492.5	492.5	493.6
32.5°	481.4	473.2	469.1	468.1	464.0	464.0	463.1	464.0	464.0	465.1
35°	444.8	437.7	436.7	433.6	432.6	432.6	432.6	434.6	436.7	433.6
37.5°	410.3	405.1	402.1	401.1	402.1	402.1	403.2	406.2	405.1	404.2
40°	374.8	370.7	368.6	368.6	370.7	372.7	372.7	375.7	376.8	375.7
42.5°	339.2	336.1	336.1	337.2	339.2	340.2	343.2	346.3	347.3	348.4
45°	305.7	305.7	305.7	306.7	307.6	309.7	313.8	316.8	317.9	318.8
47.5°	273.2	272.2	275.2	276.2	279.2	280.3	283.3	287.4	288.4	289.4
50°	242.7	244.7	245.7	248.8	250.9	250.9	254.9	256.9	259.9	259.9
52.5°	214.2	217.3	218.3	221.4	222.4	223.4	225.5	228.5	230.5	230.5
55°	188.8	189.9	192.0	192.9	195.9	197.0	199.1	200.0	203.0	202.1
56°	177.7	179.8	180.8	182.8	184.8	185.8	187.9	188.8	190.9	192.0
57°	167.5	168.6	171.6	172.7	174.6	174.6	175.7	178.7	178.7	179.8
58°	157.4	159.4	160.5	161.5	163.5	164.5	166.5	167.5	168.6	167.5
59°	148.2	149.3	150.3	150.3	152.3	152.3	155.3	157.4	158.5	158.5
60°	139.2	139.2	140.1	141.1	143.2	144.2	144.2	146.3	146.3	146.3
61°	130.0	130.0	131.0	132.1	133.0	133.0	135.1	135.1	136.0	137.1
62°	121.8	120.9	120.9	121.8	121.8	123.9	125.0	125.9	126.9	125.9
63°	112.7	111.7	111.7	111.7	111.7	113.8	113.8	114.7	116.8	115.8
64°	102.5	102.5	102.5	102.5	103.6	103.6	105.6	106.6	107.6	108.7
65°	95.4	93.4	92.4	92.4	93.4	94.5	95.4	96.5	97.5	97.5
66°	87.4	85.3	84.2	84.2	84.2	84.2	86.3	86.3	88.3	88.3
67°	78.2	76.2	75.2	74.1	74.1	74.1	77.1	76.2	76.2	76.2
67.5°	75.2	72.1	71.1	70.0	69.0	71.1	70.0	71.1	71.1	70.0
68°	71.1	69.0	67.0	64.9	64.9	64.9	66.0	67.0	66.0	64.9
69°	62.9	61.9	58.9	56.9	55.8	56.9	55.8	56.9	55.8	56.9
70°	55.8	52.8	49.8	48.8	47.7	47.7	47.7	46.8	47.7	46.8
71°	48.8	45.7	42.7	40.6	39.6	39.6	38.6	39.6	38.6	39.6
72°	41.7	38.6	34.6	32.5	32.5	32.5	32.5	31.5	32.5	31.5
72.5°	38.6	34.6	31.5	29.4	28.4	28.4	28.4	28.4	27.5	28.4
73°	35.5	31.5	27.5	26.4	26.4	26.4	25.4	24.3	25.4	25.4



TEST NUMBER: P583941
CATALOG NUMBER: HCC8S15D010MW-HM80520935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	12.2	9.2	8.1	8.1	8.1	8.1	8.1	8.1	7.1	7.1
80°	5.1	4.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	66.0	66.0	64.0	61.0	55.8	50.7	46.8	42.7	37.6	32.5	30.5
75°	61.0	59.9	57.8	54.8	50.7	45.7	41.7	36.5	32.5	27.5	25.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	29.4	24.3	22.3	20.4	20.4	20.4	19.3	19.3	19.3	20.4
75°	23.4	19.3	17.2	15.2	16.3	15.2	16.3	15.2	15.2	15.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)