

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593571

Luminaire Tested: **HCC8S15D010BZ-HM80520950-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S15D010BZ-HM80520950-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1663.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593571
CATALOG NUMBER: HCC8S15D010BZ-HM80520950-81WDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593571

CATALOG NUMBER: HCC8S15D010BZ-HM80520950-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57																			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44																			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38071
5°	37213
10°	36075
15°	35346
20°	35027
25°	34504
30°	32680
35°	27153
40°	15993
45°	10580
50°	8323
55°	6129
60°	4255
65°	2590
70°	1127
75°	500
80°	355
85°	0



TEST NUMBER: P593571
 CATALOG NUMBER: HCC8S15D010BZ-HM80520950-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.2	6.8
10°-20°	313.0	18.8
20°-30°	463.7	27.9
30°-40°	428.5	25.8
40°-50°	197.6	11.9
50°-60°	103.9	6.2
60°-70°	36.7	2.2
70°-80°	5.8	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.9	53.5
0°-40°	1318.4	79.3
0°-60°	1619.9	97.4
0°-90°	1663.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1663.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1235	
5°	1202	113
15°	1107	313
25°	1014	464
35°	721	428
45°	243	198
55°	114	104
65°	36	37
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P593571
CATALOG NUMBER: HCC8S15D010BZ-HM80520950-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1234.6
2.5°	1224.2
5°	1202.2
7.5°	1178.2
10°	1152.1
12.5°	1127.0
15°	1107.2
17.5°	1089.3
20°	1067.4
22.5°	1043.3
25°	1014.1
27.5°	974.4
30°	917.8
32.5°	837.4
35°	721.3
37.5°	554.1
40°	397.3
42.5°	298.0
45°	242.6
47.5°	205.9
50°	173.5
52.5°	142.2
55°	114.0
57.5°	89.9
60°	69.0
62.5°	52.3
65°	35.5
67.5°	21.0
70°	12.5
72.5°	7.4
75°	4.2
77.5°	3.1
80°	2.0
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)