

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583992

Luminaire Tested: **HCC8S20D010MB-HM80520830-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520830-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2003.9 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583992
CATALOG NUMBER: HCC8S20D010MB-HM80520830-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583992

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32961	32961	32961
5°	33579	32821	32059
10°	34105	32248	30886
15°	34446	31445	29546
20°	34315	30233	28188
25°	33412	28485	26610
30°	31822	26406	25064
35°	28734	24100	23279
40°	25247	21628	21572
45°	21791	19009	19833
50°	18968	16675	17788
55°	16822	14483	15499
60°	15011	12242	12865
65°	13535	9938	10142
70°	12009	7438	6014
75°	10353	4313	2585
80°	7973	1545	781
85°	5130	495	495



TEST NUMBER: P583992
 CATALOG NUMBER: HCC8S20D010MB-HM80520830-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	5.0
10°-20°	279.3	13.9
20°-30°	395.1	19.7
30°-40°	416.3	20.8
40°-50°	353.8	17.7
50°-60°	254.8	12.7
60°-70°	147.0	7.3
70°-80°	50.3	2.5
80°-90°	6.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	774.8	38.7
0°-40°	1191.1	59.4
0°-60°	1799.7	89.8
0°-90°	2003.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2003.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1069	1069	1069	1069	1069	
5°	1085	1078	1060	1042	1036	104
15°	1079	1046	985	942	926	304
25°	982	931	837	794	782	450
35°	763	718	640	617	618	475
45°	500	477	436	439	455	388
55°	313	288	269	280	288	282
65°	186	159	136	133	139	184
75°	87	65	36	23	22	92
85°	14	9	1	1	1	20
90°	0	0	0	0	0	



TEST NUMBER: P583992

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9
2.5°	1079.0	1080.5	1079.0	1079.0	1077.6	1076.2	1074.7	1073.3	1070.4	1067.5	1067.5
5°	1084.8	1087.8	1084.8	1084.8	1080.5	1077.6	1074.7	1070.4	1064.6	1060.3	1060.3
7.5°	1089.2	1089.2	1089.2	1084.8	1082.0	1077.6	1070.4	1063.1	1055.9	1048.7	1045.7
10°	1089.2	1089.2	1087.8	1082.0	1079.0	1070.4	1063.1	1053.0	1042.9	1032.7	1029.9
12.5°	1084.8	1086.3	1083.4	1077.6	1070.4	1060.3	1050.1	1037.1	1025.5	1013.9	1008.1
15°	1079.0	1077.6	1074.7	1067.5	1058.8	1045.7	1035.7	1021.1	1005.2	990.8	985.0
17.5°	1064.6	1064.6	1060.3	1053.0	1041.5	1026.9	1011.0	995.0	977.6	961.8	954.5
20°	1045.7	1045.7	1039.9	1031.3	1019.7	1000.9	983.4	964.6	944.4	928.5	921.3
22.5°	1018.3	1019.7	1012.5	1002.3	989.2	967.6	950.2	927.0	906.7	887.9	882.1
25°	982.0	985.0	977.6	967.6	950.2	931.3	909.7	887.9	864.8	845.8	837.2
27.5°	940.0	941.5	934.3	924.1	906.7	886.4	864.8	841.6	819.8	799.5	790.9
30°	893.7	887.9	885.0	872.0	853.2	835.8	811.1	792.3	769.1	751.8	741.6
32.5°	828.5	831.4	822.7	812.5	798.1	777.8	757.5	735.8	714.0	701.0	693.8
35°	763.3	766.2	761.9	751.8	735.8	718.4	698.1	682.3	663.3	647.5	640.2
37.5°	695.3	695.3	692.3	686.5	674.9	659.1	638.8	622.8	606.8	593.8	589.5
40°	627.2	624.2	622.8	618.4	608.4	593.8	580.8	567.8	551.9	543.1	537.3
42.5°	560.5	560.5	557.7	553.3	543.1	535.9	522.9	508.4	496.8	488.2	488.2
45°	499.7	501.2	496.8	494.0	488.2	476.6	465.0	454.8	444.7	438.9	435.9
47.5°	446.1	446.1	441.7	438.9	433.1	422.9	412.8	404.1	396.9	392.5	391.1
50°	395.4	395.4	395.4	388.2	381.0	373.7	366.4	356.3	352.0	349.0	347.6
52.5°	352.0	350.5	350.5	344.7	337.5	328.8	321.5	312.9	308.5	305.7	307.1
55°	312.9	312.9	311.5	304.1	296.9	288.3	281.0	273.8	270.8	268.0	269.4
56°	296.9	296.9	295.5	289.7	281.0	273.8	265.0	257.8	253.4	255.0	255.0
57°	285.3	282.5	282.5	275.2	268.0	257.8	250.6	243.4	240.4	239.0	239.0
58°	270.8	269.4	268.0	260.7	253.4	244.8	237.6	230.3	226.0	226.0	224.5
59°	256.4	256.4	253.4	247.6	240.4	231.8	224.5	217.3	212.9	211.5	211.5
60°	243.4	244.8	240.4	234.6	228.8	218.7	210.0	204.2	199.9	198.5	198.5
61°	231.8	231.8	228.8	221.6	214.4	207.1	198.5	191.2	188.3	185.5	185.5
62°	221.6	218.7	217.3	210.0	202.8	194.1	186.9	179.5	175.3	172.3	173.8
63°	208.6	207.1	204.2	198.5	191.2	182.5	173.8	168.0	163.7	159.3	160.8
64°	198.5	197.0	192.7	186.9	179.5	170.9	162.2	156.4	153.5	149.2	147.8
65°	185.5	183.9	182.5	175.3	168.0	159.3	152.1	146.3	142.0	139.0	136.2
66°	173.8	175.3	172.3	166.5	157.9	150.6	140.5	134.7	131.8	127.4	124.6
67°	163.7	163.7	160.8	155.0	146.3	139.0	131.8	124.6	120.2	115.8	114.4
67.5°	157.9	157.9	155.0	147.8	142.0	133.2	126.0	120.2	114.4	111.6	108.6
68°	152.1	152.1	150.6	144.8	137.6	129.0	121.6	114.4	108.6	104.3	102.8
69°	142.0	143.4	140.5	134.7	127.4	118.8	111.6	105.8	100.0	95.6	92.7
70°	133.2	131.8	129.0	123.2	115.8	110.0	102.8	95.6	89.8	84.0	82.5
71°	121.6	121.6	118.8	114.4	107.2	100.0	92.7	86.9	81.1	73.9	72.5
72°	113.0	113.0	110.0	104.3	98.5	91.3	84.0	76.7	72.5	65.1	62.3
72.5°	107.2	108.6	105.8	100.0	94.2	85.5	79.7	73.9	66.7	60.9	57.9
73°	104.3	102.8	101.4	95.6	88.3	82.5	75.3	69.5	62.3	56.5	53.5



TEST NUMBER: P583992
 CATALOG NUMBER: HCC8S20D010MB-HM80520830-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	65.1	65.1	63.7	57.9	52.1	46.3	40.5	34.8	29.0	23.2	20.3
80°	44.9	46.3	43.5	40.5	36.2	30.4	24.6	20.3	14.5	11.6	8.7
82.5°	29.0	29.0	27.5	24.6	21.7	17.4	14.5	10.2	7.2	5.8	4.4
85°	14.5	16.0	14.5	13.0	10.2	8.7	7.2	4.4	3.0	1.4	1.4
87.5°	5.8	5.8	5.8	4.4	4.4	3.0	1.4	1.4	1.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P583992

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9	1068.9
2.5°	1064.6	1064.6	1061.7	1060.3	1058.8	1057.3	1055.9	1054.5	1054.5	1055.9
5°	1055.9	1053.0	1047.3	1045.7	1041.5	1039.9	1037.1	1035.7	1037.1	1035.7
7.5°	1042.9	1037.1	1029.9	1026.9	1021.1	1018.3	1013.9	1013.9	1011.0	1012.5
10°	1025.5	1016.8	1008.1	1002.3	998.0	993.6	990.8	987.8	986.4	986.4
12.5°	1003.8	993.6	985.0	976.2	969.0	966.0	960.3	960.3	957.4	956.0
15°	979.2	966.0	956.0	947.3	941.5	935.7	931.3	928.5	925.5	925.5
17.5°	947.3	935.7	925.5	915.5	906.7	902.3	898.0	893.7	893.7	890.8
20°	912.5	899.5	890.8	880.6	873.4	866.2	860.4	860.4	857.4	859.0
22.5°	873.4	857.4	848.8	841.6	834.3	828.5	822.7	822.7	821.3	819.8
25°	830.0	816.9	806.7	798.1	793.7	787.9	786.5	783.5	782.1	782.1
27.5°	783.5	773.5	760.4	756.1	750.3	747.4	747.4	746.0	743.0	744.5
30°	734.4	722.8	715.5	712.6	706.8	706.8	705.4	702.5	702.5	703.9
32.5°	686.5	674.9	669.1	667.7	661.9	661.9	660.5	661.9	661.9	663.3
35°	634.4	624.2	622.8	618.4	617.0	617.0	617.0	620.0	622.8	618.4
37.5°	585.2	577.9	573.6	572.1	573.6	573.6	575.0	579.4	577.9	576.5
40°	534.5	528.7	525.8	525.8	528.7	531.5	531.5	535.9	537.3	535.9
42.5°	483.8	479.4	479.4	480.8	483.8	485.2	489.6	494.0	495.4	496.8
45°	435.9	435.9	435.9	437.5	438.9	441.7	447.5	451.9	453.4	454.8
47.5°	389.6	388.2	392.5	394.0	398.3	399.8	404.1	409.9	411.3	412.8
50°	346.2	349.0	350.5	354.8	357.8	357.8	363.6	366.4	370.8	370.8
52.5°	305.7	309.9	311.5	315.7	317.2	318.7	321.5	325.9	328.8	328.8
55°	269.4	270.8	273.8	275.2	279.5	281.0	283.9	285.3	289.7	288.3
56°	253.4	256.4	257.8	260.7	263.6	265.0	268.0	269.4	272.3	273.8
57°	239.0	240.4	244.8	246.2	249.2	249.2	250.6	255.0	255.0	256.4
58°	224.5	227.4	228.8	230.3	233.2	234.6	237.6	239.0	240.4	239.0
59°	211.5	212.9	214.4	214.4	217.3	217.3	221.6	224.5	226.0	226.0
60°	198.5	198.5	199.9	201.3	204.2	205.7	205.7	208.6	208.6	208.6
61°	185.5	185.5	186.9	188.3	189.7	189.7	192.7	192.7	194.1	195.5
62°	173.8	172.3	172.3	173.8	173.8	176.7	178.1	179.5	181.1	179.5
63°	160.8	159.3	159.3	159.3	159.3	162.2	162.2	163.7	166.5	165.1
64°	146.3	146.3	146.3	146.3	147.8	147.8	150.6	152.1	153.5	155.0
65°	136.2	133.2	131.8	131.8	133.2	134.7	136.2	137.6	139.0	139.0
66°	124.6	121.6	120.2	120.2	120.2	120.2	123.2	123.2	126.0	126.0
67°	111.6	108.6	107.2	105.8	105.8	105.8	110.0	108.6	108.6	108.6
67.5°	107.2	102.8	101.4	100.0	98.5	101.4	100.0	101.4	101.4	100.0
68°	101.4	98.5	95.6	92.7	92.7	92.7	94.2	95.6	94.2	92.7
69°	89.8	88.3	84.0	81.1	79.7	81.1	79.7	81.1	79.7	81.1
70°	79.7	75.3	70.9	69.5	68.1	68.1	68.1	66.7	68.1	66.7
71°	69.5	65.1	60.9	57.9	56.5	56.5	55.1	56.5	55.1	56.5
72°	59.3	55.1	49.3	46.3	46.3	46.3	46.3	44.9	46.3	44.9
72.5°	55.1	49.3	44.9	42.0	40.5	40.5	40.5	40.5	39.1	40.5
73°	50.7	44.9	39.1	37.7	37.7	37.7	36.2	34.8	36.2	36.2



TEST NUMBER: P583992

CATALOG NUMBER: HCC8S20D010MB-HM80520830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	17.4	13.0	11.6	11.6	11.6	11.6	11.6	11.6	10.2	10.2
80°	7.2	5.8	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
82.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
85°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	94.2	94.2	91.3	86.9	79.7	72.5	66.7	60.9	53.5	46.3	43.5
75°	86.9	85.5	82.5	78.2	72.5	65.1	59.3	52.1	46.3	39.1	36.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	42.0	34.8	31.9	29.0	29.0	29.0	27.5	27.5	27.5	29.0
75°	33.3	27.5	24.6	21.7	23.2	21.7	23.2	21.7	21.7	21.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)