

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583772

Luminaire Tested: **HCC8S10D010MW-HM80520927-81WDBB**

Issue Date: 10/21/2021

### Test Information

Test Method: LM-41-14  
 Report Number: P583772  
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 10/21/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO COMMERCIAL  
 Catalog Number: HCC8S10D010MW-HM80520927-81WDBB  
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
 Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
 Ballast/Driver: ELECTRONIC DRIVER

### Summary


Lumens per Lamp: N/A  
 Luminaire Lumens: 947.2 lumens  
 Efficiency: N/A  
 Efficacy: 95.7 lumens/watt  
 Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
 Luminous Opening: Circular (Dia: 0.67' x H: 0')  
 CIE Type: Direct

Input Watts (W): 9.9  
 Input Voltage (V): NR  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



TEST NUMBER: P583772  
CATALOG NUMBER: HCC8S10D010MW-HM80520927-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P583772  
 CATALOG NUMBER: HCC8S10D010MW-HM80520927-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62																			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	17746
5°	17597
10°	17366
15°	17565
20°	18967
25°	20744
30°	20492
35°	17000
40°	10007
45°	6537
50°	5071
55°	3365
60°	1640
65°	511
70°	171
75°	155
80°	107
85°	212



TEST NUMBER: P583772  
 CATALOG NUMBER: HCC8S10D010MW-HM80520927-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.8	5.7
10°-20°	158.1	16.7
20°-30°	276.4	29.2
30°-40°	268.9	28.4
40°-50°	122.3	12.9
50°-60°	56.7	6.0
60°-70°	9.5	1.0
70°-80°	1.2	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	488.3	51.6
0°-40°	757.1	79.9
0°-60°	936.1	98.8
0°-90°	947.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	576	
5°	568	54
15°	550	158
25°	610	276
35°	452	269
45°	150	122
55°	63	57
65°	7	9
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P583772  
CATALOG NUMBER: HCC8S10D010MW-HM80520927-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	575.5
2.5°	574.2
5°	568.5
7.5°	562.2
10°	554.6
12.5°	549.0
15°	550.2
17.5°	560.4
20°	578.0
22.5°	598.2
25°	609.7
27.5°	603.3
30°	575.5
32.5°	526.8
35°	451.6
37.5°	347.9
40°	248.6
42.5°	185.3
45°	149.9
47.5°	126.5
50°	105.7
52.5°	84.1
55°	62.6
57.5°	43.0
60°	26.6
62.5°	14.5
65°	7.0
67.5°	3.1
70°	1.9
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)