

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583784

Luminaire Tested: **HCC8S10D010MB-HM80520930-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583784  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S10D010MB-HM80520930-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 948.1 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583784  
CATALOG NUMBER: HCC8S10D010MB-HM80520930-81NDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P583784

CATALOG NUMBER: HCC8S10D010MB-HM80520930-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95																																				
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																																				
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84																																				
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80																																				
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75																																				
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72																																				
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68																																				
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65																																				
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62																																				
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75444
5°	63917
10°	46376
15°	34826
20°	27476
25°	22167
30°	16425
35°	6655
40°	2806
45°	1505
50°	676
55°	344
60°	216
65°	161
70°	126
75°	83
80°	124
85°	248



TEST NUMBER: P583784  
 CATALOG NUMBER: HCC8S10D010MB-HM80520930-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	177.3	18.7
10°-20°	306.4	32.3
20°-30°	296.3	31.2
30°-40°	130.1	13.7
40°-50°	28.1	3.0
50°-60°	6.3	0.7
60°-70°	2.2	0.2
70°-80°	0.8	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	779.9	82.3
0°-40°	910.0	96.0
0°-60°	944.5	99.6
0°-90°	948.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2447	
5°	2065	177
15°	1091	306
25°	652	296
35°	177	130
45°	34	28
55°	6	6
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P583784

CATALOG NUMBER: HCC8S10D010MB-HM80520930-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2446.6
1°	2428.3
2°	2378.3
3°	2288.1
4°	2180.3
5°	2064.9
6°	1938.8
7°	1812.0
8°	1693.0
9°	1582.4
10°	1481.1
11°	1385.3
12°	1299.4
13°	1221.2
14°	1152.1
15°	1090.9
17.5°	953.5
20°	837.3
22.5°	735.3
25°	651.5
27.5°	566.3
30°	461.3
32.5°	313.4
35°	176.8
37.5°	104.2
40°	69.7
42.5°	49.3
45°	34.5
47.5°	22.5
50°	14.1
52.5°	8.4
55°	6.4
57.5°	4.9
60°	3.5
62.5°	2.8
65°	2.2
67.5°	1.4
70°	1.4
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P583784  
CATALOG NUMBER: HCC8S10D010MB-HM80520930-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°		0.7
87.5°		0.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)