

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593600

Luminaire Tested: **HCC8S20D010MB-HM80520850-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520850-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2291.5 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593600
CATALOG NUMBER: HCC8S20D010MB-HM80520850-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P593600

CATALOG NUMBER: HCC8S20D010MB-HM80520850-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			87
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75			75
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65			65
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50			50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45			45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40			40
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33			33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35132	35132	35132
5°	36421	35018	33814
10°	37452	34712	32433
15°	38287	34101	30998
20°	38345	32769	29744
25°	37610	30945	28689
30°	35674	28699	27431
35°	32412	26136	26200
40°	28339	23452	24688
45°	24561	20893	23008
50°	21506	18556	20964
55°	19139	16446	18967
60°	17268	14771	16670
65°	15585	12988	14520
70°	14002	10945	10792
75°	12331	8674	8102
80°	10353	7174	7760
85°	8031	6298	6864



TEST NUMBER: P593600

CATALOG NUMBER: HCC8S20D010MB-HM80520850-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	4.7
10°-20°	302.7	13.2
20°-30°	432.7	18.9
30°-40°	459.7	20.1
40°-50°	395.8	17.3
50°-60°	295.9	12.9
60°-70°	188.8	8.2
70°-80°	85.9	3.7
80°-90°	22.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	842.9	36.8
0°-40°	1302.6	56.8
0°-60°	1994.4	87.0
0°-90°	2291.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2291.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1139	1139	1139	1139	1139	
5°	1177	1160	1131	1102	1092	113
15°	1199	1159	1068	995	971	338
25°	1105	1036	910	855	843	506
35°	861	801	694	676	696	536
45°	563	532	479	492	528	438
55°	356	327	306	332	353	320
65°	214	189	178	186	199	213
75°	104	89	73	66	68	110
85°	23	19	18	19	19	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593600

CATALOG NUMBER: HCC8S20D010MB-HM80520850-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3
2.5°	1160.4	1157.2	1158.8	1157.2	1158.8	1158.8	1155.5	1155.5	1155.5	1155.5	1150.7
5°	1176.6	1175.0	1175.0	1173.4	1171.7	1173.4	1171.7	1170.2	1166.9	1165.3	1160.4
7.5°	1186.4	1186.4	1186.4	1186.4	1184.7	1183.1	1181.4	1178.2	1175.0	1171.7	1168.5
10°	1196.1	1197.6	1196.1	1194.4	1192.8	1189.6	1187.9	1184.7	1179.9	1175.0	1171.7
12.5°	1200.9	1200.9	1199.3	1199.3	1196.1	1194.4	1189.6	1184.7	1179.9	1175.0	1166.9
15°	1199.3	1199.3	1197.6	1196.1	1191.2	1189.6	1186.4	1181.4	1173.4	1166.9	1158.8
17.5°	1189.6	1187.9	1184.7	1184.7	1178.2	1176.6	1173.4	1166.9	1158.8	1149.1	1139.3
20°	1168.5	1168.5	1166.9	1165.3	1158.8	1154.0	1150.7	1142.6	1136.1	1124.8	1115.1
22.5°	1139.3	1142.6	1139.3	1136.1	1128.1	1126.4	1121.6	1111.9	1102.2	1089.2	1077.9
25°	1105.4	1103.8	1102.2	1098.9	1092.4	1089.2	1082.7	1073.0	1063.3	1048.8	1035.8
27.5°	1061.7	1055.2	1055.2	1048.8	1043.9	1039.1	1035.8	1026.1	1013.1	1001.9	985.7
30°	1001.9	1003.4	995.4	993.7	985.7	982.4	976.0	966.2	954.9	941.9	928.9
32.5°	937.1	932.2	932.2	925.7	919.2	914.4	912.9	901.5	891.8	878.8	865.8
35°	861.0	861.0	856.1	854.6	848.1	844.8	839.9	833.5	822.2	810.9	801.2
37.5°	786.5	783.3	781.7	778.5	773.6	768.8	768.8	757.4	755.8	742.9	729.9
40°	704.0	707.3	704.0	699.2	697.5	694.3	692.7	686.3	681.3	670.1	661.9
42.5°	634.4	631.2	631.2	629.5	623.2	623.2	619.8	616.6	608.5	605.3	595.6
45°	563.2	566.4	561.6	563.2	556.7	556.7	556.7	550.2	543.8	539.0	532.5
47.5°	501.8	503.3	503.3	498.4	496.9	496.9	493.6	490.4	485.6	479.1	474.2
50°	448.3	449.9	446.7	445.0	441.8	440.2	440.2	433.8	430.5	424.0	420.8
52.5°	399.8	399.8	398.1	398.1	393.3	393.3	390.1	385.2	381.9	378.7	370.7
55°	356.0	356.0	354.5	352.8	352.8	348.0	346.3	341.5	338.3	331.8	326.9
57.5°	313.9	315.6	313.9	312.4	310.7	309.1	305.9	301.1	297.7	292.9	289.7
60°	280.0	280.0	278.4	276.7	273.5	271.9	270.3	267.0	262.2	259.0	254.1
62.5°	247.6	246.0	244.4	242.8	239.5	239.5	236.3	233.1	228.2	224.9	221.7
65°	213.6	213.6	212.1	212.1	210.4	207.2	205.5	203.9	197.4	195.9	189.4
67.5°	182.9	184.5	181.3	181.3	178.0	178.0	176.4	171.5	170.0	166.7	163.5
70°	155.3	155.3	155.3	153.8	150.5	148.9	147.3	144.1	142.4	139.2	135.9
72.5°	127.9	127.9	126.2	126.2	124.6	123.0	121.4	118.2	118.2	114.9	111.7
75°	103.5	103.5	102.0	100.4	98.7	98.7	97.2	95.5	92.2	90.7	89.0
77.5°	79.3	79.3	79.3	77.7	76.1	76.1	76.1	72.8	69.6	69.6	68.0
80°	58.3	58.3	56.6	56.6	55.1	55.1	55.1	53.4	51.8	50.1	48.6
82.5°	38.9	38.9	38.9	38.9	37.2	37.2	37.2	35.6	34.0	34.0	34.0
85°	22.7	22.7	22.7	22.7	21.0	21.0	21.0	21.0	21.0	19.4	19.4
87.5°	9.7	8.0	9.7	8.0	9.7	8.0	9.7	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593600

CATALOG NUMBER: HCC8S20D010MB-HM80520850-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3
2.5°	1152.3	1150.7	1149.1	1147.5	1147.5	1145.8	1142.6	1141.0	1139.3	1137.8	1137.8
5°	1158.8	1157.2	1154.0	1150.7	1149.1	1145.8	1142.6	1139.3	1136.1	1131.3	1129.6
7.5°	1163.7	1158.8	1155.5	1149.1	1147.5	1144.3	1139.3	1134.5	1128.1	1121.6	1116.8
10°	1163.7	1157.2	1152.3	1144.3	1141.0	1137.8	1131.3	1123.3	1115.1	1108.6	1100.6
12.5°	1160.4	1152.3	1144.3	1136.1	1131.3	1126.4	1116.8	1108.6	1098.9	1089.2	1082.7
15°	1149.1	1139.3	1129.6	1119.9	1115.1	1108.6	1098.9	1087.6	1077.9	1068.2	1056.8
17.5°	1128.1	1118.3	1107.1	1095.7	1089.2	1084.4	1069.8	1061.7	1047.1	1037.4	1027.7
20°	1100.6	1089.2	1074.7	1063.3	1055.2	1050.3	1039.1	1024.4	1013.1	998.6	988.9
22.5°	1065.0	1050.3	1035.8	1024.4	1016.4	1009.9	995.4	980.8	971.0	958.1	946.8
25°	1022.9	1008.2	993.7	977.5	969.5	963.0	950.0	937.1	924.1	909.5	899.9
27.5°	972.7	956.5	943.6	928.9	920.9	911.2	896.7	883.7	870.8	861.0	848.1
30°	917.7	899.9	886.9	872.3	864.3	856.1	841.6	828.6	817.4	806.0	799.5
32.5°	851.3	838.4	825.4	810.9	804.4	799.5	785.0	772.0	759.1	749.4	744.4
35°	788.2	773.6	762.3	749.4	741.2	736.4	723.4	712.2	705.7	694.3	687.8
37.5°	721.8	710.5	697.5	684.6	679.8	674.9	665.2	653.9	644.2	636.0	632.8
40°	652.2	642.5	631.2	623.2	618.2	613.3	605.3	597.1	590.8	582.6	579.4
42.5°	585.9	579.4	569.7	560.0	555.1	553.5	543.8	537.3	534.0	530.8	527.6
45°	526.0	516.3	509.8	503.3	498.4	495.3	490.4	485.6	482.3	479.1	475.9
47.5°	467.7	459.7	453.2	448.3	443.5	441.8	438.6	433.8	430.5	430.5	430.5
50°	414.3	407.8	401.4	398.1	396.6	393.3	390.1	388.4	386.8	386.8	386.8
52.5°	367.4	360.9	356.0	352.8	352.8	349.6	346.3	344.7	344.7	344.7	344.7
55°	323.6	318.8	315.6	312.4	309.1	307.6	307.6	307.6	305.9	305.9	307.6
57.5°	284.9	281.6	276.7	273.5	271.9	271.9	270.3	268.7	270.3	271.9	273.5
60°	249.3	246.0	244.4	239.5	239.5	239.5	237.9	237.9	237.9	239.5	241.1
62.5°	216.9	215.2	212.1	210.4	208.7	208.7	207.2	207.2	207.2	207.2	208.7
65°	187.7	184.5	181.3	181.3	181.3	179.7	179.7	176.4	178.0	178.0	176.4
67.5°	160.3	157.0	155.3	153.8	152.1	152.1	150.5	148.9	147.3	147.3	147.3
70°	134.3	131.1	131.1	127.9	127.9	126.2	124.6	124.6	123.0	121.4	119.7
72.5°	108.4	106.9	105.2	103.5	103.5	103.5	102.0	100.4	98.7	97.2	93.9
75°	85.8	85.8	82.5	81.0	81.0	79.3	77.7	76.1	74.5	72.8	71.2
77.5°	66.3	64.8	61.5	59.9	59.9	59.9	58.3	56.6	55.1	53.4	51.8
80°	48.6	46.9	45.3	43.7	43.7	43.7	42.1	42.1	40.4	40.4	40.4
82.5°	32.4	32.4	30.7	30.7	30.7	30.7	29.1	29.1	29.1	29.1	29.1
85°	19.4	19.4	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593600

CATALOG NUMBER: HCC8S20D010MB-HM80520850-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3
2.5°	1134.5	1134.5	1131.3	1129.6	1128.1	1129.6	1126.4	1124.8	1123.3	1123.3	1121.6
5°	1124.8	1123.3	1116.8	1115.1	1113.4	1111.9	1108.6	1105.4	1102.2	1100.6	1098.9
7.5°	1111.9	1107.1	1100.6	1098.9	1097.3	1092.4	1087.6	1084.4	1079.5	1077.9	1074.7
10°	1094.1	1087.6	1082.7	1077.9	1074.7	1069.8	1065.0	1060.1	1053.6	1052.0	1047.1
12.5°	1073.0	1065.0	1055.2	1053.6	1048.8	1042.3	1035.8	1030.9	1026.1	1022.9	1018.1
15°	1047.1	1039.1	1029.3	1024.4	1019.6	1014.7	1006.7	1000.2	995.4	990.5	985.7
17.5°	1016.4	1006.7	998.6	993.7	990.5	982.4	976.0	967.8	963.0	958.1	953.3
20°	979.2	971.0	959.8	954.9	953.3	946.8	938.7	935.4	928.9	924.1	920.9
22.5°	937.1	928.9	919.2	916.0	909.5	906.4	898.2	895.0	891.8	886.9	885.3
25°	890.2	882.0	874.0	872.3	867.5	864.3	859.4	854.6	854.6	849.7	849.7
27.5°	841.6	833.5	827.0	823.7	822.2	818.9	814.0	812.5	810.9	809.2	809.2
30°	789.8	780.1	776.8	775.3	773.6	770.4	768.8	765.5	767.1	768.8	767.1
32.5°	734.7	731.5	725.0	721.8	723.4	721.8	718.5	721.8	720.2	723.4	725.0
35°	681.3	678.1	674.9	674.9	671.6	671.6	671.6	673.3	676.5	678.1	681.3
37.5°	629.5	624.7	623.2	621.5	623.2	623.2	623.2	626.3	629.5	632.8	637.7
40°	574.6	571.3	571.3	571.3	571.3	576.1	574.6	577.8	581.1	585.9	590.8
42.5°	522.8	522.8	524.3	524.3	524.3	524.3	527.6	532.5	537.3	542.2	547.0
45°	474.2	474.2	474.2	477.4	477.4	479.1	485.6	488.8	491.9	496.9	501.8
47.5°	428.8	428.8	430.5	432.1	433.8	437.0	440.2	445.0	449.9	453.2	458.0
50°	386.8	388.4	391.7	394.9	394.9	396.6	401.4	404.6	407.8	412.8	414.3
52.5°	346.3	349.6	352.8	354.5	356.0	359.3	360.9	365.7	367.4	372.2	373.9
55°	309.1	310.7	315.6	317.2	317.2	320.4	323.6	326.9	331.8	331.8	335.0
57.5°	275.2	276.7	280.0	281.6	280.0	284.9	286.5	289.7	291.4	294.6	296.2
60°	241.1	244.4	246.0	246.0	247.6	249.3	252.5	252.5	255.7	259.0	259.0
62.5°	208.7	210.4	212.1	213.6	215.2	213.6	218.4	218.4	221.7	223.4	226.6
65°	178.0	179.7	179.7	181.3	181.3	182.9	182.9	184.5	186.2	189.4	191.0
67.5°	147.3	147.3	147.3	148.9	147.3	148.9	148.9	150.5	150.5	153.8	155.3
70°	119.7	118.2	116.5	116.5	116.5	116.5	114.9	116.5	116.5	118.2	118.2
72.5°	92.2	90.7	89.0	87.3	87.3	85.8	84.2	85.8	85.8	87.3	87.3
75°	69.6	66.3	66.3	66.3	64.8	64.8	64.8	66.3	66.3	66.3	68.0
77.5°	51.8	51.8	50.1	50.1	50.1	51.8	51.8	53.4	53.4	53.4	53.4
80°	38.9	40.4	40.4	40.4	40.4	42.1	42.1	42.1	42.1	43.7	43.7
82.5°	29.1	29.1	29.1	29.1	30.7	30.7	30.7	30.7	30.7	30.7	30.7
85°	17.8	19.4	19.4	17.8	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593600

CATALOG NUMBER: HCC8S20D010MB-HM80520850-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3	1139.3
2.5°	1119.9	1119.9	1119.9	1119.9	1118.3	1118.3	1118.3	1116.8
5°	1095.7	1095.7	1095.7	1092.4	1094.1	1094.1	1090.9	1092.4
7.5°	1071.4	1069.8	1068.2	1068.2	1066.5	1065.0	1063.3	1065.0
10°	1043.9	1039.1	1039.1	1037.4	1037.4	1034.1	1034.1	1035.8
12.5°	1013.1	1009.9	1009.9	1008.2	1006.7	1005.1	1003.4	1003.4
15°	982.4	979.2	977.5	976.0	974.3	971.0	972.7	971.0
17.5°	951.6	946.8	946.8	945.1	943.6	940.3	940.3	938.7
20°	916.0	914.4	911.2	912.9	911.2	907.9	906.4	906.4
22.5°	880.5	880.5	878.8	878.8	877.2	875.6	874.0	874.0
25°	846.4	844.8	846.4	846.4	841.6	841.6	841.6	843.2
27.5°	807.5	809.2	807.5	807.5	807.5	807.5	809.2	807.5
30°	768.8	768.8	768.8	770.4	773.6	772.0	772.0	770.4
32.5°	726.7	728.3	728.3	729.9	731.5	734.7	734.7	736.4
35°	684.6	687.8	689.5	687.8	692.7	692.7	696.0	696.0
37.5°	640.9	642.5	645.7	647.4	650.6	652.2	653.9	653.9
40°	594.0	600.5	602.1	603.6	608.5	608.5	610.1	613.3
42.5°	550.2	556.7	558.4	560.0	563.2	568.1	566.4	569.7
45°	508.1	513.0	514.6	516.3	521.1	522.8	522.8	527.6
47.5°	462.9	466.1	467.7	470.9	474.2	477.4	480.7	479.1
50°	417.6	422.4	425.6	427.3	432.1	433.8	435.3	437.0
52.5°	377.1	380.4	381.9	383.6	388.4	390.1	391.7	394.9
55°	338.3	339.8	343.1	341.5	346.3	348.0	349.6	352.8
57.5°	299.4	301.1	302.6	302.6	305.9	309.1	310.7	312.4
60°	262.2	265.5	267.0	267.0	267.0	270.3	270.3	270.3
62.5°	228.2	228.2	229.8	229.8	233.1	233.1	233.1	233.1
65°	192.5	194.2	195.9	195.9	199.0	197.4	200.7	199.0
67.5°	155.3	155.3	158.6	158.6	157.0	158.6	158.6	158.6
70°	118.2	118.2	119.7	119.7	119.7	119.7	119.7	119.7
72.5°	87.3	87.3	87.3	89.0	87.3	87.3	89.0	87.3
75°	68.0	68.0	68.0	68.0	68.0	68.0	68.0	68.0
77.5°	53.4	53.4	55.1	55.1	55.1	55.1	55.1	55.1
80°	43.7	43.7	43.7	43.7	45.3	43.7	43.7	43.7
82.5°	32.4	30.7	32.4	30.7	32.4	32.4	32.4	32.4
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)