

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593596

Luminaire Tested: **HCC8S20D010MW-HM80520850-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MW-HM80520850-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2304.5 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593596
CATALOG NUMBER: HCC8S20D010MW-HM80520850-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P593596

CATALOG NUMBER: HCC8S20D010MW-HM80520850-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	37389	37389	37389
5°	37882	37232	36882
10°	38273	36851	36294
15°	38660	36074	35350
20°	38463	34742	33947
25°	37566	32663	32221
30°	35681	30319	30205
35°	32483	27668	27913
40°	28476	24764	25674
45°	24565	22027	23584
50°	21516	19338	21353
55°	19058	16623	18795
60°	17176	13975	15579
65°	15476	11222	11930
70°	13578	8177	6564
75°	11581	4241	1728
80°	8914	1154	302
85°	5732	0	0



TEST NUMBER: P593596
 CATALOG NUMBER: HCC8S20D010MW-HM80520850-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	5.0
10°-20°	321.6	14.0
20°-30°	456.5	19.8
30°-40°	480.5	20.9
40°-50°	408.8	17.7
50°-60°	295.4	12.8
60°-70°	168.0	7.3
70°-80°	52.9	2.3
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	892.5	38.7
0°-40°	1373.0	59.6
0°-60°	2077.1	90.1
0°-90°	2304.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2304.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1212	1212	1212	1212	1212	
5°	1224	1218	1203	1195	1192	117
15°	1211	1180	1130	1109	1107	341
25°	1104	1049	960	944	947	506
35°	863	813	735	730	742	537
45°	563	542	505	518	541	438
55°	354	329	309	327	350	320
65°	212	183	154	152	164	210
75°	97	74	36	16	14	105
85°	16	10	0	0	0	21
90°	0	0	0	0	0	



TEST NUMBER: P593596

CATALOG NUMBER: HCC8S20D010MW-HM80520850-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5
2.5°	1219.0	1220.7	1217.5	1217.5	1220.7	1217.5	1219.0	1219.0	1217.5	1217.5	1215.8
5°	1223.8	1222.3	1222.3	1222.3	1223.8	1220.7	1219.0	1220.7	1217.5	1217.5	1217.5
7.5°	1225.5	1225.5	1223.8	1222.3	1222.3	1222.3	1220.7	1219.0	1217.5	1214.2	1212.5
10°	1222.3	1222.3	1223.8	1220.7	1220.7	1217.5	1217.5	1214.2	1214.2	1211.0	1206.1
12.5°	1219.0	1217.5	1217.5	1214.2	1214.2	1211.0	1211.0	1206.1	1204.5	1199.6	1194.8
15°	1211.0	1209.3	1206.1	1204.5	1202.8	1201.3	1198.0	1196.3	1191.5	1185.1	1180.2
17.5°	1194.8	1193.1	1191.5	1188.3	1185.1	1183.4	1181.8	1176.9	1170.4	1165.6	1157.5
20°	1172.1	1170.4	1170.4	1165.6	1164.0	1159.1	1157.5	1151.0	1146.2	1136.5	1130.0
22.5°	1141.3	1143.0	1139.7	1136.5	1133.2	1128.3	1125.1	1118.6	1110.6	1100.8	1092.8
25°	1104.1	1105.6	1102.5	1099.3	1094.4	1091.1	1087.9	1078.2	1070.1	1058.7	1049.0
27.5°	1057.2	1057.2	1057.2	1053.9	1045.8	1044.2	1041.0	1031.2	1019.9	1010.1	1000.4
30°	1002.1	1000.4	1000.4	995.6	992.4	985.9	981.1	972.9	964.9	953.5	942.2
32.5°	935.7	937.3	932.5	929.3	924.4	924.4	917.9	911.4	901.7	890.4	879.1
35°	862.9	864.5	861.2	859.7	851.5	849.9	848.3	840.2	833.8	825.6	812.6
37.5°	788.4	786.7	785.2	785.2	780.4	777.0	773.9	769.0	759.3	752.8	746.3
40°	707.4	707.4	707.4	705.9	704.2	700.9	699.4	696.1	689.7	683.2	678.3
42.5°	634.6	634.6	633.0	631.4	628.1	629.8	626.5	623.3	616.8	611.9	608.7
45°	563.3	563.3	563.3	565.0	561.8	556.8	556.8	553.6	550.5	547.1	542.3
47.5°	500.2	505.1	501.9	500.2	501.9	495.4	495.4	492.2	488.9	485.7	479.2
50°	448.5	448.5	448.5	445.1	443.6	443.6	438.8	435.4	433.9	430.6	424.1
52.5°	401.5	398.2	398.2	396.7	395.0	391.7	391.7	388.5	382.0	378.8	374.0
55°	354.5	354.5	352.9	351.3	349.6	348.1	346.4	341.6	338.4	333.4	328.6
57.5°	312.4	315.7	314.1	310.9	307.6	307.6	304.4	301.1	296.2	291.4	286.5
60°	278.5	276.8	276.8	275.2	272.0	270.3	268.8	263.8	259.0	254.1	249.3
62.5°	242.8	242.8	242.8	239.6	236.4	234.7	233.1	229.9	223.4	218.6	215.4
65°	212.1	210.5	208.9	207.2	205.5	202.4	200.7	197.5	192.7	187.8	183.0
67.5°	181.3	179.7	179.7	178.1	173.2	171.6	171.6	166.8	161.9	157.1	152.1
70°	150.6	150.6	150.6	147.3	145.7	144.1	142.4	139.2	134.4	129.5	124.7
72.5°	124.7	123.0	123.0	121.4	116.5	114.9	113.4	110.0	105.2	102.0	98.7
75°	97.2	97.2	95.5	93.9	92.3	90.7	89.0	85.8	81.0	76.1	74.5
77.5°	74.5	72.8	72.8	71.3	68.0	66.4	66.4	63.1	58.3	55.1	51.8
80°	50.2	51.8	50.2	48.6	46.9	45.3	43.7	42.1	38.9	35.6	32.4
82.5°	30.7	32.4	30.7	30.7	29.2	27.5	27.5	24.2	22.7	21.0	19.4
85°	16.2	16.2	16.2	16.2	14.5	14.5	14.5	13.0	11.3	9.7	9.7
87.5°	4.8	6.5	4.8	4.8	4.8	4.8	4.8	4.8	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593596

CATALOG NUMBER: HCC8S20D010MW-HM80520850-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5
2.5°	1217.5	1215.8	1214.2	1214.2	1214.2	1214.2	1214.2	1212.5	1211.0	1211.0	1211.0
5°	1214.2	1214.2	1214.2	1212.5	1211.0	1211.0	1207.6	1206.1	1204.5	1202.8	1201.3
7.5°	1211.0	1207.6	1206.1	1204.5	1202.8	1202.8	1199.6	1196.3	1196.3	1193.1	1189.9
10°	1201.3	1199.6	1196.3	1193.1	1191.5	1189.9	1186.6	1181.8	1180.2	1176.9	1173.7
12.5°	1189.9	1186.6	1183.4	1176.9	1175.3	1173.7	1167.2	1162.4	1159.1	1157.5	1149.4
15°	1175.3	1168.9	1164.0	1155.9	1154.2	1151.0	1146.2	1141.3	1134.8	1130.0	1126.8
17.5°	1149.4	1143.0	1134.8	1126.8	1123.5	1123.5	1115.5	1109.0	1100.8	1097.6	1091.1
20°	1118.6	1110.6	1104.1	1094.4	1089.6	1084.6	1079.8	1070.1	1063.6	1058.7	1050.7
22.5°	1083.1	1071.7	1063.6	1053.9	1045.8	1041.0	1032.8	1024.8	1016.6	1011.8	1005.3
25°	1037.7	1028.0	1015.1	1005.3	1000.4	993.9	984.3	976.2	968.1	960.0	956.7
27.5°	987.6	974.6	963.2	951.9	947.0	942.2	930.8	921.1	914.6	906.6	903.3
30°	932.5	919.5	906.6	896.9	892.1	883.9	877.4	866.1	858.0	851.5	843.5
32.5°	869.4	859.7	848.3	833.8	830.5	824.0	814.3	809.4	799.7	794.9	788.4
35°	801.4	794.9	783.5	772.2	767.4	764.2	756.0	746.3	739.8	735.0	731.8
37.5°	736.6	728.5	717.1	709.1	705.9	700.9	691.2	686.4	679.9	676.7	670.2
40°	667.0	658.8	650.8	646.0	641.1	637.8	631.4	626.5	620.1	615.2	613.6
42.5°	599.0	594.1	587.7	581.2	579.5	574.7	571.5	566.7	561.8	560.1	555.3
45°	537.5	532.6	526.1	519.6	518.1	514.8	513.2	508.4	505.1	505.1	505.1
47.5°	476.0	471.1	464.6	461.3	463.0	456.5	456.5	455.0	451.6	451.6	453.3
50°	420.9	414.4	412.9	409.6	406.4	403.1	404.7	399.9	399.9	403.1	401.5
52.5°	369.1	362.6	361.0	357.8	356.1	356.1	354.5	354.5	352.9	354.5	354.5
55°	322.2	317.2	314.1	310.9	309.2	309.2	309.2	307.6	306.0	309.2	310.9
57.5°	280.0	278.5	275.2	270.3	268.8	267.1	265.5	265.5	265.5	265.5	267.1
60°	242.8	239.6	236.4	231.6	231.6	229.9	228.2	226.6	226.6	226.6	226.6
62.5°	210.5	205.5	200.7	197.5	195.9	194.3	192.7	189.4	189.4	189.4	189.4
65°	178.1	173.2	170.0	166.8	163.5	163.5	160.3	158.6	155.4	153.8	150.6
67.5°	147.3	144.1	140.9	135.9	134.4	132.7	129.5	127.9	123.0	121.4	119.9
70°	119.9	114.9	111.7	108.5	106.9	103.7	100.4	97.2	93.9	90.7	87.5
72.5°	93.9	89.0	85.8	82.6	79.3	79.3	74.5	71.3	66.4	63.1	58.3
75°	69.6	64.8	61.5	56.6	55.1	53.4	48.6	45.3	40.4	35.6	32.4
77.5°	46.9	43.7	40.4	35.6	32.4	32.4	27.5	24.2	21.0	16.2	14.5
80°	29.2	25.9	22.7	19.4	19.4	16.2	14.5	11.3	8.0	6.5	4.8
82.5°	16.2	14.5	13.0	9.7	9.7	8.0	6.5	4.8	3.2	1.7	1.7
85°	8.0	6.5	4.8	4.8	3.2	3.2	3.2	1.7	1.7	0.0	0.0
87.5°	3.2	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593596

CATALOG NUMBER: HCC8S20D010MW-HM80520850-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5
2.5°	1209.3	1209.3	1207.6	1207.6	1207.6	1206.1	1207.6	1206.1	1206.1	1206.1	1207.6
5°	1202.8	1199.6	1199.6	1198.0	1198.0	1196.3	1198.0	1196.3	1194.8	1193.1	1194.8
7.5°	1189.9	1186.6	1185.1	1183.4	1183.4	1183.4	1181.8	1180.2	1181.8	1176.9	1180.2
10°	1172.1	1170.4	1167.2	1165.6	1164.0	1165.6	1164.0	1160.7	1160.7	1160.7	1159.1
12.5°	1149.4	1146.2	1144.5	1143.0	1139.7	1139.7	1141.3	1138.0	1138.0	1134.8	1134.8
15°	1121.8	1118.6	1115.5	1115.5	1112.1	1112.1	1110.6	1110.6	1109.0	1107.3	1107.3
17.5°	1087.9	1083.1	1079.8	1081.4	1079.8	1078.2	1078.2	1074.9	1073.4	1074.9	1074.9
20°	1047.4	1044.2	1041.0	1042.5	1039.3	1037.7	1039.3	1034.5	1036.1	1036.1	1036.1
22.5°	1002.1	1000.4	995.6	995.6	992.4	990.8	992.4	992.4	993.9	992.4	992.4
25°	951.9	948.7	945.5	945.5	943.8	942.2	943.8	945.5	943.8	945.5	945.5
27.5°	898.4	893.6	893.6	890.4	890.4	892.1	890.4	892.1	893.6	893.6	896.9
30°	840.2	838.6	837.0	835.3	835.3	837.0	837.0	837.0	838.6	841.8	841.8
32.5°	785.2	781.9	778.7	778.7	781.9	780.4	781.9	781.9	785.2	785.2	788.4
35°	725.3	725.3	722.0	723.6	723.6	723.6	723.6	726.9	730.1	731.8	735.0
37.5°	670.2	665.3	667.0	667.0	668.7	667.0	671.8	671.8	675.0	675.0	678.3
40°	610.3	610.3	611.9	610.3	611.9	611.9	615.2	618.4	620.1	623.3	624.9
42.5°	553.6	556.8	553.6	555.3	556.8	558.5	560.1	561.8	568.2	571.5	576.3
45°	501.9	503.5	505.1	506.7	505.1	508.4	509.9	513.2	518.1	519.6	521.3
47.5°	451.6	453.3	455.0	456.5	456.5	459.8	461.3	464.6	467.8	469.5	471.1
50°	403.1	406.4	407.9	407.9	409.6	412.9	416.1	416.1	419.3	424.1	425.8
52.5°	359.4	359.4	362.6	364.3	365.8	365.8	370.7	372.3	374.0	377.2	380.5
55°	310.9	315.7	317.2	317.2	320.6	323.7	325.4	327.1	327.1	333.4	333.4
57.5°	268.8	270.3	273.6	273.6	273.6	278.5	278.5	281.7	283.3	285.0	288.2
60°	226.6	229.9	229.9	231.6	229.9	233.1	234.7	237.9	239.6	241.2	242.8
62.5°	187.8	187.8	189.4	189.4	189.4	189.4	192.7	192.7	195.9	197.5	199.2
65°	150.6	150.6	150.6	150.6	150.6	150.6	150.6	150.6	152.1	152.1	155.4
67.5°	116.5	114.9	111.7	113.4	111.7	111.7	110.0	110.0	111.7	111.7	114.9
70°	84.2	82.6	79.3	79.3	77.7	76.1	74.5	72.8	71.3	71.3	71.3
72.5°	55.1	51.8	46.9	45.3	45.3	42.1	38.9	37.2	37.2	37.2	37.2
75°	27.5	24.2	21.0	19.4	19.4	16.2	17.8	16.2	16.2	16.2	16.2
77.5°	11.3	8.0	6.5	6.5	6.5	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.2	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593596

CATALOG NUMBER: HCC8S20D010MW-HM80520850-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5	1212.5
2.5°	1206.1	1206.1	1202.8	1204.5	1204.5	1204.5	1204.5	1204.5
5°	1191.5	1193.1	1191.5	1193.1	1193.1	1191.5	1191.5	1191.5
7.5°	1176.9	1178.6	1176.9	1178.6	1178.6	1178.6	1176.9	1176.9
10°	1159.1	1159.1	1159.1	1159.1	1159.1	1157.5	1159.1	1159.1
12.5°	1134.8	1134.8	1134.8	1136.5	1136.5	1134.8	1134.8	1133.2
15°	1109.0	1105.6	1107.3	1109.0	1107.3	1107.3	1107.3	1107.3
17.5°	1073.4	1074.9	1073.4	1073.4	1073.4	1073.4	1074.9	1073.4
20°	1036.1	1036.1	1037.7	1036.1	1036.1	1036.1	1036.1	1034.5
22.5°	993.9	992.4	992.4	993.9	993.9	992.4	993.9	993.9
25°	947.0	948.7	947.0	947.0	948.7	948.7	948.7	947.0
27.5°	896.9	898.4	900.1	898.4	898.4	898.4	900.1	901.7
30°	845.0	848.3	845.0	845.0	848.3	846.7	848.3	848.3
32.5°	790.0	794.9	791.6	794.9	794.9	796.5	794.9	796.5
35°	735.0	739.8	739.8	739.8	741.5	743.1	743.1	741.5
37.5°	683.2	684.7	684.7	688.0	689.7	691.2	691.2	689.7
40°	629.8	633.0	634.6	634.6	634.6	637.8	641.1	637.8
42.5°	578.0	579.5	581.2	581.2	584.4	586.0	587.7	587.7
45°	527.8	531.0	532.6	534.3	535.8	539.1	537.5	540.8
47.5°	476.0	480.8	482.4	484.0	487.3	488.9	490.5	492.2
50°	428.9	432.3	432.3	435.4	440.3	440.3	443.6	445.1
52.5°	382.0	383.7	385.3	386.9	390.2	393.4	393.4	396.7
55°	336.8	338.4	338.4	339.9	341.6	348.1	349.6	349.6
57.5°	289.8	289.8	293.0	294.7	296.2	299.5	299.5	299.5
60°	244.4	246.1	246.1	247.7	249.3	252.6	254.1	252.6
62.5°	199.2	200.7	200.7	202.4	205.5	207.2	205.5	205.5
65°	157.1	158.6	158.6	160.3	163.5	163.5	161.9	163.5
67.5°	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9
70°	72.8	71.3	69.6	71.3	71.3	71.3	69.6	72.8
72.5°	35.6	37.2	37.2	37.2	37.2	37.2	37.2	35.6
75°	16.2	16.2	14.5	14.5	14.5	16.2	16.2	14.5
77.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)