

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593598

Luminaire Tested: **HCC8W20D010MW-HM80520850-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593598  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W20D010MW-HM80520850-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2016.5 lumens  
Efficiency: N/A  
Efficacy: 100.8 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593598  
CATALOG NUMBER: HCC8W20D010MW-HM80520850-81WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P593598

CATALOG NUMBER: HCC8W20D010MW-HM80520850-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67					67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59					59			
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47					47			
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43					43			
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39					39			
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	33383	33383	33383
5°	34761	33310	31907
10°	35921	32884	30348
15°	36834	32132	28773
20°	36907	30797	27345
25°	36283	28852	25933
30°	34339	26620	24718
35°	31312	23938	23208
40°	27224	21105	21431
45°	23357	18277	19620
50°	19947	15759	17625
55°	17489	13575	15306
60°	15572	11576	12871
65°	13820	9442	10273
70°	12253	7005	5842
75°	10222	3658	1728
80°	8044	1154	302
85°	5732	601	0



TEST NUMBER: P593598  
 CATALOG NUMBER: HCC8W20D010MW-HM80520850-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.0	5.1
10°-20°	285.9	14.2
20°-30°	404.7	20.1
30°-40°	423.4	21.0
40°-50°	353.1	17.5
50°-60°	250.4	12.4
60°-70°	144.2	7.2
70°-80°	46.4	2.3
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	792.6	39.3
0°-40°	1215.9	60.3
0°-60°	1819.4	90.2
0°-90°	2016.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2016.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1083	1083	1083	1083	1083	
5°	1123	1108	1076	1044	1031	108
15°	1154	1107	1006	927	901	324
25°	1066	987	848	780	762	487
35°	832	759	636	602	616	516
45°	536	492	419	424	450	415
55°	325	291	252	265	285	294
65°	189	159	129	129	141	189
75°	86	63	31	14	14	93
85°	16	8	2	0	0	20
90°	0	0	0	0	0	



TEST NUMBER: P593598

CATALOG NUMBER: HCC8W20D010MW-HM80520850-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1105.2	1103.6	1102.0	1103.6	1102.0	1103.6	1102.0	1102.0	1100.3	1098.8	1098.8
5°	1123.0	1121.4	1121.4	1121.4	1119.8	1118.2	1118.2	1116.5	1113.3	1111.7	1108.5
7.5°	1134.4	1135.9	1135.9	1135.9	1132.7	1132.7	1129.5	1126.2	1123.0	1119.8	1114.9
10°	1147.2	1147.2	1145.7	1144.1	1140.7	1139.2	1137.6	1134.4	1129.5	1123.0	1118.2
12.5°	1152.1	1152.1	1150.6	1147.2	1145.7	1144.1	1142.4	1137.6	1131.1	1123.0	1116.5
15°	1153.8	1150.6	1148.9	1147.2	1144.1	1139.2	1139.2	1132.7	1124.7	1114.9	1106.8
17.5°	1140.7	1142.4	1139.2	1135.9	1131.1	1127.9	1123.0	1118.2	1108.5	1097.1	1089.0
20°	1124.7	1123.0	1121.4	1116.5	1110.0	1108.5	1103.6	1095.5	1087.4	1074.4	1063.1
22.5°	1098.8	1097.1	1093.8	1090.6	1084.1	1080.9	1076.1	1066.4	1055.1	1042.1	1029.2
25°	1066.4	1063.1	1058.2	1051.9	1046.9	1043.7	1037.2	1027.5	1014.6	1000.0	987.1
27.5°	1014.6	1019.5	1016.2	1006.5	1001.6	995.1	993.6	980.6	969.2	954.7	940.2
30°	964.4	964.4	959.5	954.7	946.7	941.8	935.3	925.6	914.3	896.4	885.1
32.5°	901.3	899.7	893.2	891.6	885.1	875.4	873.9	860.9	849.5	836.6	822.1
35°	831.8	828.5	822.1	817.1	813.9	809.1	804.2	792.9	781.5	768.7	759.0
37.5°	752.5	752.5	750.8	742.8	739.5	736.3	731.4	720.1	713.6	700.7	691.0
40°	676.3	674.8	670.0	668.3	665.1	660.3	657.0	650.5	640.8	631.1	621.4
42.5°	602.0	603.5	597.1	598.7	592.3	589.0	587.3	577.6	572.8	563.1	555.1
45°	535.6	534.0	530.7	529.2	525.9	522.7	519.5	514.5	506.5	496.8	491.9
47.5°	474.1	469.3	469.3	467.6	466.1	459.6	457.9	453.1	448.2	438.5	432.0
50°	415.8	415.8	415.8	414.3	409.4	407.8	404.6	399.6	394.8	388.4	378.6
52.5°	368.9	368.9	368.9	367.4	360.9	359.2	357.7	351.2	344.7	339.8	333.3
55°	325.3	326.8	325.3	322.0	317.1	317.1	312.3	309.1	302.6	297.7	291.2
57.5°	288.1	288.1	284.7	283.2	279.9	278.4	275.1	271.9	263.7	258.9	250.8
60°	252.5	250.8	250.8	247.6	244.3	241.1	239.5	234.6	231.4	223.3	216.8
62.5°	220.1	220.1	216.8	216.8	210.4	210.4	208.7	203.9	199.0	190.9	187.7
65°	189.4	189.4	187.7	186.0	181.2	179.7	178.0	173.2	168.3	163.5	158.6
67.5°	161.8	161.8	158.6	157.0	153.8	152.1	148.8	145.6	140.8	135.9	131.1
70°	135.9	134.3	132.7	131.1	127.9	126.2	122.9	119.7	114.9	111.7	106.9
72.5°	110.0	110.0	108.4	105.2	103.5	101.9	100.4	97.0	92.2	87.3	84.2
75°	85.8	85.8	85.8	82.5	79.3	77.7	77.7	74.5	71.2	66.3	63.1
77.5°	66.3	64.8	63.1	63.1	59.9	58.3	56.6	55.0	50.1	48.6	45.3
80°	45.3	46.9	45.3	43.7	42.1	40.4	40.4	37.2	35.6	32.4	29.1
82.5°	30.7	29.1	29.1	27.5	27.5	25.9	25.9	22.7	21.0	19.4	17.8
85°	16.2	16.2	14.5	14.5	14.5	13.0	13.0	11.3	11.3	9.7	8.0
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8W20D010MW-HM80520850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1097.1	1093.8	1092.3	1092.3	1090.6	1089.0	1087.4	1085.8	1082.6	1082.6	1079.3
5°	1105.2	1102.0	1100.3	1095.5	1092.3	1092.3	1085.8	1084.1	1079.3	1076.1	1072.9
7.5°	1111.7	1105.2	1100.3	1095.5	1092.3	1089.0	1082.6	1076.1	1069.6	1063.1	1059.9
10°	1111.7	1105.2	1097.1	1089.0	1085.8	1082.6	1074.4	1064.7	1056.7	1050.2	1042.1
12.5°	1108.5	1098.8	1089.0	1082.6	1076.1	1071.2	1061.6	1051.9	1042.1	1029.2	1022.7
15°	1098.8	1085.8	1076.1	1064.7	1059.9	1051.9	1043.7	1029.2	1017.8	1006.5	998.4
17.5°	1079.3	1063.1	1051.9	1040.5	1032.4	1027.5	1014.6	1001.6	988.7	975.7	966.0
20°	1050.2	1035.7	1022.7	1008.1	1001.6	995.1	978.9	966.0	953.0	938.5	928.8
22.5°	1014.6	1000.0	982.2	970.9	961.2	953.0	938.5	924.0	911.0	898.1	885.1
25°	970.9	956.4	940.2	922.3	915.9	907.8	891.6	877.0	862.5	848.0	836.6
27.5°	924.0	904.6	891.6	872.2	865.7	857.7	839.8	823.6	810.7	799.4	786.4
30°	867.4	852.8	835.0	817.1	810.7	802.6	788.0	773.5	760.5	747.6	734.6
32.5°	805.9	791.2	773.5	760.5	750.8	744.3	729.8	716.9	703.9	691.0	679.6
35°	741.1	724.9	712.0	699.0	691.0	682.8	668.3	657.0	647.3	635.9	624.6
37.5°	674.8	663.5	650.5	635.9	627.9	621.4	610.0	597.1	589.0	579.3	571.3
40°	610.0	597.1	585.8	572.8	566.4	561.4	550.2	540.4	532.4	524.3	519.5
42.5°	543.7	532.4	521.0	513.0	508.1	503.3	495.1	483.8	478.9	470.9	466.1
45°	482.3	472.4	464.4	453.1	449.9	446.6	436.9	428.8	424.0	419.1	415.8
47.5°	424.0	417.5	407.8	401.3	396.4	393.3	386.8	380.2	375.4	372.2	368.9
50°	373.7	365.7	359.2	352.7	349.5	344.7	338.2	335.0	331.7	328.5	328.5
52.5°	326.8	318.8	312.3	307.4	304.2	300.9	296.1	294.6	291.2	291.2	289.7
55°	283.2	278.4	271.9	265.4	263.7	262.2	258.9	255.7	254.0	252.5	254.0
57.5°	246.0	241.1	234.6	229.8	228.1	226.6	224.9	221.7	220.1	220.1	220.1
60°	211.9	207.1	202.2	197.4	197.4	194.2	192.5	190.9	189.4	187.7	187.7
62.5°	181.2	176.4	171.5	168.3	166.7	165.0	161.8	160.2	158.6	158.6	157.0
65°	153.8	147.3	145.6	140.8	139.1	137.6	135.9	132.7	131.1	129.4	127.9
67.5°	126.2	122.9	118.1	114.9	113.2	111.7	110.0	106.9	105.2	103.5	100.4
70°	101.9	98.7	95.5	92.2	90.7	89.0	85.8	82.5	81.0	77.7	72.8
72.5°	79.3	76.0	72.8	69.6	68.0	66.3	63.1	59.9	56.6	53.4	50.1
75°	59.9	56.6	51.8	48.6	46.9	46.9	42.1	38.9	35.6	30.7	27.5
77.5°	42.1	37.2	35.6	32.4	30.7	27.5	24.2	21.0	17.8	16.2	13.0
80°	27.5	24.2	21.0	19.4	17.8	16.2	14.5	11.3	8.0	6.5	4.8
82.5°	16.2	14.5	13.0	11.3	9.7	8.0	6.5	6.5	4.8	3.2	1.7
85°	8.0	6.5	4.8	4.8	3.2	3.2	3.2	1.7	1.7	1.7	1.7
87.5°	3.2	1.7	1.7	1.7	1.7	1.7	1.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8W20D010MW-HM80520850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1077.7	1076.1	1074.4	1072.9	1072.9	1069.6	1069.6	1067.9	1064.7	1063.1	1063.1
5°	1067.9	1063.1	1059.9	1058.2	1056.7	1051.9	1050.2	1046.9	1043.7	1040.5	1038.9
7.5°	1053.4	1045.4	1042.1	1040.5	1035.7	1030.8	1027.5	1022.7	1017.8	1013.0	1011.3
10°	1035.7	1027.5	1019.5	1016.2	1011.3	1008.1	1001.6	995.1	990.3	985.4	980.6
12.5°	1013.0	1003.3	995.1	991.9	987.1	980.6	970.9	967.7	959.5	956.4	949.9
15°	987.1	975.7	967.7	962.9	958.0	948.2	941.8	935.3	927.2	924.0	917.5
17.5°	954.7	941.8	933.7	928.8	925.6	917.5	907.8	899.7	891.6	888.4	883.5
20°	915.9	907.8	896.4	891.6	888.4	878.7	869.0	865.7	859.2	852.8	848.0
22.5°	872.2	864.0	852.8	848.0	846.3	838.2	830.1	825.3	820.4	815.6	810.7
25°	826.9	817.1	807.4	804.2	801.0	794.5	788.0	784.8	780.0	776.7	773.5
27.5°	778.3	768.7	760.5	755.7	752.5	747.6	744.3	741.1	737.9	734.6	733.1
30°	726.6	716.9	710.4	707.2	703.9	702.2	697.4	695.8	694.2	691.0	692.5
32.5°	674.8	666.6	660.3	655.3	655.3	652.1	650.5	650.5	648.9	648.9	648.9
35°	618.2	613.3	608.4	606.8	605.2	603.5	602.0	603.5	602.0	603.5	605.2
37.5°	566.4	561.4	558.3	556.6	555.1	556.6	555.1	555.1	556.6	559.9	561.4
40°	513.0	509.7	506.5	508.1	506.5	506.5	506.5	511.3	513.0	514.5	516.2
42.5°	462.8	459.6	457.9	457.9	459.6	457.9	461.2	462.8	466.1	470.9	474.1
45°	414.3	412.6	412.6	414.3	412.6	415.8	415.8	419.1	424.0	427.2	430.5
47.5°	368.9	368.9	368.9	370.6	370.6	372.2	375.4	377.1	380.2	383.6	386.8
50°	326.8	328.5	330.1	330.1	330.1	333.3	336.6	338.2	339.8	341.5	346.3
52.5°	289.7	291.2	291.2	292.9	294.6	296.1	297.7	300.9	302.6	305.8	307.4
55°	254.0	254.0	257.3	258.9	258.9	258.9	262.2	262.2	265.4	267.0	270.2
57.5°	220.1	221.7	221.7	223.3	223.3	224.9	226.6	228.1	229.8	231.4	233.0
60°	187.7	187.7	187.7	189.4	190.9	192.5	190.9	194.2	194.2	197.4	199.0
62.5°	157.0	158.6	158.6	158.6	158.6	158.6	158.6	160.2	161.8	163.5	165.0
65°	127.9	127.9	127.9	126.2	127.9	126.2	127.9	129.4	129.4	131.1	132.7
67.5°	98.7	98.7	95.5	95.5	97.0	97.0	97.0	97.0	95.5	98.7	98.7
70°	71.2	69.6	68.0	66.3	66.3	64.8	64.8	63.1	63.1	63.1	63.1
72.5°	46.9	43.7	40.4	38.9	37.2	37.2	33.9	32.4	33.9	33.9	33.9
75°	24.2	21.0	19.4	17.8	16.2	16.2	14.5	14.5	14.5	14.5	14.5
77.5°	9.7	8.0	6.5	6.5	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.2	3.2	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.7	0.0	0.0	1.7	0.0	1.7	1.7	1.7	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P593598

CATALOG NUMBER: HCC8W20D010MW-HM80520850-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6
2.5°	1061.6	1061.6	1059.9	1061.6	1058.2	1059.9	1058.2	1058.2
5°	1037.2	1034.0	1034.0	1034.0	1032.4	1032.4	1030.8	1030.8
7.5°	1008.1	1006.5	1004.9	1003.3	1001.6	1000.0	1000.0	1000.0
10°	978.9	975.7	975.7	974.1	970.9	969.2	969.2	969.2
12.5°	945.0	943.4	941.8	941.8	935.3	937.0	935.3	935.3
15°	912.6	911.0	911.0	906.1	902.9	902.9	902.9	901.3
17.5°	878.7	877.0	875.4	872.2	869.0	869.0	867.4	869.0
20°	843.1	841.5	838.2	838.2	836.6	835.0	831.8	833.3
22.5°	807.4	804.2	802.6	802.6	801.0	801.0	797.7	797.7
25°	770.2	768.7	767.0	768.7	765.3	765.3	762.2	762.2
27.5°	731.4	729.8	729.8	729.8	728.2	729.8	728.2	728.2
30°	692.5	692.5	691.0	691.0	692.5	691.0	692.5	694.2
32.5°	650.5	650.5	652.1	652.1	653.8	653.8	653.8	653.8
35°	606.8	610.0	610.0	611.7	613.3	614.9	614.9	616.5
37.5°	566.4	568.0	569.6	571.3	574.5	574.5	574.5	574.5
40°	522.7	524.3	527.5	525.9	532.4	534.0	532.4	532.4
42.5°	477.4	480.6	482.3	485.4	487.1	490.3	491.9	491.9
45°	435.3	436.9	440.2	443.4	445.0	449.9	449.9	449.9
47.5°	391.6	394.8	396.4	399.6	401.3	406.1	407.8	406.1
50°	349.5	352.7	356.0	356.0	360.9	362.5	365.7	367.4
52.5°	309.1	310.6	313.9	315.6	318.8	322.0	323.6	325.3
55°	270.2	271.9	275.1	275.1	279.9	281.6	284.7	284.7
57.5°	234.6	236.3	239.5	237.8	241.1	244.3	244.3	242.8
60°	200.7	200.7	200.7	203.9	205.5	207.1	208.7	208.7
62.5°	165.0	168.3	169.9	169.9	171.5	173.2	173.2	171.5
65°	132.7	135.9	137.6	137.6	139.1	139.1	139.1	140.8
67.5°	100.4	100.4	100.4	101.9	100.4	100.4	100.4	100.4
70°	63.1	63.1	63.1	63.1	61.5	63.1	63.1	64.8
72.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.9
75°	14.5	14.5	14.5	16.2	14.5	14.5	14.5	14.5
77.5°	6.5	4.8	6.5	6.5	4.8	4.8	4.8	4.8
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	0.0	1.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)