

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583834

Luminaire Tested: **HCC8W15D010MB-HM80520827-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583834  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W15D010MB-HM80520827-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1587.6 lumens  
Efficiency: N/A  
Efficacy: 113.4 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583834  
CATALOG NUMBER: HCC8W15D010MB-HM80520827-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583834

CATALOG NUMBER: HCC8W15D010MB-HM80520827-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			96																
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			91																
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87			87																
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83			83																
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80			80																
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76			76																
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73			73																
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			71																
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68			68																
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66			66																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	298798
5°	191652
10°	86578
15°	52237
20°	39808
25°	32146
30°	23554
35°	8526
40°	3180
45°	1443
50°	461
55°	118
60°	68
65°	80
70°	0
75°	0
80°	195
85°	389



TEST NUMBER: P583834  
 CATALOG NUMBER: HCC8W15D010MB-HM80520827-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	472.2	29.7
10°-20°	479.6	30.2
20°-30°	429.4	27.0
30°-40°	172.9	10.9
40°-50°	28.4	1.8
50°-60°	2.6	0.2
60°-70°	1.0	0.1
70°-80°	0.7	0.0
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1381.2	87.0
0°-40°	1554.1	97.9
0°-60°	1585.1	99.8
0°-90°	1587.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1587.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9690	
5°	6192	472
15°	1636	480
25°	945	429
35°	226	173
45°	33	28
55°	2	3
65°	1	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P583834  
CATALOG NUMBER: HCC8W15D010MB-HM80520827-81NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9689.8
0.5°	9659.8
1°	9534.7
1.5°	9333.8
2°	9029.2
2.5°	8669.0
3°	8218.0
3.5°	7723.1
4°	7233.6
4.5°	6685.3
5°	6191.5
5.5°	5654.0
6°	5217.9
6.5°	4763.6
7°	4406.7
7.5°	4029.4
8°	3725.9
8.5°	3421.2
9°	3192.5
9.5°	2940.2
10°	2765.0
12.5°	2039.2
15°	1636.3
17.5°	1398.0
20°	1213.1
22.5°	1065.6
25°	944.8
27.5°	824.1
30°	661.5
32.5°	425.4
35°	226.5
37.5°	125.1
40°	79.0
42.5°	52.4
45°	33.1
47.5°	20.4
50°	9.6
52.5°	3.3
55°	2.2
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1



TEST NUMBER: P583834  
CATALOG NUMBER: HCC8W15D010MB-HM80520827-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	1.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.1
70°		0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)