

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584047

Luminaire Tested: **HCC8S20D010MB-HM80520927-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584047
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MB-HM80520927-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1673.6 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584047
CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584047

CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25659	25659	25659
5°	26599	25574	24695
10°	27351	25353	23688
15°	27962	24904	22641
20°	28005	23932	21720
25°	27468	22602	20952
30°	26053	20958	20032
35°	23671	19089	19135
40°	20699	17128	18034
45°	17936	15259	16803
50°	15706	13552	15308
55°	13978	12010	13854
60°	12612	10787	12174
65°	11383	9485	10609
70°	10233	7988	7889
75°	9007	6338	5909
80°	7565	5256	5665
85°	5838	4599	5024



TEST NUMBER: P584047
 CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	4.7
10°-20°	221.1	13.2
20°-30°	316.0	18.9
30°-40°	335.8	20.1
40°-50°	289.1	17.3
50°-60°	216.1	12.9
60°-70°	137.9	8.2
70°-80°	62.7	3.7
80°-90°	16.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	615.6	36.8
0°-40°	951.4	56.8
0°-60°	1456.6	87.0
0°-90°	1673.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1673.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	832	832	832	832	832	
5°	859	848	826	805	798	82
15°	876	846	780	727	709	247
25°	807	756	664	624	616	370
35°	629	585	507	494	508	392
45°	411	389	350	359	385	320
55°	260	239	223	242	258	234
65°	156	138	130	136	145	156
75°	76	65	53	48	50	80
85°	16	14	13	14	14	20
90°	0	0	0	0	0	



TEST NUMBER: P584047

CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1
2.5°	847.5	845.1	846.3	845.1	846.3	846.3	843.9	843.9	843.9	843.9	840.4
5°	859.3	858.1	858.1	857.0	855.8	857.0	855.8	854.6	852.2	851.0	847.5
7.5°	866.4	866.4	866.4	866.4	865.2	864.0	862.9	860.5	858.1	855.8	853.4
10°	873.5	874.7	873.5	872.3	871.1	868.8	867.6	865.2	861.7	858.1	855.8
12.5°	877.0	877.0	875.9	875.9	873.5	872.3	868.8	865.2	861.7	858.1	852.2
15°	875.9	875.9	874.7	873.5	870.0	868.8	866.4	862.9	857.0	852.2	846.3
17.5°	868.8	867.6	865.2	865.2	860.5	859.3	857.0	852.2	846.3	839.2	832.1
20°	853.4	853.4	852.2	851.0	846.3	842.8	840.4	834.5	829.8	821.5	814.4
22.5°	832.1	834.5	832.1	829.8	823.9	822.7	819.1	812.0	804.9	795.5	787.2
25°	807.3	806.1	804.9	802.6	797.8	795.5	790.8	783.7	776.6	765.9	756.5
27.5°	775.4	770.7	770.7	765.9	762.4	758.8	756.5	749.4	739.9	731.7	719.8
30°	731.7	732.8	726.9	725.7	719.8	717.5	712.7	705.7	697.4	687.9	678.5
32.5°	684.4	680.8	680.8	676.1	671.4	667.8	666.6	658.4	651.3	641.8	632.4
35°	628.8	628.8	625.3	624.1	619.4	617.0	613.5	608.7	600.5	592.2	585.1
37.5°	574.5	572.1	570.9	568.5	565.0	561.4	561.4	553.2	552.0	542.5	533.1
40°	514.2	516.5	514.2	510.6	509.4	507.1	505.9	501.2	497.6	489.3	483.4
42.5°	463.3	461.0	461.0	459.8	455.1	455.1	452.7	450.3	444.4	442.1	435.0
45°	411.3	413.7	410.2	411.3	406.6	406.6	406.6	401.9	397.2	393.6	388.9
47.5°	366.4	367.6	367.6	364.1	362.9	362.9	360.5	358.1	354.6	349.9	346.3
50°	327.4	328.6	326.2	325.0	322.7	321.5	321.5	316.8	314.4	309.7	307.3
52.5°	292.0	292.0	290.8	290.8	287.2	287.2	284.9	281.3	279.0	276.6	270.7
55°	260.0	260.0	258.9	257.7	257.7	254.1	252.9	249.4	247.0	242.3	238.8
57.5°	229.3	230.5	229.3	228.1	226.9	225.8	223.4	219.9	217.5	213.9	211.6
60°	204.5	204.5	203.3	202.1	199.8	198.6	197.4	195.0	191.5	189.1	185.6
62.5°	180.8	179.7	178.5	177.3	174.9	174.9	172.6	170.2	166.7	164.3	161.9
65°	156.0	156.0	154.8	154.8	153.7	151.3	150.1	148.9	144.2	143.0	138.3
67.5°	133.6	134.7	132.4	132.4	130.0	130.0	128.8	125.3	124.1	121.7	119.4
70°	113.5	113.5	113.5	112.3	109.9	108.7	107.6	105.2	104.0	101.7	99.3
72.5°	93.4	93.4	92.2	92.2	91.0	89.8	88.6	86.3	86.3	83.9	81.6
75°	75.6	75.6	74.5	73.3	72.1	72.1	70.9	69.7	67.4	66.2	65.0
77.5°	57.9	57.9	57.9	56.7	55.6	55.6	55.6	53.2	50.8	50.8	49.6
80°	42.6	42.6	41.4	41.4	40.2	40.2	40.2	39.0	37.8	36.6	35.5
82.5°	28.4	28.4	28.4	28.4	27.2	27.2	27.2	26.0	24.8	24.8	24.8
85°	16.5	16.5	16.5	16.5	15.4	15.4	15.4	15.4	15.4	14.2	14.2
87.5°	7.1	5.9	7.1	5.9	7.1	5.9	7.1	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584047

CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1
2.5°	841.6	840.4	839.2	838.0	838.0	836.9	834.5	833.3	832.1	830.9	830.9
5°	846.3	845.1	842.8	840.4	839.2	836.9	834.5	832.1	829.8	826.2	825.0
7.5°	849.9	846.3	843.9	839.2	838.0	835.7	832.1	828.6	823.9	819.1	815.6
10°	849.9	845.1	841.6	835.7	833.3	830.9	826.2	820.3	814.4	809.7	803.8
12.5°	847.5	841.6	835.7	829.8	826.2	822.7	815.6	809.7	802.6	795.5	790.8
15°	839.2	832.1	825.0	817.9	814.4	809.7	802.6	794.3	787.2	780.1	771.8
17.5°	823.9	816.8	808.5	800.2	795.5	791.9	781.3	775.4	764.8	757.7	750.6
20°	803.8	795.5	784.8	776.6	770.7	767.1	758.8	748.2	739.9	729.3	722.2
22.5°	777.8	767.1	756.5	748.2	742.3	737.6	726.9	716.3	709.2	699.7	691.5
25°	747.0	736.4	725.7	713.9	708.0	703.3	693.8	684.4	674.9	664.3	657.2
27.5°	710.4	698.6	689.1	678.5	672.6	665.5	654.8	645.4	635.9	628.8	619.4
30°	670.2	657.2	647.7	637.1	631.2	625.3	614.6	605.2	596.9	588.6	583.9
32.5°	621.7	612.3	602.8	592.2	587.5	583.9	573.3	563.8	554.4	547.3	543.7
35°	575.6	565.0	556.7	547.3	541.4	537.8	528.4	520.1	515.4	507.1	502.4
37.5°	527.2	518.9	509.4	500.0	496.4	492.9	485.8	477.5	470.4	464.5	462.2
40°	476.3	469.3	461.0	455.1	451.5	448.0	442.1	436.2	431.4	425.5	423.2
42.5°	427.9	423.2	416.1	409.0	405.4	404.2	397.2	392.4	390.1	387.7	385.3
45°	384.2	377.1	372.3	367.6	364.1	361.7	358.1	354.6	352.2	349.9	347.5
47.5°	341.6	335.7	331.0	327.4	323.9	322.7	320.3	316.8	314.4	314.4	314.4
50°	302.6	297.9	293.1	290.8	289.6	287.2	284.9	283.7	282.5	282.5	282.5
52.5°	268.3	263.6	260.0	257.7	257.7	255.3	252.9	251.8	251.8	251.8	251.8
55°	236.4	232.9	230.5	228.1	225.8	224.6	224.6	224.6	223.4	223.4	224.6
57.5°	208.0	205.7	202.1	199.8	198.6	198.6	197.4	196.2	197.4	198.6	199.8
60°	182.0	179.7	178.5	174.9	174.9	174.9	173.8	173.8	173.8	174.9	176.1
62.5°	158.4	157.2	154.8	153.7	152.5	152.5	151.3	151.3	151.3	151.3	152.5
65°	137.1	134.7	132.4	132.4	132.4	131.2	131.2	128.8	130.0	130.0	128.8
67.5°	117.0	114.7	113.5	112.3	111.1	111.1	109.9	108.7	107.6	107.6	107.6
70°	98.1	95.7	95.7	93.4	93.4	92.2	91.0	91.0	89.8	88.6	87.5
72.5°	79.2	78.0	76.8	75.6	75.6	75.6	74.5	73.3	72.1	70.9	68.6
75°	62.6	62.6	60.3	59.1	59.1	57.9	56.7	55.6	54.4	53.2	52.0
77.5°	48.5	47.3	44.9	43.7	43.7	43.7	42.6	41.4	40.2	39.0	37.8
80°	35.5	34.3	33.1	31.9	31.9	31.9	30.7	30.7	29.6	29.6	29.6
82.5°	23.6	23.6	22.5	22.5	22.5	22.5	21.3	21.3	21.3	21.3	21.3
85°	14.2	14.2	13.0	13.0	13.0	13.0	13.0	13.0	13.0	13.0	13.0
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584047

CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1
2.5°	828.6	828.6	826.2	825.0	823.9	825.0	822.7	821.5	820.3	820.3	819.1
5°	821.5	820.3	815.6	814.4	813.2	812.0	809.7	807.3	804.9	803.8	802.6
7.5°	812.0	808.5	803.8	802.6	801.4	797.8	794.3	791.9	788.4	787.2	784.8
10°	799.0	794.3	790.8	787.2	784.8	781.3	777.8	774.2	769.5	768.3	764.8
12.5°	783.7	777.8	770.7	769.5	765.9	761.2	756.5	752.9	749.4	747.0	743.5
15°	764.8	758.8	751.8	748.2	744.7	741.1	735.2	730.5	726.9	723.4	719.8
17.5°	742.3	735.2	729.3	725.7	723.4	717.5	712.7	706.8	703.3	699.7	696.2
20°	715.1	709.2	700.9	697.4	696.2	691.5	685.6	683.2	678.5	674.9	672.6
22.5°	684.4	678.5	671.4	669.0	664.3	661.9	656.0	653.6	651.3	647.7	646.6
25°	650.1	644.2	638.3	637.1	633.6	631.2	627.6	624.1	624.1	620.6	620.6
27.5°	614.6	608.7	604.0	601.6	600.5	598.1	594.5	593.4	592.2	591.0	591.0
30°	576.8	569.7	567.4	566.2	565.0	562.6	561.4	559.1	560.3	561.4	560.3
32.5°	536.6	534.3	529.5	527.2	528.4	527.2	524.8	527.2	526.0	528.4	529.5
35°	497.6	495.3	492.9	492.9	490.5	490.5	490.5	491.7	494.1	495.3	497.6
37.5°	459.8	456.3	455.1	453.9	455.1	455.1	455.1	457.4	459.8	462.2	465.7
40°	419.6	417.2	417.2	417.2	417.2	420.8	419.6	422.0	424.3	427.9	431.4
42.5°	381.8	381.8	383.0	383.0	383.0	383.0	385.3	388.9	392.4	396.0	399.5
45°	346.3	346.3	346.3	348.7	348.7	349.9	354.6	357.0	359.3	362.9	366.4
47.5°	313.2	313.2	314.4	315.6	316.8	319.1	321.5	325.0	328.6	331.0	334.5
50°	282.5	283.7	286.0	288.4	288.4	289.6	293.1	295.5	297.9	301.4	302.6
52.5°	252.9	255.3	257.7	258.9	260.0	262.4	263.6	267.1	268.3	271.9	273.0
55°	225.8	226.9	230.5	231.7	231.7	234.0	236.4	238.8	242.3	242.3	244.7
57.5°	200.9	202.1	204.5	205.7	204.5	208.0	209.2	211.6	212.8	215.1	216.3
60°	176.1	178.5	179.7	179.7	180.8	182.0	184.4	184.4	186.8	189.1	189.1
62.5°	152.5	153.7	154.8	156.0	157.2	156.0	159.6	159.6	161.9	163.1	165.5
65°	130.0	131.2	131.2	132.4	132.4	133.6	133.6	134.7	135.9	138.3	139.5
67.5°	107.6	107.6	107.6	108.7	107.6	108.7	108.7	109.9	109.9	112.3	113.5
70°	87.5	86.3	85.1	85.1	85.1	85.1	83.9	85.1	85.1	86.3	86.3
72.5°	67.4	66.2	65.0	63.8	63.8	62.6	61.5	62.6	62.6	63.8	63.8
75°	50.8	48.5	48.5	48.5	47.3	47.3	47.3	48.5	48.5	48.5	49.6
77.5°	37.8	37.8	36.6	36.6	36.6	37.8	37.8	39.0	39.0	39.0	39.0
80°	28.4	29.6	29.6	29.6	29.6	30.7	30.7	30.7	30.7	31.9	31.9
82.5°	21.3	21.3	21.3	21.3	22.5	22.5	22.5	22.5	22.5	22.5	22.5
85°	13.0	14.2	14.2	13.0	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584047

CATALOG NUMBER: HCC8S20D010MB-HM80520927-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1
2.5°	817.9	817.9	817.9	817.9	816.8	816.8	816.8	815.6
5°	800.2	800.2	800.2	797.8	799.0	799.0	796.7	797.8
7.5°	782.5	781.3	780.1	780.1	778.9	777.8	776.6	777.8
10°	762.4	758.8	758.8	757.7	757.7	755.3	755.3	756.5
12.5°	739.9	737.6	737.6	736.4	735.2	734.0	732.8	732.8
15°	717.5	715.1	713.9	712.7	711.6	709.2	710.4	709.2
17.5°	695.0	691.5	691.5	690.3	689.1	686.7	686.7	685.6
20°	669.0	667.8	665.5	666.6	665.5	663.1	661.9	661.9
22.5°	643.0	643.0	641.8	641.8	640.6	639.5	638.3	638.3
25°	618.2	617.0	618.2	618.2	614.6	614.6	614.6	615.8
27.5°	589.8	591.0	589.8	589.8	589.8	589.8	591.0	589.8
30°	561.4	561.4	561.4	562.6	565.0	563.8	563.8	562.6
32.5°	530.7	531.9	531.9	533.1	534.3	536.6	536.6	537.8
35°	500.0	502.4	503.5	502.4	505.9	505.9	508.3	508.3
37.5°	468.1	469.3	471.6	472.8	475.2	476.3	477.5	477.5
40°	433.8	438.5	439.7	440.9	444.4	444.4	445.6	448.0
42.5°	401.9	406.6	407.8	409.0	411.3	414.9	413.7	416.1
45°	371.1	374.7	375.9	377.1	380.6	381.8	381.8	385.3
47.5°	338.1	340.4	341.6	344.0	346.3	348.7	351.1	349.9
50°	305.0	308.5	310.9	312.0	315.6	316.8	318.0	319.1
52.5°	275.4	277.8	279.0	280.1	283.7	284.9	286.0	288.4
55°	247.0	248.2	250.6	249.4	252.9	254.1	255.3	257.7
57.5°	218.7	219.9	221.0	221.0	223.4	225.8	226.9	228.1
60°	191.5	193.8	195.0	195.0	195.0	197.4	197.4	197.4
62.5°	166.7	166.7	167.8	167.8	170.2	170.2	170.2	170.2
65°	140.7	141.8	143.0	143.0	145.4	144.2	146.6	145.4
67.5°	113.5	113.5	115.8	115.8	114.7	115.8	115.8	115.8
70°	86.3	86.3	87.5	87.5	87.5	87.5	87.5	87.5
72.5°	63.8	63.8	63.8	65.0	63.8	63.8	65.0	63.8
75°	49.6	49.6	49.6	49.6	49.6	49.6	49.6	49.6
77.5°	39.0	39.0	40.2	40.2	40.2	40.2	40.2	40.2
80°	31.9	31.9	31.9	31.9	33.1	31.9	31.9	31.9
82.5°	23.6	22.5	23.6	22.5	23.6	23.6	23.6	23.6
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)