

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583868

Luminaire Tested: **HCC8W15D010BZ-HM80520835-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010BZ-HM80520835-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1642.6 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583868
CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81NDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P583868

CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96																												
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91																												
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87																												
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83																												
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80																												
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76																												
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73																												
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71																												
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68																												
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	309159
5°	198301
10°	89581
15°	54051
20°	41187
25°	33262
30°	24376
35°	8828
40°	3293
45°	1491
50°	480
55°	118
60°	68
65°	80
70°	0
75°	0
80°	195
85°	389



TEST NUMBER: P583868
 CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	488.6	29.7
10°-20°	496.3	30.2
20°-30°	444.3	27.0
30°-40°	179.0	10.9
40°-50°	29.3	1.8
50°-60°	2.7	0.2
60°-70°	1.0	0.1
70°-80°	0.7	0.0
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.1	87.0
0°-40°	1608.1	97.9
0°-60°	1640.1	99.9
0°-90°	1642.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1642.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10026	
5°	6406	489
15°	1693	496
25°	978	444
35°	234	179
45°	34	29
55°	2	3
65°	1	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P583868
CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	10025.8
0.5°	9994.9
1°	9865.5
1.5°	9657.6
2°	9342.4
2.5°	8969.8
3°	8503.1
3.5°	7991.1
4°	7484.5
4.5°	6917.2
5°	6406.3
5.5°	5850.0
6°	5398.9
6.5°	4928.8
7°	4559.5
7.5°	4169.2
8°	3855.0
8.5°	3539.9
9°	3303.3
9.5°	3042.3
10°	2860.9
12.5°	2110.0
15°	1693.1
17.5°	1446.5
20°	1255.1
22.5°	1102.6
25°	977.6
27.5°	852.7
30°	684.6
32.5°	440.2
35°	234.5
37.5°	129.4
40°	81.8
42.5°	54.2
45°	34.2
47.5°	21.0
50°	10.0
52.5°	3.4
55°	2.2
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1



TEST NUMBER: P583868
CATALOG NUMBER: HCC8W15D010BZ-HM80520835-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	1.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.1
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)