

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584056

Luminaire Tested: **HCC8S20D010MW-HM80520930-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584056
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S20D010MW-HM80520930-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1811.7 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584056
CATALOG NUMBER: HCC8S20D010MW-HM80520930-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584056

CATALOG NUMBER: HCC8S20D010MW-HM80520930-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	29800	29800	29800
5°	30360	29673	28982
10°	30833	29155	27924
15°	31145	28428	26711
20°	31027	27329	25484
25°	30207	25749	24058
30°	28770	23871	22660
35°	25978	21788	21051
40°	22824	19555	19503
45°	19703	17191	17932
50°	17145	15078	16080
55°	15209	13096	14010
60°	13568	11064	11625
65°	12229	8975	9179
70°	10855	6726	5437
75°	9365	3896	2335
80°	7192	1385	693
85°	4635	460	460



TEST NUMBER: P584056
 CATALOG NUMBER: HCC8S20D010MW-HM80520930-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	5.0
10°-20°	252.6	13.9
20°-30°	357.2	19.7
30°-40°	376.4	20.8
40°-50°	319.9	17.7
50°-60°	230.4	12.7
60°-70°	132.9	7.3
70°-80°	45.5	2.5
80°-90°	6.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.5	38.7
0°-40°	1076.9	59.4
0°-60°	1627.1	89.8
0°-90°	1811.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1811.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	966	966	966	966	966	
5°	981	974	959	942	936	94
15°	976	946	890	851	837	275
25°	888	842	757	718	707	407
35°	690	650	579	558	559	430
45°	452	431	394	397	411	351
55°	283	261	244	253	261	255
65°	168	144	123	120	126	167
75°	79	59	33	21	20	83
85°	13	8	1	1	1	18
90°	0	0	0	0	0	



TEST NUMBER: P584056

CATALOG NUMBER: HCC8S20D010MW-HM80520930-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	966.4	966.4	966.4	966.4	966.4	966.4	966.4	966.4	966.4	966.4	966.4
2.5°	975.6	976.9	975.6	975.6	974.3	972.9	971.6	970.3	967.7	965.1	965.1
5°	980.8	983.4	980.8	980.8	976.9	974.3	971.6	967.7	962.5	958.6	958.6
7.5°	984.7	984.7	984.7	980.8	978.2	974.3	967.7	961.2	954.6	948.1	945.5
10°	984.7	984.7	983.4	978.2	975.6	967.7	961.2	952.0	942.9	933.7	931.1
12.5°	980.8	982.1	979.5	974.3	967.7	958.6	949.4	937.6	927.2	916.6	911.4
15°	975.6	974.3	971.6	965.1	957.3	945.5	936.3	923.1	908.8	895.7	890.5
17.5°	962.5	962.5	958.6	952.0	941.6	928.5	914.0	899.6	883.9	869.5	863.0
20°	945.5	945.5	940.2	932.4	921.8	904.8	889.1	872.1	853.8	839.3	832.8
22.5°	920.5	921.8	915.3	906.1	894.4	874.8	859.1	838.0	819.7	802.7	797.5
25°	887.8	890.5	883.9	874.8	859.1	842.1	822.3	802.7	781.8	764.8	756.8
27.5°	849.9	851.2	844.7	835.4	819.7	801.4	781.8	760.9	741.2	722.8	715.0
30°	808.0	802.7	800.1	788.3	771.3	755.5	733.3	716.3	695.4	679.6	670.4
32.5°	749.0	751.6	743.8	734.6	721.5	703.2	684.9	665.2	645.6	633.8	627.3
35°	690.1	692.8	688.8	679.6	665.2	649.5	631.2	616.8	599.7	585.3	578.8
37.5°	628.6	628.6	626.0	620.7	610.3	595.8	577.5	563.1	548.7	536.9	533.0
40°	567.0	564.4	563.1	559.2	550.0	536.9	525.2	513.3	498.9	491.1	485.8
42.5°	506.7	506.7	504.1	500.2	491.1	484.5	472.7	459.7	449.2	441.4	441.4
45°	451.8	453.1	449.2	446.6	441.4	430.8	420.3	411.2	402.0	396.8	394.2
47.5°	403.3	403.3	399.4	396.8	391.6	382.4	373.2	365.4	358.9	354.8	353.5
50°	357.4	357.4	357.4	350.9	344.4	337.8	331.3	322.1	318.2	315.6	314.3
52.5°	318.2	316.9	316.9	311.7	305.1	297.3	290.7	282.9	279.0	276.4	277.7
55°	282.9	282.9	281.6	275.1	268.4	260.6	254.0	247.5	244.9	242.3	243.6
56°	268.4	268.4	267.1	261.9	254.0	247.5	239.6	233.1	229.2	230.5	230.5
57°	258.0	255.3	255.3	248.8	242.3	233.1	226.6	220.0	217.4	216.1	216.1
58°	244.9	243.6	242.3	235.7	229.2	221.3	214.8	208.3	204.2	204.2	202.9
59°	231.8	231.8	229.2	223.9	217.4	209.6	202.9	196.4	192.5	191.1	191.1
60°	220.0	221.3	217.4	212.2	206.8	197.7	189.8	184.6	180.7	179.4	179.4
61°	209.6	209.6	206.8	200.3	193.8	187.2	179.4	172.8	170.2	167.6	167.6
62°	200.3	197.7	196.4	189.8	183.3	175.5	168.9	162.4	158.5	155.8	157.1
63°	188.5	187.2	184.6	179.4	172.8	165.0	157.1	151.9	148.0	144.1	145.4
64°	179.4	178.1	174.1	168.9	162.4	154.5	146.7	141.4	138.8	134.9	133.6
65°	167.6	166.3	165.0	158.5	151.9	144.1	137.5	132.3	128.4	125.8	123.0
66°	157.1	158.5	155.8	150.6	142.8	136.2	127.1	121.7	119.1	115.2	112.6
67°	148.0	148.0	145.4	140.1	132.3	125.8	119.1	112.6	108.7	104.7	103.4
67.5°	142.8	142.8	140.1	133.6	128.4	120.4	113.9	108.7	103.4	100.8	98.2
68°	137.5	137.5	136.2	131.0	124.3	116.5	110.0	103.4	98.2	94.3	93.0
69°	128.4	129.7	127.1	121.7	115.2	107.3	100.8	95.6	90.3	86.4	83.8
70°	120.4	119.1	116.5	111.3	104.7	99.5	93.0	86.4	81.2	76.0	74.6
71°	110.0	110.0	107.3	103.4	96.9	90.3	83.8	78.6	73.3	66.8	65.5
72°	102.1	102.1	99.5	94.3	89.0	82.5	76.0	69.4	65.5	59.0	56.3
72.5°	96.9	98.2	95.6	90.3	85.1	77.3	72.0	66.8	60.3	55.0	52.4
73°	94.3	93.0	91.7	86.4	79.9	74.6	68.1	62.9	56.3	51.1	48.5



TEST NUMBER: P584056
 CATALOG NUMBER: HCC8S20D010MW-HM80520930-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	59.0	59.0	57.6	52.4	47.2	42.0	36.6	31.4	26.2	20.9	18.3
80°	40.5	42.0	39.2	36.6	32.7	27.5	22.2	18.3	13.1	10.5	7.8
82.5°	26.2	26.2	24.8	22.2	19.6	15.7	13.1	9.2	6.5	5.2	3.9
85°	13.1	14.4	13.1	11.8	9.2	7.8	6.5	3.9	2.6	1.3	1.3
87.5°	5.2	5.2	5.2	3.9	3.9	2.6	1.3	1.3	1.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584056

CATALOG NUMBER: HCC8S20D010MW-HM80520930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	966.4	966.4	966.4	966.4	966.4	966.4	966.4	966.4	966.4	966.4
2.5°	962.5	962.5	959.9	958.6	957.3	955.9	954.6	953.3	953.3	954.6
5°	954.6	952.0	946.8	945.5	941.6	940.2	937.6	936.3	937.6	936.3
7.5°	942.9	937.6	931.1	928.5	923.1	920.5	916.6	916.6	914.0	915.3
10°	927.2	919.2	911.4	906.1	902.2	898.3	895.7	893.1	891.8	891.8
12.5°	907.5	898.3	890.5	882.6	876.1	873.4	868.2	868.2	865.6	864.3
15°	885.2	873.4	864.3	856.4	851.2	846.0	842.1	839.3	836.7	836.7
17.5°	856.4	846.0	836.7	827.6	819.7	815.8	811.9	808.0	808.0	805.3
20°	825.0	813.2	805.3	796.2	789.6	783.1	777.9	777.9	775.3	776.6
22.5°	789.6	775.3	767.4	760.9	754.2	749.0	743.8	743.8	742.5	741.2
25°	750.3	738.5	729.4	721.5	717.6	712.4	711.1	708.5	707.1	707.1
27.5°	708.5	699.3	687.5	683.6	678.3	675.7	675.7	674.4	671.7	673.0
30°	663.9	653.4	646.9	644.3	639.0	639.0	637.7	635.1	635.1	636.4
32.5°	620.7	610.3	604.9	603.6	598.4	598.4	597.1	598.4	598.4	599.7
35°	573.5	564.4	563.1	559.2	557.9	557.9	557.9	560.5	563.1	559.2
37.5°	529.1	522.4	518.5	517.2	518.5	518.5	519.8	523.7	522.4	521.1
40°	483.2	478.0	475.4	475.4	478.0	480.6	480.6	484.5	485.8	484.5
42.5°	437.3	433.4	433.4	434.7	437.3	438.6	442.7	446.6	447.9	449.2
45°	394.2	394.2	394.2	395.5	396.8	399.4	404.6	408.6	409.9	411.2
47.5°	352.2	350.9	354.8	356.1	360.2	361.5	365.4	370.6	371.9	373.2
50°	313.0	315.6	316.9	320.8	323.4	323.4	328.7	331.3	335.2	335.2
52.5°	276.4	280.3	281.6	285.5	286.8	288.1	290.7	294.7	297.3	297.3
55°	243.6	244.9	247.5	248.8	252.7	254.0	256.6	258.0	261.9	260.6
56°	229.2	231.8	233.1	235.7	238.3	239.6	242.3	243.6	246.2	247.5
57°	216.1	217.4	221.3	222.6	225.3	225.3	226.6	230.5	230.5	231.8
58°	202.9	205.5	206.8	208.3	210.9	212.2	214.8	216.1	217.4	216.1
59°	191.1	192.5	193.8	193.8	196.4	196.4	200.3	202.9	204.2	204.2
60°	179.4	179.4	180.7	182.0	184.6	185.9	185.9	188.5	188.5	188.5
61°	167.6	167.6	168.9	170.2	171.5	171.5	174.1	174.1	175.5	176.8
62°	157.1	155.8	155.8	157.1	157.1	159.8	161.1	162.4	163.7	162.4
63°	145.4	144.1	144.1	144.1	144.1	146.7	146.7	148.0	150.6	149.3
64°	132.3	132.3	132.3	132.3	133.6	133.6	136.2	137.5	138.8	140.1
65°	123.0	120.4	119.1	119.1	120.4	121.7	123.0	124.3	125.8	125.8
66°	112.6	110.0	108.7	108.7	108.7	108.7	111.3	111.3	113.9	113.9
67°	100.8	98.2	96.9	95.6	95.6	95.6	99.5	98.2	98.2	98.2
67.5°	96.9	93.0	91.7	90.3	89.0	91.7	90.3	91.7	91.7	90.3
68°	91.7	89.0	86.4	83.8	83.8	83.8	85.1	86.4	85.1	83.8
69°	81.2	79.9	76.0	73.3	72.0	73.3	72.0	73.3	72.0	73.3
70°	72.0	68.1	64.2	62.9	61.6	61.6	61.6	60.3	61.6	60.3
71°	62.9	59.0	55.0	52.4	51.1	51.1	49.8	51.1	49.8	51.1
72°	53.7	49.8	44.6	42.0	42.0	42.0	42.0	40.5	42.0	40.5
72.5°	49.8	44.6	40.5	37.9	36.6	36.6	36.6	36.6	35.3	36.6
73°	45.9	40.5	35.3	34.0	34.0	34.0	32.7	31.4	32.7	32.7



TEST NUMBER: P584056
CATALOG NUMBER: HCC8S20D010MW-HM80520930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	15.7	11.8	10.5	10.5	10.5	10.5	10.5	10.5	9.2	9.2
80°	6.5	5.2	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
82.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
85°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	85.1	85.1	82.5	78.6	72.0	65.5	60.3	55.0	48.5	42.0	39.2
75°	78.6	77.3	74.6	70.7	65.5	59.0	53.7	47.2	42.0	35.3	32.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	37.9	31.4	28.8	26.2	26.2	26.2	24.8	24.8	24.8	26.2
75°	30.1	24.8	22.2	19.6	20.9	19.6	20.9	19.6	19.6	19.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)