

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583870

Luminaire Tested: **HCC8W15D010MW-HM80520835-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W15D010MW-HM80520835-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1481.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583870
CATALOG NUMBER: HCC8W15D010MW-HM80520835-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P583870
 CATALOG NUMBER: HCC8W15D010MW-HM80520835-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																																				
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81																																				
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																																				
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67																																				
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																																				
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56																																				
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52																																				
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																																				
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45																																				
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36917
5°	36820
10°	36203
15°	35675
20°	34820
25°	33054
30°	27264
35°	14034
40°	9395
45°	8055
50°	6956
55°	6070
60°	5390
65°	4845
70°	4391
75°	3944
80°	3534
85°	3538



TEST NUMBER: P583870
 CATALOG NUMBER: HCC8W15D010MW-HM80520835-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	7.6
10°-20°	314.4	21.2
20°-30°	435.6	29.4
30°-40°	261.6	17.7
40°-50°	143.2	9.7
50°-60°	101.7	6.9
60°-70°	66.1	4.5
70°-80°	35.3	2.4
80°-90°	10.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.5	58.2
0°-40°	1124.1	75.9
0°-60°	1369.1	92.4
0°-90°	1481.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1481.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1197	
5°	1190	112
15°	1118	314
25°	972	436
35°	373	262
45°	185	143
55°	113	102
65°	66	66
75°	33	35
85°	10	11
90°	0	



TEST NUMBER: P583870
CATALOG NUMBER: HCC8W15D010MW-HM80520835-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1197.2
2.5°	1195.0
5°	1189.5
7.5°	1176.2
10°	1156.2
12.5°	1137.4
15°	1117.5
17.5°	1092.1
20°	1061.1
22.5°	1023.4
25°	971.5
27.5°	889.5
30°	765.7
32.5°	560.9
35°	372.8
37.5°	275.5
40°	233.4
42.5°	206.9
45°	184.7
47.5°	163.8
50°	145.0
52.5°	127.2
55°	112.9
57.5°	99.5
60°	87.4
62.5°	76.4
65°	66.4
67.5°	56.4
70°	48.7
72.5°	39.9
75°	33.1
77.5°	26.5
80°	19.9
82.5°	14.3
85°	10.0
87.5°	4.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)