

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584072

Luminaire Tested: **HCC8W20D010SL-HM80520935-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W20D010SL-HM80520935-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1968.5 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584072
CATALOG NUMBER: HCC8W20D010SL-HM80520935-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584072

CATALOG NUMBER: HCC8W20D010SL-HM80520935-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31940	31940	31940
5°	32363	31805	31505
10°	32693	31481	31005
15°	33022	30813	30194
20°	32855	29675	28999
25°	32088	27903	27526
30°	30479	25900	25804
35°	27748	23637	23840
40°	24329	21153	21934
45°	20985	18813	20143
50°	18378	16517	18239
55°	16279	14204	16059
60°	14666	11940	13303
65°	13221	9580	10193
70°	11594	6978	5608
75°	9889	3622	1477
80°	7618	994	249
85°	4883	0	0



TEST NUMBER: P584072

CATALOG NUMBER: HCC8W20D010SL-HM80520935-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.7	5.0
10°-20°	274.7	14.0
20°-30°	389.9	19.8
30°-40°	410.5	20.9
40°-50°	349.2	17.7
50°-60°	252.3	12.8
60°-70°	143.5	7.3
70°-80°	45.2	2.3
80°-90°	5.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.4	38.7
0°-40°	1172.8	59.6
0°-60°	1774.3	90.1
0°-90°	1968.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1968.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1036	1036	1036	1036	1036	
5°	1046	1040	1028	1020	1018	100
15°	1034	1008	965	947	946	291
25°	943	896	820	806	809	432
35°	737	694	628	624	633	459
45°	481	463	431	442	462	374
55°	303	281	264	279	299	273
65°	181	156	131	130	140	180
75°	83	64	30	14	12	89
85°	14	8	0	0	0	18
90°	0	0	0	0	0	



TEST NUMBER: P584072

CATALOG NUMBER: HCC8W20D010SL-HM80520935-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	1041.3	1042.6	1039.9	1039.9	1042.6	1039.9	1041.3	1041.3	1039.9	1039.9	1038.5
5°	1045.5	1044.1	1044.1	1044.1	1045.5	1042.6	1041.3	1042.6	1039.9	1039.9	1039.9
7.5°	1046.9	1046.9	1045.5	1044.1	1044.1	1044.1	1042.6	1041.3	1039.9	1037.2	1035.8
10°	1044.1	1044.1	1045.5	1042.6	1042.6	1039.9	1039.9	1037.2	1037.2	1034.4	1030.2
12.5°	1041.3	1039.9	1039.9	1037.2	1037.2	1034.4	1034.4	1030.2	1028.8	1024.7	1020.5
15°	1034.4	1033.1	1030.2	1028.8	1027.5	1026.1	1023.4	1022.0	1017.8	1012.3	1008.1
17.5°	1020.5	1019.2	1017.8	1015.0	1012.3	1010.8	1009.5	1005.4	999.9	995.7	988.7
20°	1001.2	999.9	999.9	995.7	994.3	990.2	988.7	983.2	979.1	970.8	965.2
22.5°	974.9	976.3	973.5	970.8	968.1	963.9	961.1	955.5	948.7	940.4	933.4
25°	943.1	944.5	941.7	939.0	934.8	932.0	929.3	921.0	914.0	904.3	896.1
27.5°	903.0	903.0	903.0	900.2	893.4	891.9	889.2	880.9	871.3	862.9	854.6
30°	856.0	854.6	854.6	850.4	847.7	842.2	838.0	831.1	824.2	814.5	804.8
32.5°	799.3	800.7	796.5	793.8	789.6	789.6	784.1	778.6	770.3	760.6	750.9
35°	737.1	738.5	735.7	734.3	727.4	726.0	724.7	717.7	712.2	705.3	694.2
37.5°	673.5	672.1	670.7	670.7	666.5	663.8	661.0	656.8	648.6	643.0	637.5
40°	604.4	604.4	604.4	602.9	601.5	598.8	597.4	594.7	589.1	583.6	579.4
42.5°	542.1	542.1	540.8	539.3	536.5	537.9	535.2	532.4	526.9	522.7	520.0
45°	481.2	481.2	481.2	482.6	479.9	475.8	475.8	472.9	470.2	467.4	463.2
47.5°	427.3	431.4	428.7	427.3	428.7	423.2	423.2	420.4	417.6	414.9	409.3
50°	383.1	383.1	383.1	380.2	378.9	378.9	374.8	372.0	370.6	367.8	362.3
52.5°	342.9	340.2	340.2	338.8	337.5	334.6	334.6	331.9	326.4	323.6	319.5
55°	302.8	302.8	301.4	300.1	298.7	297.3	296.0	291.8	289.0	284.9	280.7
57.5°	266.9	269.6	268.3	265.5	262.8	262.8	260.0	257.2	253.1	248.9	244.8
60°	237.8	236.5	236.5	235.1	232.4	231.0	229.5	225.4	221.3	217.1	213.0
62.5°	207.4	207.4	207.4	204.7	201.9	200.5	199.2	196.3	190.9	186.6	183.9
65°	181.2	179.8	178.4	177.1	175.6	172.8	171.5	168.7	164.5	160.4	156.3
67.5°	154.8	153.5	153.5	152.1	148.0	146.6	146.6	142.4	138.3	134.2	130.0
70°	128.6	128.6	128.6	125.9	124.5	123.0	121.7	118.9	114.8	110.6	106.5
72.5°	106.5	105.1	105.1	103.7	99.5	98.2	96.8	94.1	89.8	87.1	84.4
75°	83.0	83.0	81.6	80.3	78.8	77.4	76.0	73.3	69.1	65.0	63.6
77.5°	63.6	62.2	62.2	60.9	58.0	56.7	56.7	53.9	49.8	47.0	44.2
80°	42.9	44.2	42.9	41.5	40.1	38.8	37.4	35.9	33.2	30.4	27.7
82.5°	26.2	27.7	26.2	26.2	24.9	23.5	23.5	20.7	19.4	18.0	16.5
85°	13.8	13.8	13.8	13.8	12.4	12.4	12.4	11.1	9.7	8.3	8.3
87.5°	4.1	5.6	4.1	4.1	4.1	4.1	4.1	4.1	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584072

CATALOG NUMBER: HCC8W20D010SL-HM80520935-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	1039.9	1038.5	1037.2	1037.2	1037.2	1037.2	1037.2	1035.8	1034.4	1034.4	1034.4
5°	1037.2	1037.2	1037.2	1035.8	1034.4	1034.4	1031.6	1030.2	1028.8	1027.5	1026.1
7.5°	1034.4	1031.6	1030.2	1028.8	1027.5	1027.5	1024.7	1022.0	1022.0	1019.2	1016.4
10°	1026.1	1024.7	1022.0	1019.2	1017.8	1016.4	1013.7	1009.5	1008.1	1005.4	1002.6
12.5°	1016.4	1013.7	1010.8	1005.4	1004.0	1002.6	997.0	992.9	990.2	988.7	981.9
15°	1004.0	998.4	994.3	987.3	986.0	983.2	979.1	974.9	969.4	965.2	962.5
17.5°	981.9	976.3	969.4	962.5	959.7	959.7	952.8	947.3	940.4	937.6	932.0
20°	955.5	948.7	943.1	934.8	930.7	926.6	922.4	914.0	908.6	904.3	897.5
22.5°	925.2	915.5	908.6	900.2	893.4	889.2	882.2	875.4	868.4	864.3	858.7
25°	886.4	878.1	867.1	858.7	854.6	849.1	840.8	833.9	826.9	820.1	817.2
27.5°	843.6	832.5	822.8	813.1	809.0	804.8	795.1	786.9	781.3	774.4	771.6
30°	796.5	785.4	774.4	766.2	761.9	755.1	749.5	739.8	733.0	727.4	720.4
32.5°	742.7	734.3	724.7	712.2	709.4	703.9	695.6	691.5	683.2	678.9	673.5
35°	684.5	678.9	669.4	659.7	655.5	652.7	645.8	637.5	632.0	627.9	625.0
37.5°	629.2	622.3	612.6	605.7	602.9	598.8	590.5	586.4	580.8	578.0	572.6
40°	569.7	562.9	555.9	551.8	547.6	544.9	539.3	535.2	529.7	525.5	524.1
42.5°	511.7	507.6	502.0	496.4	495.0	490.9	488.2	484.0	479.9	478.5	474.3
45°	459.1	455.0	449.4	444.0	442.5	439.7	438.4	434.3	431.4	431.4	431.4
47.5°	406.6	402.5	396.9	394.1	395.5	389.9	389.9	388.6	385.8	385.8	387.2
50°	359.6	354.0	352.6	349.9	347.2	344.3	345.7	341.6	341.6	344.3	342.9
52.5°	315.2	309.8	308.4	305.7	304.2	304.2	302.8	302.8	301.4	302.8	302.8
55°	275.2	271.0	268.3	265.5	264.2	264.2	264.2	262.8	261.3	264.2	265.5
57.5°	239.2	237.8	235.1	231.0	229.5	228.1	226.8	226.8	226.8	226.8	228.1
60°	207.4	204.7	201.9	197.7	197.7	196.3	195.0	193.6	193.6	193.6	193.6
62.5°	179.8	175.6	171.5	168.7	167.4	166.0	164.5	161.8	161.8	161.8	161.8
65°	152.1	148.0	145.1	142.4	139.7	139.7	136.9	135.6	132.7	131.3	128.6
67.5°	125.9	123.0	120.3	116.2	114.8	113.4	110.6	109.2	105.1	103.7	102.4
70°	102.4	98.2	95.4	92.7	91.3	88.5	85.7	83.0	80.3	77.4	74.7
72.5°	80.3	76.0	73.3	70.6	67.7	67.7	63.6	60.9	56.7	53.9	49.8
75°	59.5	55.3	52.6	48.3	47.0	45.6	41.5	38.8	34.5	30.4	27.7
77.5°	40.1	37.4	34.5	30.4	27.7	27.7	23.5	20.7	18.0	13.8	12.4
80°	24.9	22.1	19.4	16.5	16.5	13.8	12.4	9.7	6.9	5.6	4.1
82.5°	13.8	12.4	11.1	8.3	8.3	6.9	5.6	4.1	2.7	1.4	1.4
85°	6.9	5.6	4.1	4.1	2.7	2.7	2.7	1.4	1.4	0.0	0.0
87.5°	2.7	1.4	1.4	1.4	1.4	1.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584072

CATALOG NUMBER: HCC8W20D010SL-HM80520935-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	1033.1	1033.1	1031.6	1031.6	1031.6	1030.2	1031.6	1030.2	1030.2	1030.2	1031.6
5°	1027.5	1024.7	1024.7	1023.4	1023.4	1022.0	1023.4	1022.0	1020.5	1019.2	1020.5
7.5°	1016.4	1013.7	1012.3	1010.8	1010.8	1010.8	1009.5	1008.1	1009.5	1005.4	1008.1
10°	1001.2	999.9	997.0	995.7	994.3	995.7	994.3	991.6	991.6	991.6	990.2
12.5°	981.9	979.1	977.8	976.3	973.5	973.5	974.9	972.2	972.2	969.4	969.4
15°	958.4	955.5	952.8	952.8	950.1	950.1	948.7	948.7	947.3	945.8	945.8
17.5°	929.3	925.2	922.4	923.7	922.4	921.0	921.0	918.2	916.9	918.2	918.2
20°	894.8	891.9	889.2	890.5	887.8	886.4	887.8	883.7	885.1	885.1	885.1
22.5°	856.0	854.6	850.4	850.4	847.7	846.3	847.7	847.7	849.1	847.7	847.7
25°	813.1	810.4	807.7	807.7	806.2	804.8	806.2	807.7	806.2	807.7	807.7
27.5°	767.5	763.3	763.3	760.6	760.6	761.9	760.6	761.9	763.3	763.3	766.2
30°	717.7	716.3	715.0	713.6	713.6	715.0	715.0	715.0	716.3	719.1	719.1
32.5°	670.7	667.9	665.1	665.1	667.9	666.5	667.9	667.9	670.7	670.7	673.5
35°	619.5	619.5	616.8	618.2	618.2	618.2	618.2	620.9	623.6	625.0	627.9
37.5°	572.6	568.4	569.7	569.7	571.1	569.7	573.9	573.9	576.7	576.7	579.4
40°	521.4	521.4	522.7	521.4	522.7	522.7	525.5	528.2	529.7	532.4	533.8
42.5°	472.9	475.8	472.9	474.3	475.8	477.1	478.5	479.9	485.4	488.2	492.3
45°	428.7	430.1	431.4	432.8	431.4	434.3	435.6	438.4	442.5	444.0	445.3
47.5°	385.8	387.2	388.6	389.9	389.9	392.8	394.1	396.9	399.6	401.1	402.5
50°	344.3	347.2	348.5	348.5	349.9	352.6	355.4	355.4	358.1	362.3	363.7
52.5°	307.0	307.0	309.8	311.1	312.5	312.5	316.7	318.1	319.5	322.2	324.9
55°	265.5	269.6	271.0	271.0	273.9	276.6	278.0	279.3	279.3	284.9	284.9
57.5°	229.5	231.0	233.7	233.7	233.7	237.8	237.8	240.7	242.0	243.4	246.2
60°	193.6	196.3	196.3	197.7	196.3	199.2	200.5	203.3	204.7	206.0	207.4
62.5°	160.4	160.4	161.8	161.8	161.8	161.8	164.5	164.5	167.4	168.7	170.1
65°	128.6	128.6	128.6	128.6	128.6	128.6	128.6	128.6	130.0	130.0	132.7
67.5°	99.5	98.2	95.4	96.8	95.4	95.4	94.1	94.1	95.4	95.4	98.2
70°	71.9	70.6	67.7	67.7	66.4	65.0	63.6	62.2	60.9	60.9	60.9
72.5°	47.0	44.2	40.1	38.8	38.8	35.9	33.2	31.8	31.8	31.8	31.8
75°	23.5	20.7	18.0	16.5	16.5	13.8	15.2	13.8	13.8	13.8	13.8
77.5°	9.7	6.9	5.6	5.6	5.6	4.1	4.1	4.1	4.1	4.1	4.1
80°	2.7	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584072

CATALOG NUMBER: HCC8W20D010SL-HM80520935-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8	1035.8
2.5°	1030.2	1030.2	1027.5	1028.8	1028.8	1028.8	1028.8	1028.8
5°	1017.8	1019.2	1017.8	1019.2	1019.2	1017.8	1017.8	1017.8
7.5°	1005.4	1006.7	1005.4	1006.7	1006.7	1006.7	1005.4	1005.4
10°	990.2	990.2	990.2	990.2	990.2	988.7	990.2	990.2
12.5°	969.4	969.4	969.4	970.8	970.8	969.4	969.4	968.1
15°	947.3	944.5	945.8	947.3	945.8	945.8	945.8	945.8
17.5°	916.9	918.2	916.9	916.9	916.9	916.9	918.2	916.9
20°	885.1	885.1	886.4	885.1	885.1	885.1	885.1	883.7
22.5°	849.1	847.7	847.7	849.1	849.1	847.7	849.1	849.1
25°	809.0	810.4	809.0	809.0	810.4	810.4	810.4	809.0
27.5°	766.2	767.5	768.9	767.5	767.5	767.5	768.9	770.3
30°	721.8	724.7	721.8	721.8	724.7	723.3	724.7	724.7
32.5°	674.8	678.9	676.2	678.9	678.9	680.4	678.9	680.4
35°	627.9	632.0	632.0	632.0	633.3	634.7	634.7	633.3
37.5°	583.6	585.0	585.0	587.7	589.1	590.5	590.5	589.1
40°	537.9	540.8	542.1	542.1	542.1	544.9	547.6	544.9
42.5°	493.7	495.0	496.4	496.4	499.3	500.6	502.0	502.0
45°	450.8	453.5	455.0	456.4	457.8	460.5	459.1	461.9
47.5°	406.6	410.7	412.0	413.5	416.3	417.6	419.0	420.4
50°	366.4	369.3	369.3	372.0	376.1	376.1	378.9	380.2
52.5°	326.4	327.8	329.1	330.5	333.3	336.0	336.0	338.8
55°	287.6	289.0	289.0	290.4	291.8	297.3	298.7	298.7
57.5°	247.5	247.5	250.3	251.6	253.1	255.8	255.8	255.8
60°	208.9	210.2	210.2	211.6	213.0	215.7	217.1	215.7
62.5°	170.1	171.5	171.5	172.8	175.6	177.1	175.6	175.6
65°	134.2	135.6	135.6	136.9	139.7	139.7	138.3	139.7
67.5°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
70°	62.2	60.9	59.5	60.9	60.9	60.9	59.5	62.2
72.5°	30.4	31.8	31.8	31.8	31.8	31.8	31.8	30.4
75°	13.8	13.8	12.4	12.4	12.4	13.8	13.8	12.4
77.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)