

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593555

Luminaire Tested: **HCC8W15D010BZ-HM80520850-81MDC**

Issue Date: 10/21/2021

### Test Information

Test Method: LM-41-14  
 Report Number: P593555  
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 10/21/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO COMMERCIAL  
 Catalog Number: HCC8W15D010BZ-HM80520850-81MDC  
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
 Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
 CYLINDER  
 Ballast/Driver: ELECTRONIC DRIVER

### Summary


Lumens per Lamp: N/A  
 Luminaire Lumens: 1920.4 lumens  
 Efficiency: N/A  
 Efficacy: 137.2 lumens/watt  
 Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
 Luminous Opening: Circular (Dia: 0.67' x H: 0')  
 CIE Type: Direct

Input Watts (W): 14  
 Input Voltage (V): NR  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



TEST NUMBER: P593555  
CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P593555

CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	73	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114742
5°	109478
10°	94518
15°	72276
20°	55300
25°	43752
30°	33050
35°	17584
40°	6698
45°	3210
50°	1372
55°	575
60°	222
65°	175
70°	108
75°	0
80°	0
85°	0



TEST NUMBER: P593555  
 CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	321.0	16.7
10°-20°	632.0	32.9
20°-30°	588.6	30.7
30°-40°	303.8	15.8
40°-50°	61.9	3.2
50°-60°	10.6	0.6
60°-70°	2.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1541.7	80.3
0°-40°	1845.5	96.1
0°-60°	1917.9	99.9
0°-90°	1920.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1920.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3721	
5°	3537	321
15°	2264	632
25°	1286	589
35°	467	304
45°	74	62
55°	11	11
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P593555  
CATALOG NUMBER: HCC8W15D010BZ-HM80520850-81MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3721.0
2.5°	3671.0
5°	3536.8
7.5°	3315.7
10°	3018.6
12.5°	2628.8
15°	2264.0
17.5°	1947.9
20°	1685.2
22.5°	1471.3
25°	1285.9
27.5°	1110.0
30°	928.2
32.5°	711.9
35°	467.1
37.5°	271.0
40°	166.4
42.5°	109.3
45°	73.6
47.5°	46.4
50°	28.6
52.5°	16.6
55°	10.7
57.5°	4.7
60°	3.6
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)