

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593607

Luminaire Tested: **HCC8S20D010SL-HM80520950-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593607  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S20D010SL-HM80520950-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2113.8 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593607  
CATALOG NUMBER: HCC8S20D010SL-HM80520950-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P593607

CATALOG NUMBER: HCC8S20D010SL-HM80520950-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	94	93	91	96	96		
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	96	94	93	91	96	96		
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	92	90	89	87	92	92		
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	89	87	85	83	89	89		
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	87	84	82	80	86	86		
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	84	81	78	76	83	83		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	81	78	75	73	80	80		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	78	75	72	71	77	77		
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	76	72	69	68	75	75		
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	73	69	67	66	73	73		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	397866
5°	255198
10°	115281
15°	69559
20°	53007
25°	42806
30°	31366
35°	11361
40°	4239
45°	1923
50°	614
55°	151
60°	86
65°	102
70°	0
75°	0
80°	249
85°	495



TEST NUMBER: P593607  
 CATALOG NUMBER: HCC8S20D010SL-HM80520950-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	628.8	29.7
10°-20°	638.7	30.2
20°-30°	571.7	27.0
30°-40°	230.3	10.9
40°-50°	37.8	1.8
50°-60°	3.4	0.2
60°-70°	1.2	0.1
70°-80°	0.9	0.0
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1839.2	87.0
0°-40°	2069.5	97.9
0°-60°	2110.7	99.9
0°-90°	2114.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2113.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12902	
5°	8244	629
15°	2179	639
25°	1258	572
35°	302	230
45°	44	38
55°	3	3
65°	1	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P593607  
CATALOG NUMBER: HCC8S20D010SL-HM80520950-81NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12902.5
0.5°	12862.6
1°	12696.1
1.5°	12428.5
2°	12022.9
2.5°	11543.3
3°	10942.7
3.5°	10283.8
4°	9632.0
4.5°	8901.9
5°	8244.4
5.5°	7528.5
6°	6947.9
6.5°	6343.1
7°	5867.7
7.5°	5365.3
8°	4961.2
8.5°	4555.5
9°	4250.9
9.5°	3915.1
10°	3681.7
12.5°	2715.4
15°	2178.9
17.5°	1861.5
20°	1615.3
22.5°	1418.9
25°	1258.1
27.5°	1097.3
30°	880.9
32.5°	566.4
35°	301.8
37.5°	166.5
40°	105.3
42.5°	69.7
45°	44.1
47.5°	27.1
50°	12.8
52.5°	4.3
55°	2.8
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4



TEST NUMBER: P593607  
CATALOG NUMBER: HCC8S20D010SL-HM80520950-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	1.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.4
70°		0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)