

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584115

Luminaire Tested: **HCC8W25D010MW-HM82555827-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MW-HM82555827-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2338.2 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584115
CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P584115

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75			
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65			
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57			
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50			
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45			
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40			
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33			
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35850	35850	35850
5°	37160	35730	34505
10°	38210	35420	33091
15°	39066	34794	31630
20°	39126	33439	30348
25°	38376	31578	29274
30°	36397	29283	27987
35°	33074	26667	26731
40°	28918	23931	25191
45°	25062	21316	23475
50°	21943	18935	21391
55°	19532	16779	19360
60°	17620	15073	17003
65°	15906	13258	14819
70°	14299	11171	11017
75°	12593	8864	8257
80°	10566	7334	7920
85°	8173	6439	7005



TEST NUMBER: P584115

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.7	4.7
10°-20°	308.9	13.2
20°-30°	441.5	18.9
30°-40°	469.1	20.1
40°-50°	403.9	17.3
50°-60°	302.0	12.9
60°-70°	192.6	8.2
70°-80°	87.6	3.7
80°-90°	23.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	860.1	36.8
0°-40°	1329.2	56.8
0°-60°	2035.0	87.0
0°-90°	2338.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2338.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1163	1163	1163	1163	1163	
5°	1200	1184	1154	1125	1115	115
15°	1224	1182	1090	1016	991	345
25°	1128	1057	928	872	860	516
35°	879	818	708	690	710	547
45°	575	543	489	502	538	447
55°	363	334	312	338	360	327
65°	218	193	182	190	203	217
75°	106	91	74	68	69	112
85°	23	20	18	20	20	28
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584115

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	1184.1	1180.7	1182.4	1180.7	1182.4	1182.4	1179.1	1179.1	1179.1	1179.1	1174.1
5°	1200.5	1198.9	1198.9	1197.2	1195.6	1197.2	1195.6	1193.9	1190.7	1189.0	1184.1
7.5°	1210.5	1210.5	1210.5	1210.5	1208.8	1207.2	1205.6	1202.3	1198.9	1195.6	1192.3
10°	1220.3	1222.0	1220.3	1218.7	1217.1	1213.8	1212.1	1208.8	1203.9	1198.9	1195.6
12.5°	1225.4	1225.4	1223.7	1223.7	1220.3	1218.7	1213.8	1208.8	1203.9	1198.9	1190.7
15°	1223.7	1223.7	1222.0	1220.3	1215.4	1213.8	1210.5	1205.6	1197.2	1190.7	1182.4
17.5°	1213.8	1212.1	1208.8	1208.8	1202.3	1200.5	1197.2	1190.7	1182.4	1172.5	1162.6
20°	1192.3	1192.3	1190.7	1189.0	1182.4	1177.4	1174.1	1165.9	1159.2	1147.7	1137.8
22.5°	1162.6	1165.9	1162.6	1159.2	1151.0	1149.4	1144.4	1134.5	1124.6	1111.4	1099.9
25°	1127.9	1126.3	1124.6	1121.3	1114.7	1111.4	1104.8	1094.8	1085.0	1070.1	1056.8
27.5°	1083.3	1076.7	1076.7	1070.1	1065.2	1060.2	1056.8	1047.0	1033.7	1022.2	1005.7
30°	1022.2	1023.9	1015.6	1013.9	1005.7	1002.4	995.7	985.9	974.3	961.1	947.9
32.5°	956.2	951.2	951.2	944.6	938.0	933.0	931.4	919.9	909.9	896.7	883.5
35°	878.6	878.6	873.5	871.9	865.3	862.0	857.1	850.4	838.9	827.3	817.5
37.5°	802.6	799.3	797.6	794.4	789.3	784.4	784.4	772.9	771.1	758.0	744.8
40°	718.4	721.6	718.4	713.4	711.8	708.4	706.8	700.2	695.3	683.7	675.4
42.5°	647.4	644.0	644.0	642.4	635.8	635.8	632.5	629.2	620.9	617.6	607.8
45°	574.7	578.0	573.0	574.7	568.1	568.1	568.1	561.4	554.9	549.9	543.3
47.5°	511.9	513.6	513.6	508.7	507.0	507.0	503.6	500.3	495.4	488.8	483.9
50°	457.4	459.1	455.8	454.1	450.8	449.2	449.2	442.6	439.2	432.7	429.4
52.5°	407.9	407.9	406.3	406.3	401.2	401.2	397.9	393.0	389.7	386.4	378.1
55°	363.3	363.3	361.7	360.1	360.1	355.0	353.4	348.4	345.2	338.5	333.6
57.5°	320.4	322.1	320.4	318.8	317.0	315.4	312.1	307.2	303.9	298.9	295.6
60°	285.7	285.7	284.1	282.4	279.1	277.5	275.7	272.5	267.5	264.2	259.3
62.5°	252.6	251.0	249.3	247.7	244.4	244.4	241.1	237.8	232.8	229.5	226.2
65°	218.0	218.0	216.4	216.4	214.6	211.3	209.7	208.1	201.5	199.8	193.2
67.5°	186.6	188.2	185.0	185.0	181.7	181.7	180.0	175.1	173.4	170.1	166.8
70°	158.6	158.6	158.6	156.9	153.5	151.9	150.2	147.0	145.3	142.0	138.7
72.5°	130.4	130.4	128.8	128.8	127.1	125.5	123.9	120.6	120.6	117.3	114.0
75°	105.7	105.7	104.0	102.4	100.7	100.7	99.1	97.5	94.2	92.4	90.8
77.5°	80.9	80.9	80.9	79.3	77.6	77.6	77.6	74.4	71.0	71.0	69.3
80°	59.5	59.5	57.8	57.8	56.2	56.2	56.2	54.5	52.9	51.1	49.5
82.5°	39.6	39.6	39.6	39.6	38.0	38.0	38.0	36.4	34.7	34.7	34.7
85°	23.1	23.1	23.1	23.1	21.5	21.5	21.5	21.5	21.5	19.8	19.8
87.5°	10.0	8.2	10.0	8.2	10.0	8.2	10.0	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584115

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	1175.8	1174.1	1172.5	1170.8	1170.8	1169.2	1165.9	1164.3	1162.6	1161.0	1161.0
5°	1182.4	1180.7	1177.4	1174.1	1172.5	1169.2	1165.9	1162.6	1159.2	1154.3	1152.7
7.5°	1187.4	1182.4	1179.1	1172.5	1170.8	1167.6	1162.6	1157.6	1151.0	1144.4	1139.4
10°	1187.4	1180.7	1175.8	1167.6	1164.3	1161.0	1154.3	1146.1	1137.8	1131.2	1123.0
12.5°	1184.1	1175.8	1167.6	1159.2	1154.3	1149.4	1139.4	1131.2	1121.3	1111.4	1104.8
15°	1172.5	1162.6	1152.7	1142.8	1137.8	1131.2	1121.3	1109.7	1099.9	1089.9	1078.3
17.5°	1151.0	1141.2	1129.6	1118.0	1111.4	1106.5	1091.6	1083.3	1068.5	1058.6	1048.6
20°	1123.0	1111.4	1096.5	1085.0	1076.7	1071.7	1060.2	1045.3	1033.7	1019.0	1009.0
22.5°	1086.6	1071.7	1056.8	1045.3	1037.0	1030.5	1015.6	1000.8	990.8	977.7	966.1
25°	1043.7	1028.8	1013.9	997.5	989.2	982.6	969.4	956.2	943.0	928.1	918.2
27.5°	992.5	975.9	962.8	947.9	939.7	929.7	914.8	901.7	888.4	878.6	865.3
30°	936.4	918.2	905.0	890.1	881.9	873.5	858.7	845.5	834.0	822.4	815.8
32.5°	868.6	855.5	842.2	827.3	820.7	815.8	800.9	787.7	774.5	764.6	759.6
35°	804.2	789.3	777.8	764.6	756.4	751.4	738.2	726.6	720.0	708.4	701.8
37.5°	736.5	724.9	711.8	698.5	693.6	688.7	678.7	667.1	657.3	649.0	645.7
40°	665.5	655.6	644.0	635.8	630.9	625.8	617.6	609.4	602.7	594.5	591.2
42.5°	597.8	591.2	581.3	571.4	566.5	564.7	554.9	548.3	545.0	541.6	538.3
45°	536.7	526.8	520.2	513.6	508.7	505.4	500.3	495.4	492.1	488.8	485.5
47.5°	477.2	469.0	462.3	457.4	452.5	450.8	447.6	442.6	439.2	439.2	439.2
50°	422.8	416.1	409.6	406.3	404.6	401.2	397.9	396.3	394.7	394.7	394.7
52.5°	374.8	368.3	363.3	360.1	360.1	356.7	353.4	351.7	351.7	351.7	351.7
55°	330.3	325.3	322.1	318.8	315.4	313.7	313.7	313.7	312.1	312.1	313.7
57.5°	290.6	287.3	282.4	279.1	277.5	277.5	275.7	274.1	275.7	277.5	279.1
60°	254.3	251.0	249.3	244.4	244.4	244.4	242.8	242.8	242.8	244.4	246.1
62.5°	221.3	219.7	216.4	214.6	213.0	213.0	211.3	211.3	211.3	211.3	213.0
65°	191.5	188.2	185.0	185.0	185.0	183.3	183.3	180.0	181.7	181.7	180.0
67.5°	163.5	160.2	158.6	156.9	155.3	155.3	153.5	151.9	150.2	150.2	150.2
70°	137.1	133.8	133.8	130.4	130.4	128.8	127.1	127.1	125.5	123.9	122.2
72.5°	110.6	109.0	107.3	105.7	105.7	105.7	104.0	102.4	100.7	99.1	95.8
75°	87.5	87.5	84.2	82.6	82.6	80.9	79.3	77.6	76.0	74.4	72.7
77.5°	67.7	66.0	62.7	61.1	61.1	61.1	59.5	57.8	56.2	54.5	52.9
80°	49.5	47.9	46.2	44.6	44.6	44.6	42.9	42.9	41.3	41.3	41.3
82.5°	33.1	33.1	31.4	31.4	31.4	31.4	29.7	29.7	29.7	29.7	29.7
85°	19.8	19.8	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
87.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584115

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	1157.6	1157.6	1154.3	1152.7	1151.0	1152.7	1149.4	1147.7	1146.1	1146.1	1144.4
5°	1147.7	1146.1	1139.4	1137.8	1136.1	1134.5	1131.2	1127.9	1124.6	1123.0	1121.3
7.5°	1134.5	1129.6	1123.0	1121.3	1119.6	1114.7	1109.7	1106.5	1101.5	1099.9	1096.5
10°	1116.3	1109.7	1104.8	1099.9	1096.5	1091.6	1086.6	1081.7	1075.0	1073.4	1068.5
12.5°	1094.8	1086.6	1076.7	1075.0	1070.1	1063.5	1056.8	1051.9	1047.0	1043.7	1038.8
15°	1068.5	1060.2	1050.3	1045.3	1040.4	1035.4	1027.2	1020.6	1015.6	1010.6	1005.7
17.5°	1037.0	1027.2	1019.0	1013.9	1010.6	1002.4	995.7	987.5	982.6	977.7	972.6
20°	999.1	990.8	979.3	974.3	972.6	966.1	957.8	954.5	947.9	943.0	939.7
22.5°	956.2	947.9	938.0	934.6	928.1	924.8	916.6	913.2	909.9	905.0	903.3
25°	908.2	900.0	891.7	890.1	885.1	881.9	876.9	871.9	871.9	867.0	867.0
27.5°	858.7	850.4	843.9	840.6	838.9	835.6	830.6	829.0	827.3	825.7	825.7
30°	805.9	796.0	792.7	791.1	789.3	786.0	784.4	781.1	782.8	784.4	782.8
32.5°	749.7	746.4	739.8	736.5	738.2	736.5	733.3	736.5	734.9	738.2	739.8
35°	695.3	692.0	688.7	688.7	685.3	685.3	685.3	686.9	690.3	692.0	695.3
37.5°	642.4	637.4	635.8	634.1	635.8	635.8	635.8	639.1	642.4	645.7	650.7
40°	586.3	582.9	582.9	582.9	582.9	587.9	586.3	589.6	592.9	597.8	602.7
42.5°	533.4	533.4	535.0	535.0	535.0	535.0	538.3	543.3	548.3	553.2	558.2
45°	483.9	483.9	483.9	487.2	487.2	488.8	495.4	498.7	502.0	507.0	511.9
47.5°	437.6	437.6	439.2	440.9	442.6	445.9	449.2	454.1	459.1	462.3	467.4
50°	394.7	396.3	399.6	403.0	403.0	404.6	409.6	412.8	416.1	421.2	422.8
52.5°	353.4	356.7	360.1	361.7	363.3	366.6	368.3	373.2	374.8	379.8	381.5
55°	315.4	317.0	322.1	323.7	323.7	327.0	330.3	333.6	338.5	338.5	341.9
57.5°	280.8	282.4	285.7	287.3	285.7	290.6	292.3	295.6	297.2	300.6	302.2
60°	246.1	249.3	251.0	251.0	252.6	254.3	257.7	257.7	261.0	264.2	264.2
62.5°	213.0	214.6	216.4	218.0	219.7	218.0	223.0	223.0	226.2	227.9	231.2
65°	181.7	183.3	183.3	185.0	185.0	186.6	186.6	188.2	189.9	193.2	194.8
67.5°	150.2	150.2	150.2	151.9	150.2	151.9	151.9	153.5	153.5	156.9	158.6
70°	122.2	120.6	118.9	118.9	118.9	118.9	117.3	118.9	118.9	120.6	120.6
72.5°	94.2	92.4	90.8	89.1	89.1	87.5	85.9	87.5	87.5	89.1	89.1
75°	71.0	67.7	67.7	67.7	66.0	66.0	66.0	67.7	67.7	67.7	69.3
77.5°	52.9	52.9	51.1	51.1	51.1	52.9	52.9	54.5	54.5	54.5	54.5
80°	39.6	41.3	41.3	41.3	41.3	42.9	42.9	42.9	42.9	44.6	44.6
82.5°	29.7	29.7	29.7	29.7	31.4	31.4	31.4	31.4	31.4	31.4	31.4
85°	18.2	19.8	19.8	18.2	19.8	19.8	19.8	19.8	19.8	19.8	19.8
87.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584115

CATALOG NUMBER: HCC8W25D010MW-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6	1162.6
2.5°	1142.8	1142.8	1142.8	1142.8	1141.2	1141.2	1141.2	1139.4
5°	1118.0	1118.0	1118.0	1114.7	1116.3	1116.3	1113.0	1114.7
7.5°	1093.2	1091.6	1089.9	1089.9	1088.3	1086.6	1085.0	1086.6
10°	1065.2	1060.2	1060.2	1058.6	1058.6	1055.2	1055.2	1056.8
12.5°	1033.7	1030.5	1030.5	1028.8	1027.2	1025.5	1023.9	1023.9
15°	1002.4	999.1	997.5	995.7	994.1	990.8	992.5	990.8
17.5°	971.0	966.1	966.1	964.4	962.8	959.5	959.5	957.8
20°	934.6	933.0	929.7	931.4	929.7	926.4	924.8	924.8
22.5°	898.4	898.4	896.7	896.7	895.1	893.4	891.7	891.7
25°	863.7	862.0	863.7	863.7	858.7	858.7	858.7	860.4
27.5°	824.0	825.7	824.0	824.0	824.0	824.0	825.7	824.0
30°	784.4	784.4	784.4	786.0	789.3	787.7	787.7	786.0
32.5°	741.5	743.1	743.1	744.8	746.4	749.7	749.7	751.4
35°	698.5	701.8	703.5	701.8	706.8	706.8	710.1	710.1
37.5°	654.0	655.6	658.9	660.5	663.8	665.5	667.1	667.1
40°	606.0	612.7	614.3	616.0	620.9	620.9	622.5	625.8
42.5°	561.4	568.1	569.8	571.4	574.7	579.6	578.0	581.3
45°	518.5	523.4	525.2	526.8	531.8	533.4	533.4	538.3
47.5°	472.3	475.6	477.2	480.5	483.9	487.2	490.5	488.8
50°	426.1	431.0	434.3	435.9	440.9	442.6	444.3	445.9
52.5°	384.8	388.1	389.7	391.4	396.3	397.9	399.6	403.0
55°	345.2	346.8	350.1	348.4	353.4	355.0	356.7	360.1
57.5°	305.5	307.2	308.8	308.8	312.1	315.4	317.0	318.8
60°	267.5	270.8	272.5	272.5	272.5	275.7	275.7	275.7
62.5°	232.8	232.8	234.5	234.5	237.8	237.8	237.8	237.8
65°	196.6	198.2	199.8	199.8	203.1	201.5	204.8	203.1
67.5°	158.6	158.6	161.8	161.8	160.2	161.8	161.8	161.8
70°	120.6	120.6	122.2	122.2	122.2	122.2	122.2	122.2
72.5°	89.1	89.1	89.1	90.8	89.1	89.1	90.8	89.1
75°	69.3	69.3	69.3	69.3	69.3	69.3	69.3	69.3
77.5°	54.5	54.5	56.2	56.2	56.2	56.2	56.2	56.2
80°	44.6	44.6	44.6	44.6	46.2	44.6	44.6	44.6
82.5°	33.1	31.4	33.1	31.4	33.1	33.1	33.1	33.1
85°	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.8
87.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)