

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584124

Luminaire Tested: **HCC8S25D010BZ-HM82555830-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010BZ-HM82555830-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2231.7 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584124
CATALOG NUMBER: HCC8S25D010BZ-HM82555830-81RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584124

CATALOG NUMBER: HCC8S25D010BZ-HM82555830-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36711	36711	36711
5°	37399	36548	35702
10°	37985	35912	34396
15°	38363	35018	32904
20°	38220	33665	31391
25°	37209	31724	29638
30°	35439	29408	27916
35°	32001	26837	25929
40°	28117	24092	24024
45°	24268	21177	22088
50°	21127	18570	19808
55°	18730	16128	17257
60°	16713	13630	14327
65°	15067	11061	11295
70°	13380	8286	6690
75°	11533	4801	2883
80°	8879	1705	852
85°	5732	566	566



TEST NUMBER: P584124

CATALOG NUMBER: HCC8S25D010BZ-HM82555830-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.8	5.0
10°-20°	311.1	13.9
20°-30°	440.0	19.7
30°-40°	463.7	20.8
40°-50°	394.1	17.7
50°-60°	283.7	12.7
60°-70°	163.7	7.3
70°-80°	56.0	2.5
80°-90°	7.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.9	38.7
0°-40°	1326.5	59.4
0°-60°	2004.3	89.8
0°-90°	2231.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2231.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1190	1190	1190	1190	1190	
5°	1208	1200	1181	1160	1153	115
15°	1202	1165	1097	1048	1031	338
25°	1094	1037	932	884	871	502
35°	850	800	713	687	689	529
45°	556	531	486	489	506	432
55°	348	321	300	311	321	314
65°	206	177	152	148	155	205
75°	97	72	40	26	24	102
85°	16	10	2	2	2	22
90°	0	0	0	0	0	



TEST NUMBER: P584124

CATALOG NUMBER: HCC8S25D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5
2.5°	1201.7	1203.3	1201.7	1201.7	1200.1	1198.5	1196.9	1195.3	1192.1	1188.9	1188.9
5°	1208.2	1211.5	1208.2	1208.2	1203.3	1200.1	1196.9	1192.1	1185.7	1180.7	1180.7
7.5°	1213.1	1213.1	1213.1	1208.2	1204.9	1200.1	1192.1	1184.0	1175.9	1167.9	1164.7
10°	1213.1	1213.1	1211.5	1204.9	1201.7	1192.1	1184.0	1172.7	1161.4	1150.1	1146.9
12.5°	1208.2	1209.8	1206.6	1200.1	1192.1	1180.7	1169.5	1155.0	1142.1	1129.2	1122.8
15°	1201.7	1200.1	1196.9	1188.9	1179.1	1164.7	1153.4	1137.2	1119.4	1103.4	1096.9
17.5°	1185.7	1185.7	1180.7	1172.7	1159.8	1143.7	1126.0	1108.2	1088.8	1071.1	1063.0
20°	1164.7	1164.7	1158.2	1148.5	1135.6	1114.6	1095.3	1074.3	1051.7	1033.9	1025.9
22.5°	1134.0	1135.6	1127.6	1116.2	1101.8	1077.5	1058.2	1032.3	1009.8	988.8	982.4
25°	1093.6	1096.9	1088.8	1077.5	1058.2	1037.3	1013.0	988.8	963.0	942.0	932.4
27.5°	1046.9	1048.5	1040.5	1029.1	1009.8	987.2	963.0	937.2	913.0	890.5	880.7
30°	995.3	988.8	985.6	971.0	950.2	930.8	903.3	882.3	856.5	837.2	825.9
32.5°	922.7	925.9	916.2	904.9	888.8	866.3	843.7	819.4	795.2	780.8	772.6
35°	850.1	853.3	848.5	837.2	819.4	800.0	777.5	759.8	738.8	721.1	712.9
37.5°	774.3	774.3	771.0	764.6	751.7	733.9	711.3	693.6	675.9	661.4	656.6
40°	698.5	695.3	693.6	688.8	677.5	661.4	646.8	632.4	614.6	604.9	598.5
42.5°	624.2	624.2	621.0	616.2	604.9	596.8	582.3	566.2	553.3	543.6	543.6
45°	556.5	558.1	553.3	550.1	543.6	530.7	517.8	506.5	495.2	488.8	485.6
47.5°	496.8	496.8	492.0	488.8	482.4	471.0	459.8	450.0	442.0	437.1	435.5
50°	440.4	440.4	440.4	432.3	424.3	416.1	408.1	396.9	391.9	388.7	387.1
52.5°	391.9	390.3	390.3	383.9	375.9	366.2	358.1	348.4	343.6	340.4	342.0
55°	348.4	348.4	346.8	338.8	330.6	321.0	313.0	304.8	301.6	298.4	300.0
56°	330.6	330.6	329.0	322.6	313.0	304.8	295.2	287.1	282.3	283.9	283.9
57°	317.8	314.6	314.6	306.4	298.4	287.1	279.1	271.0	267.8	266.1	266.1
58°	301.6	300.0	298.4	290.4	282.3	272.6	264.5	256.5	251.7	251.7	250.1
59°	285.5	285.5	282.3	275.8	267.8	258.1	250.1	241.9	237.1	235.5	235.5
60°	271.0	272.6	267.8	261.3	254.9	243.5	233.9	227.5	222.6	221.0	221.0
61°	258.1	258.1	254.9	246.8	238.7	230.7	221.0	212.9	209.7	206.5	206.5
62°	246.8	243.5	241.9	233.9	225.9	216.1	208.1	200.0	195.2	192.0	193.6
63°	232.3	230.7	227.5	221.0	212.9	203.3	193.6	187.1	182.3	177.4	179.0
64°	221.0	219.4	214.5	208.1	200.0	190.4	180.6	174.2	171.0	166.2	164.6
65°	206.5	204.9	203.3	195.2	187.1	177.4	169.4	163.0	158.0	154.8	151.6
66°	193.6	195.2	192.0	185.5	175.8	167.8	156.4	150.0	146.8	142.0	138.7
67°	182.3	182.3	179.0	172.6	163.0	154.8	146.8	138.7	133.9	129.0	127.4
67.5°	175.8	175.8	172.6	164.6	158.0	148.4	140.4	133.9	127.4	124.2	121.0
68°	169.4	169.4	167.8	161.4	153.2	143.6	135.5	127.4	121.0	116.1	114.5
69°	158.0	159.6	156.4	150.0	142.0	132.3	124.2	117.8	111.3	106.5	103.3
70°	148.4	146.8	143.6	137.1	129.0	122.6	114.5	106.5	100.0	93.5	91.9
71°	135.5	135.5	132.3	127.4	119.4	111.3	103.3	96.8	90.3	82.3	80.7
72°	125.8	125.8	122.6	116.1	109.7	101.6	93.5	85.5	80.7	72.5	69.3
72.5°	119.4	121.0	117.8	111.3	104.9	95.1	88.7	82.3	74.2	67.7	64.5
73°	116.1	114.5	112.9	106.5	98.4	91.9	83.9	77.5	69.3	62.9	59.7



TEST NUMBER: P584124
 CATALOG NUMBER: HCC8S25D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	72.5	72.5	70.9	64.5	58.1	51.6	45.2	38.7	32.3	25.8	22.6
80°	50.0	51.6	48.4	45.2	40.3	33.9	27.4	22.6	16.2	12.9	9.6
82.5°	32.3	32.3	30.6	27.4	24.2	19.4	16.2	11.3	8.0	6.4	4.8
85°	16.2	17.8	16.2	14.6	11.3	9.6	8.0	4.8	3.2	1.6	1.6
87.5°	6.4	6.4	6.4	4.8	4.8	3.2	1.6	1.6	1.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584124

CATALOG NUMBER: HCC8S25D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5	1190.5
2.5°	1185.7	1185.7	1182.4	1180.7	1179.1	1177.5	1175.9	1174.3	1174.3	1175.9
5°	1175.9	1172.7	1166.3	1164.7	1159.8	1158.2	1155.0	1153.4	1155.0	1153.4
7.5°	1161.4	1155.0	1146.9	1143.7	1137.2	1134.0	1129.2	1129.2	1126.0	1127.6
10°	1142.1	1132.4	1122.8	1116.2	1111.4	1106.6	1103.4	1100.2	1098.5	1098.5
12.5°	1117.8	1106.6	1096.9	1087.2	1079.2	1075.9	1069.5	1069.5	1066.3	1064.6
15°	1090.4	1075.9	1064.6	1054.9	1048.5	1042.1	1037.3	1033.9	1030.7	1030.7
17.5°	1054.9	1042.1	1030.7	1019.5	1009.8	1004.9	1000.1	995.3	995.3	992.0
20°	1016.3	1001.7	992.0	980.8	972.7	964.6	958.2	958.2	955.0	956.6
22.5°	972.7	955.0	945.2	937.2	929.2	922.7	916.2	916.2	914.6	913.0
25°	924.3	909.8	898.5	888.8	883.9	877.5	875.9	872.7	871.1	871.1
27.5°	872.7	861.4	846.9	842.0	835.6	832.4	832.4	830.7	827.5	829.1
30°	817.8	805.0	796.8	793.6	787.2	787.2	785.6	782.4	782.4	784.0
32.5°	764.6	751.7	745.3	743.7	737.2	737.2	735.5	737.2	737.2	738.8
35°	706.5	695.3	693.6	688.8	687.2	687.2	687.2	690.4	693.6	688.8
37.5°	651.7	643.6	638.8	637.2	638.8	638.8	640.4	645.2	643.6	642.0
40°	595.2	588.8	585.5	585.5	588.8	592.0	592.0	596.8	598.5	596.8
42.5°	538.7	533.9	533.9	535.5	538.7	540.4	545.3	550.1	551.7	553.3
45°	485.6	485.6	485.6	487.2	488.8	492.0	498.4	503.3	504.9	506.5
47.5°	433.9	432.3	437.1	438.8	443.6	445.2	450.0	456.5	458.1	459.8
50°	385.5	388.7	390.3	395.3	398.5	398.5	404.9	408.1	412.9	412.9
52.5°	340.4	345.2	346.8	351.6	353.3	354.9	358.1	362.9	366.2	366.2
55°	300.0	301.6	304.8	306.4	311.4	313.0	316.2	317.8	322.6	321.0
56°	282.3	285.5	287.1	290.4	293.6	295.2	298.4	300.0	303.2	304.8
57°	266.1	267.8	272.6	274.2	277.5	277.5	279.1	283.9	283.9	285.5
58°	250.1	253.3	254.9	256.5	259.7	261.3	264.5	266.1	267.8	266.1
59°	235.5	237.1	238.7	238.7	241.9	241.9	246.8	250.1	251.7	251.7
60°	221.0	221.0	222.6	224.3	227.5	229.1	229.1	232.3	232.3	232.3
61°	206.5	206.5	208.1	209.7	211.3	211.3	214.5	214.5	216.1	217.7
62°	193.6	192.0	192.0	193.6	193.6	196.8	198.4	200.0	201.6	200.0
63°	179.0	177.4	177.4	177.4	177.4	180.6	180.6	182.3	185.5	183.9
64°	163.0	163.0	163.0	163.0	164.6	164.6	167.8	169.4	171.0	172.6
65°	151.6	148.4	146.8	146.8	148.4	150.0	151.6	153.2	154.8	154.8
66°	138.7	135.5	133.9	133.9	133.9	133.9	137.1	137.1	140.4	140.4
67°	124.2	121.0	119.4	117.8	117.8	117.8	122.6	121.0	121.0	121.0
67.5°	119.4	114.5	112.9	111.3	109.7	112.9	111.3	112.9	112.9	111.3
68°	112.9	109.7	106.5	103.3	103.3	103.3	104.9	106.5	104.9	103.3
69°	100.0	98.4	93.5	90.3	88.7	90.3	88.7	90.3	88.7	90.3
70°	88.7	83.9	79.1	77.5	75.9	75.9	75.9	74.2	75.9	74.2
71°	77.5	72.5	67.7	64.5	62.9	62.9	61.3	62.9	61.3	62.9
72°	66.1	61.3	54.9	51.6	51.6	51.6	51.6	50.0	51.6	50.0
72.5°	61.3	54.9	50.0	46.8	45.2	45.2	45.2	45.2	43.5	45.2
73°	56.5	50.0	43.5	41.9	41.9	41.9	40.3	38.7	40.3	40.3



TEST NUMBER: P584124
CATALOG NUMBER: HCC8S25D010BZ-HM82555830-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	19.4	14.6	12.9	12.9	12.9	12.9	12.9	12.9	11.3	11.3
80°	8.0	6.4	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	104.9	104.9	101.6	96.8	88.7	80.7	74.2	67.7	59.7	51.6	48.4
75°	96.8	95.1	91.9	87.1	80.7	72.5	66.1	58.1	51.6	43.5	40.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	46.8	38.7	35.5	32.3	32.3	32.3	30.6	30.6	30.6	32.3
75°	37.1	30.6	27.4	24.2	25.8	24.2	25.8	24.2	24.2	24.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)